

SEFRAM9825 Datalogger, Carbon Dioxide (CO₂) Meter (NDIR)

■ Features :

- CO₂, humidity and temperature sensors
- Dual wavelength NDIR CO₂ sensor (Non-Dispersive Infrared) for superior stability
- User operated CO₂ calibration
- Data Hold & Max/Min/STEL/TWA function
- Adjustable auto power off timer
- Internal CO₂ alarm buzzer
- Datalogging up to 32,000 sets
- USB interface, PC software included
- Backlight display function



Generales Specifications

Measurement Range	
CO ₂	0 to 30000 ppm (5000~30000 ppm over range)
Temperature	-20 to 60°C (-4°F to 140°F)
Humidity	0 to 100%RH
Accuracy	
CO ₂	1 ppm
Temperature	0,1°C / 0,1°F
Humidity	0,1% RH
Précision	
CO ₂	±(75 ppm + 3% of reading) (0-5000 ppm)
Temperature	±0.8°C
Humidity	± 3%RH
Response Time	
	20 seconds
Power Source	
	9V alkaline battery or Micro USB
Operating Condition	
	0°C to 50°C (< 90%RH)
Storage Condition	
	-20°C to 60°C (< 75%RH)
Battery life	
	Approximately 10 hours normal use (alkaline battery)
Dimensions	
	284,5 x 65 x 38,5 mm
Weight	
	304 g

Supply with : Battery, Instruction manual downloadable on our website, micro USB cable, Windows software, Carrying case.

For assistance and ordering



FT SEFRAM9825 A00 - Specifications can be updated without notice

Sefram

32, rue Edouard Martel - BP55- 42009 - St Etienne - cedex 2
Tél. +33 (0) 4.77.59.01.01 / Fax. +33 (0) 4.77.57.23.23
Web : www.sefram.com - e-mail : sales@sefram.com



1997/7001



Follow us on :



Visit our website: www.sefram.com