

9825A-L(AM10267L)—13.2W CEC SWITCHING ADAPTOR SPECIFICATIONS

RD	1								
Ver: 0	Ver: 0 Date: 2011/2/22		AMPLUS	AM10267L	doc	Pag	ge	1	

Prepared by: Checked by: Approved by:

TABLE OF CONTENTS

- 1. SCOPE
- 2. SPECIFICATION NUMBER
- 3. ENVIRONMENTAL REQUIREMENTS
- 4. INPUT REQUIREMENTS
- 5. INTRODUCTION
- 6. DC INSULATION RESISTANCE
- 7. DIELECTRIC WITHSTAND-VOLTAGE
- 8. MAIN FUSE
- 9. INRUSH CURRENT
- 10. TIME SEQUENCE
- 11. EFFICIENCY
- 12. SAFETY STANDARD
- 13. RFI EMISSION
- 14. OUTPUT RATED & ELECTRICAL SPECIFICATIONS
- 15. RELIABILITY
- 16. OUTLOOK DRAWING
- 17. NAME PLATE
- 18. MODEL LIST

RD	1								
Ver: 0		Date: 2	2011/2/22	AMPLUS	AM10267I	doc	Pa	ge	2

1. SCOPE

This document is applied to 9825A-L(AM10267L) model for S.M.P.S

2. SPECIFICATION NUMBER

AMPLUS part number: 9825A-L(AM10267L)

Customer part number:

3. ENVIRONMENTAL REQUIREMENTS

Operating temperature: 0 -- 40

Storage temperature :-25 -- +85

Operating humidity : 30% -- 95%

Storage humidity : 30% --98%

Operating bar : 1BAR

4. INPUT REQUIREMENTS

Regular input voltage: AC 100 -AC 240V

Variable input voltage range: AC 90V—AV264V

Rating frequency: 50Hz—60Hz Frequency range: 47Hz—63Hz

Input current: 0.3Arms MAX (at regular voltage & current)

5. INTRODUCTION

The S.M.P.S Particular design for 2-pin multi-plug.

The S.M.P.S A variety of efficiency work mode for saving power.

The S.M.P.S Overcurrent, overload, overheat, undervoltage protection.

The S.M.P.S Advanced dithering switch work mode, reduce electromagnetic interference

The S.M.P.S Overshock resistance switch circuit design, prevent device from instant implus damage

The S.M.P.S Design with environment friendly materials, safe and healthy.

The S.M.P.S operated at input regular voltage AC 100V – 240V.

The S.M.P.S should be capable of a total continuous DC power output of 13.2 Watts.

The S.M.P.S should be capable of a total peak 15 Watts.

The S.M.P.S designed a energy saving to meet Europe energy star standard.

The S.M.P.S should be able to single output only. Refer output rated and electrical specifications table.

The S.M.P.S will shut down automatically when the AC input voltage lower than AC 90 V.

The S.M.P.S output voltage will drop to very low when overload by overload protection.

RD	1								
Ver: 0		Date: 2	2011/2/22	AMPLUS	AM10267I	doc	Pa	ige	3

The S.M.P.S should not be fired or emitted smoke by protection when the circuit is short.

The S.M.P.S can be changeable output voltage by changeable slot.

6. DC INSULATION RESISTANCE

Input – Output : 50MΩminimum (at 500VDC)

Input – Body metal : $50M\Omega$ minimum (at 500VDC)

7. DIELECTRIC WITHSTAND - VOLTAGE

Input – Output : 3750VAC minimum (2s)

Input – Body metal : 3750VAC minimum (2s)

8. MAIN FUSE

Input fuse is 2 OHM 1W fusible resistor


9. INRUSH CURRENT

Peak inrush current shall be limited to 10A for a cold start

10. TIME SEQUENCE

Time sequence should be satisfied to power ON/OFF, restart in power failure

AC switch at ON/OFF



11. EFFICIENCY

The efficiency of the S.M.P.S must be satisfied the maximum 82%.

12. SAFETY STANDARD

To meet ETL-UL1950, CETL-C22.2 NO.950, GS-DIN EN60950

AS/NZS 4665.1 : 2005, EuP 2005/32/EC

RD 1				
Ver: 0	Date: 2011/2/22	AMPLUS	AM10267L.doc	Page 4

13. RFI EMISSION

EN55022: 2006+A1 EN61000-3-2: 2000

EN61000-3-3: 1995+A1 EN55024: 1998+A1+A2

FCC PART 15

14. OUTPUT RATED & ELECTRICAL SPECIFICATIONS

RATED OUTPUT (V)	3	5	6	7.5	9	12
Rated current(A)	1.8	2.0	1.8	1.5	1.4	1.1
Max. output voltage(V)	3.6	5.5	6.5	8.0	9.5	12.5
Min. output voltage(V)	2.8	4.5	5.5	7.0	8.5	11.5
Ripple & Noise(mV)	<150	<150	<150	<150	<150	<150
Over load current(A)	>2.5	>2.2	>2.0	>1.8	>1.6	>1.4
Over heat protection	YES	YES	YES	YES	YES	YES
Rated power(W)	5.4	10	10.8	11.25	12.6	13.2
Switch frequency(KHZ)	132	132	132	132	132	132
Insulation class	II	II	II	II	II	II
Consumes(W)	<0.3W	<0.3W	<0.3W	<0.3W	<0.3W	<0.3W
Efficiency (%)	>68.75	>73.37	>73.95	>77.45	>78.17	>78.46
Efficiency Level	V	V	v	V	V	V

Note: ADJ . output voltage procedure

- 1. **Power off**
- 2. Select suitable output voltage form 3V to 12V by changeable slot.
- 3. Connect to Load
- 4. Power ON

15. RELIABILITY TESTING

A. DC OUTPUT CORD PUSH/PULL TEST OF I/O CONECTOR SIDE

 $Test\ condition:\ 8kgf\ X10sec\ at\ Y\ axis;\ 5kgfX10sec\ at\ other\ 4\ direction\ verticality$

RESULT: No cutting inner wire is acceptable

RD	1								
Ver: 0		Date: 2	2011/2/22	AMPLUS	AM10267L	doc	Pa	ge	5



B. DC OUTPUT CORD PUSH/PULL TEST OF ADAPTOR SIDE

Test condition: 8kgf X10sec at 5 direction verticality

RESULT: No cutting inner wire is acceptable

C. CORD BENDING TEST OF I/O CONECTOR SIDE


Test condition: 60'+60'=1 cycle, 30 cycle/1min, weight = 200g,

from step 1 to step 2 continuously

Step 1. 2000 cycle for difficult bending direction

Step 2. 3000 cycle for easy bending direction

RESULT: No cutting inner wire is acceptable



D. CORD BENDING TEST OF ADAPTOR SIDE

Test condition: 60'+60'=1 cycle, 30 cycle/1min, weight = 500g, from step 1 to step 2 continuously

Step 1. 500 cycle for difficult bending direction

Step 2. 500 cycle for easy bending direction

RESULT: No cutting inner wire is acceptable

E. INDIVIDUAL DROP TEST

Test condition: 6 face, each face 1 time 70 cm, on the 5mm wooden board. RESULT: Without opening of case and crack, etc. electric characteristic shall be satisfied.light crack after test is acceptable.

RD	1							
Ver: 0	: 0 Date: 2011/2/22		AMPLUS	AM10267L	doc	Page	6	

F. LOW TEMPERATURE STORAGE TEST

Keep on -30 (Packing) for 168 hours, and check the action after 3 hours in 25.

RESULT: All normal function and meet specification.

G. HIGH TEMPERATURE STORAGE TEST

Keep on +70 (Packing) for 168 hours, and check the action after 3 hours in 25.

RESULT: All normal function and meet specification.

H. HIGH HUMIDITY STORAGE TEST

Keep on +45 95%RH (Packing) for 168 hours, and check the action after 3hour in 25.

RESULT: All normal function and meet specification.

I. TEMPERATURE CYCLE TEST

Keep on -45 (Packing) for 1 hour, then keep on +85 (Packing) for 1 hour

Repeat this cycle until 10 cycle, check the action after an hour in 25 .

RESULT: All normal function and meet specification.


J. CURRENT- CARRYING OF HIGH VOLTAGE TEST

Select power consumption at a standard load condition. The test samples shall be active with input voltage is 280V/50Hz,50 ,48 hours, confirm its operation after left in the standard condition for 1 hour.

RESULT: any case deformation, smoking, or burn by heat should not be found.

RD	1										
Ver: 0	Ver: 0 Date: 2011/2/22		AMPLUS			AM10267L	doc	Pa	ge	7	

16. OUTLOOK DRAWING



RD :	1			
Ver: 0	Date: 2011/2/22	AMPLUS	AM10267L.doc	Page 8