DATASHEET - AT4/11-S/I/F2



Position switch, 1N/O+1N/C, narrow, IP65_x, spring-rod actuator

AT4/11-S/I/F2 Part no. Catalog No. 071689 Eaton Catalog No. AT4/11-S/I/F2





Delivery program		
Basic function		Position switches
Part group reference		AT4
Product range		Spring-rod actuator
Degree of Protection		IP65
Features		Complete unit
Ambient temperature	°C	-25 - +70
Snap-action contact		Yes
Description		Not to be used as a safety position switch
Approval		totally insulated
Contacts		
N/O = Normally open		1 N/O
N/C = Normally closed		1 NC
Contact sequence		$- + \begin{bmatrix} 13 \\ - \\ 14 \end{bmatrix} \begin{bmatrix} 21 \\ 22 \end{bmatrix}$
Contact travel = Contact closed = Contact open		$\begin{array}{c} 13.14 \\ 21.22 \\ 13.14 \\ 21.22 \\ 0^{\circ} 8^{\circ} 14^{\circ} 30^{\circ} \end{array} \rightarrow$
Colour		
Enclosure covers		Grey
Enclosure covers		
Housing		Insulated material
Connection type		Screw terminal

Rod length	mm	130		
Notes The operating head can be rotated at 90° intervals to adapt to the specified approach direction. For degree of protection IP65, use V-M20 (206910) cable glands with connecting thread of max. 9 mm length.				

Technical data			
General			
Standards			IEC/EN 60947
Climatic proofing			Damp heat, constant, to IEC 60068-2-78; damp heat, cyclical, to IEC 60068-2-30
Ambient temperature		°C	-25 - +70
Mounting position			As required
Degree of Protection			IP65
Terminal capacities		mm ²	
Solid		mm ²	1 x (0.75 - 2.5) 2 x (0.75 - 1.5)
Flexible with ferrule		mm ²	1 x (0.5 - 1.5) 2 x (0.5 - 1.5)
Contacts/switching capacity			
Rated impulse withstand voltage	U _{imp}	V AC	6000
Rated insulation voltage	Ui	V	500
Overvoltage category/pollution degree			111/3
Rated operational current	۱ _e	А	
AC-15			
24 V	۱ _e	Α	10
220 V 230 V 240 V	l _e	А	6
380 V 400 V 415 V	l _e	A	4
DC-13			
24 V	le	A	10
110 V	I _e	A	1
220 V	I _e	A	0.5
Supply frequency	U U	Hz	max. 400
Short-circuit rating to IEC/EN 60947-5-1			
max. fuse		A gG/gL	6
Repetition accuracy		mm	0.02
Rated conditional short-circuit current		kA	1
Aechanical variables			
ifespan, mechanical	Operations	x 10 ⁶	8
Contact temperature of roller head		°C	≦ 100
Vechanical shock resistance (half-sinusoidal shock, 20 ms)			
Standard-action contact		g	5
Snap-action contact		g	2
Operating frequency	Operations/h	3	≤ 6000
Actuation	operationa/II		
Vechanical			
Actuating force at beginning/end of stroke		N	8.0/20.0
Actuating torque of rotary drives		Nm	0.3

Design verification as per IEC/EN 61439

Technical data for design verification				
Rated operational current for specified heat dissipation	In	А	6	
Heat dissipation per pole, current-dependent	P _{vid}	W	0.1	
Equipment heat dissipation, current-dependent	P _{vid}	W	0	
Static heat dissipation, non-current-dependent	P _{vs}	W	0	
Heat dissipation capacity	P _{diss}	W	0	
Operating ambient temperature min.		°C	-25	
Operating ambient temperature max.		°C	70	
IEC/EN 61439 design verification				

10.2 Strength of materials and parts	
10.2.2 Corrosion resistance	Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures	Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat	Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects	Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation	Meets the product standard's requirements.
10.2.5 Lifting	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions	Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances	Meets the product standard's requirements.
10.5 Protection against electric shock	Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components	Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections	Is the panel builder's responsibility.
10.8 Connections for external conductors	Is the panel builder's responsibility.
10.9 Insulation properties	
10.9.2 Power-frequency electric strength	Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage	Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material	Is the panel builder's responsibility.
10.10 Temperature rise	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 7.0

Sensors (EG000026) / End switch (EC000030)	Sensors (EG000026) / End switch (EC000030)		
Electric engineering, automation, process control engineering / Binary sensor tech (ecl@ss10.0.1-27-27-06-01 [AGZ382015])	inology, safety-rela	ated sei	nsor technology / Position switch / Position switch (Type 1)
Width sensor	mn	m	40
Diameter sensor	mn	m	0
Height of sensor	mn	m	83
Length of sensor	mn	m	0
Rated operation current le at AC-15, 24 V	А		10
Rated operation current le at AC-15, 125 V	А		0
Rated operation current le at AC-15, 230 V	А		6
Rated operation current le at DC-13, 24 V	А		10
Rated operation current le at DC-13, 125 V	А		1
Rated operation current le at DC-13, 230 V	А		0.4
Switching function			Quick-break switch
Switching function latching			No
Output electronic			No
Forced opening			Yes
Number of safety auxiliary contacts			1
Number of contacts as normally closed contact			1
Number of contacts as normally open contact			1
Number of contacts as change-over contact			0
Type of interface			None
Type of interface for safety communication			None
Construction type housing			Cuboid
Material housing			Plastic
Coating housing			Other
Type of control element			Spring-rod
Alignment of the control element			Other

Type of electric connection			Other
With status indication			No
Suitable for safety functions			Yes
Explosion safety category for gas			None
Explosion safety category for dust			None
Ambient temperature during operating	٩(С	25 - 70
Degree of protection (IP)			IP65
Degree of protection (NEMA)			Other

Approvals

FF	
Product Standards	UL 508; CSA-C22.2 No. 14; IEC/EN 60947-4-1; CE marking
UL File No.	E29184
UL Category Control No.	NKCR
CSA File No.	12528
CSA Class No.	3211-03
North America Certification	UL listed, CSA certified
Specially designed for North America	No
Suitable for	Branch circuits
Max. Voltage Rating	600 V AC
Degree of Protection	UL: 1, 4X; CSA: 1, 3R, 4, 4X, 12, 13

Additional product information (links)

IL05208012Z (AWA1310-0544) Position switch

IL05208012Z (AWA1310-0544) Position switch ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL05208012Z2018_06.pdf