



98
5

Cable Knives

IEC 60900 ASTM F1505










98 52
⚡ 1000V  



98 54
⚡ 1000V  

- ergonomically improved handle shape with comfortable slip guard
- strong grip thanks to slip-proof soft components
- thumb recess and "finger hook" at the end of the handle ensure a good transmission of force when the blade is pulled
- solid, fixed straight blade
- transparent protective cap
- blade: Special tool steel; oil-hardened

98 54
back of the blade is plastic coated to avoid short circuits



Product Number	↔		⚡ 1000V  	Handle	Blade length		 Ounces
	inch	mm			inch	mm	
98 52	7 1/4	180	⚡ 1000V  	insulating multi-component handle, VDE-tested	1 31/32	50.0	2.4
98 54	7 1/4	180	⚡ 1000V  	insulating multi-component handle, VDE-tested	1 31/32	50.0	2.4

98
5



Dismantling Knives

IEC 60900 ASTM F1505



98 53 03
⚡ 1000V  



98 53 13
⚡ 1000V  












98 55
⚡ 1000V  

- ergonomically improved handle shape with comfortable slip guard
- strong grip thanks to slip-proof soft components
- thumb recess and "finger hook" at the end of the handle ensure a good transmission of force when the blade is pulled
- transparent protective cap

98 53 03
solid, fixed hook blade; suitable for round cables; blade: special tool steel; oil-hardened

98 53 13
narrow, fixed hook blade, sickle-shaped; suitable for sector cables; blade: special tool steel; oil-hardened

98 55
solid, fixed hook blade, sickle shaped; with guide shoe at the blade point; no damage of the conductor insulation; blade: surgical steel; stainless, air-hardened

Product Number	↔		⚡ 1000V  	Handle	Blade length		Radius		 Ounces
	inch	mm			inch	mm	inch	mm	
98 53 03	6	155	⚡ 1000V  	insulating multi-component handle, VDE-tested	1 7/64	28.0	9/32	7.0	2.3
98 53 13	7 1/4	180	⚡ 1000V  	insulating multi-component handle, VDE-tested	1 31/32	50.0	1 37/64	40.0	2.3
98 55	6	155	⚡ 1000V  	insulating multi-component handle, VDE-tested	1 1/2	38.0	59/64	23.5	2.4