San Ace controller

Features •

Preventive maintenance of equipment (IoT functionality)

- Easy to connect to user's terminal devices. (Wireless LAN / wired LAN)
- Enables users to monitor the status of fans and sensors from remote terminal devices.
- Enables users to control the fan speed remotely via terminal devices.
- · Detects outlier sensor measurements and sends alerts.
- Saves the fan's cumulative operating time and other fan measurement data to the cloud for later use.
- Prevents heat problems with user equipment, contributing to reducing maintenance time and costs.

Low noise and high energy efficiency (Automatic control)

- Stores temperature, humidity, and air pressure measurements for automatic fan speed control based on the setting conditions.
- Makes fan cooling and ventilation more efficient, reducing noise and improving efficiency.

Optimized fan settings (Manual control)

- Can connect and control a maximum of four fans, enabling different speed settings for individual fans.
- Optimizes the airflow and static pressure of individual fans in multi-fan systems.




Specifications


Model no.		9CT1-001	
Rated voltage [VDC]		12/24/48	
Power consumption [W]		3.1(1)	
Operating voltage range [VDC]		7 to 60	
Operating temperature range [°C]		-20 to +70	
Control functions		Manual / automatic	
Control signal		PWM signal	
		High-level voltage (V _{он}): 3.3/5 V	
		Frequency: 25 kHz	
Monitoring criteria		Fan speed, fan current, fan operation hours, sensor detection value, external input	
No. of connectable fans		Max. 4	
Max. fan connection terminal current		5 A (per terminal)	
No. of connectable sensors		Max. 4	
Compatible sensors ⁽²⁾		Temperature / humidity, air pressure, acceleration	
External I/O functions	Input	Photocoupler-isolated input, ON: 15 to 28.8 VDC, OFF: 0 to 5 VDC	
	Output	Photocoupler-isolated open-collector output, load voltage: 28.8 VDC or less, output current: 0.1 A or less	
Communication	Wireless	IEEE 802.11b/g/n, frequency: 2.4 GHz (3)	
	Wired	Ethernet 10BASE-T, 100BASE-TX	
Size [mm]		50 (W) × 135 (D) × 180 (H)	
Mass [g]		450	
Material		Casing: Plastic	
(4) 5	1 . 1 . 100°C	Combinatory water (O) Harry defined a grant (artists) (O) Australia de grant (C) 4 a 44	

⁽¹⁾ For use of this product alone, at 20°C ambient temperature (2) Use our dedicated sensors (options). (3) Available channels: Ch. 1 to 11

Front View



System Configuration




Graphical User Interface (GUI) Screens


Settings, control, monitoring, and data download can be done through web browsers.

Sample screens


Control settings



Measurement data




Graphs




Alarms



Dimensions (unit: mm)






Sensors



Sensor type	Temperature / Humidity sensor	Air pressure sensor	Accelerometer	
Model no.	9CT1-T	9CT1-P	9CT1-A	
Measurement range	Temperature: -20 to +70°C Humidity: 20 to 85%RH ⁽¹⁾	Air pressure: 800 to 1100 hPa	Acceleration: 0 to 60 m/s ^{2 (2)}	
Operating temperature range [°C]	-20 to +70			
Operating humidity range [%RH]	20 to 85 ⁽¹⁾			
Size [mm]	53 (W) × 46 (D) × 22 (H)			
Mass [g]	35			
Material	Casing: Plastic			

⁽¹⁾ Non-condensing $\ (2)$ Total acceleration from three axes

Dimensions (unit: mm)



Precautions on use

Before using the product, please read the included instructions manual carefully.

Notice

The products shown in this catalog are subject to Japanese Export Control Law. Diversion contrary to the law of exporting country is prohibited.