soft starter-ATS22-control 220V-power 230V(15kW)/400...440V(30kW)





Main Range of product Altistart 22 Product or component Soft starter type Product destination Asynchronous motors Product specific Pumps and fans application Component name ATS22 Network number of 3 phases phases [Us] rated supply 230...440 V - 15...10 % voltage Motor power kW 15 KW 230 V 30 KW 400 V 30 kW 440 V Factory setting current Power dissipation in W 59 W for standard applications Utilisation category AC-53A Type of start Start with torque control (current limited to 3.5 ln) IcL starter rating 62 A for connection in the motor supply line for standard applications

IP20

Complementary

With heat sink
Internal bypass
195484 V
5060 Hz - 1010 %
4566 Hz
To the motor delta terminals In the motor supply line
230 V - 1510 % 50/60 Hz
20 W
2
Relay outputs R1 230 V running, alarm, trip, stopped, not stopped, starting, ready C/O Relay outputs R2 230 V running, alarm, trip, stopped, not stopped, starting, ready C/O
100 mA at 12 V DC (relay outputs)
5 A 250 V AC resistive 1 relay outputs 5 A 30 V DC resistive 1 relay outputs 2 A 250 V AC inductive 0.4 20 ms relay outputs 2 A 30 V DC inductive 7 ms relay outputs
3
(LI1, LI2, LI3) logic, 5 mA 4.3 kOhm
24 V <= 30 V
Positive logic LI1, LI2, LI3 at State 0: < 5 V and <= 2 mA at State 1: > 11 V, >= 5 mA
0.41 Icl adjustable
750 Ohm
Modbus
1 RJ45

IP degree of protection

Communication data link	Serial	
Physical interface	RS485 multidrop	
Transmission rate	4800, 9600 or 19200 bps	
Installed device	31	
Protection type	Phase failure: line Thermal protection: motor Thermal protection: starter	
Marking	CE	
Type of cooling	Forced convection	
Operating position	Vertical +/- 10 degree	
Height	295 mm	
Width	145 mm	
Depth	207 mm	
Net weight	12 kg	
Motor power range AC-3	1525 KW at 200240 V 3 phases 3050 kW at 380440 V 3 phases	
Motor starter type	Soft starter	

Environment

Electromagnetic compatibility	Conducted and radiated emissions level A conforming to IEC 60947-4-2 Damped oscillating waves level 3 conforming to IEC 61000-4-12 Electrostatic discharge level 3 conforming to IEC 61000-4-2 Immunity to electrical transients level 4 conforming to IEC 61000-4-4 Immunity to radiated radio-electrical interference level 3 conforming to IEC 61000-4-3 Voltage/current impulse level 3 conforming to IEC 61000-4-5	
Standards	EN/IEC 60947-4-2	
Product certifications	C-Tick CCC UL CSA GOST	
Vibration resistance	1 gn (f= 13200 Hz) conforming to EN/IEC 60068-2-6 1.5 mm (f= 213 Hz) conforming to EN/IEC 60068-2-6	
Shock resistance	15 gn for 11 ms conforming to EN/IEC 60068-2-27	
Noise level	45 dB	
Pollution degree	Level 2 conforming to IEC 60664-1	
Relative humidity	095 % without condensation or dripping water conforming to EN/IEC 60068-2-3	
Ambient air temperature for operation	-1040 °C (without derating) 4060 °C (with current derating 2.2 % per °C)	
Ambient air temperature for storage	-2570 °C	
Operating altitude	<= 1000 m without derating > 1000< 2000 m with current derating of 2.2 % per additional 100 m	

Packing Units

· coming critic	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	8.262 kg
Package 1 Height	31.0 cm
Package 1 width	23.5 cm
Package 1 Length	36.0 cm
Unit Type of Package 2	P06
Number of Units in Package 2	6
Package 2 Weight	64.0 kg
Package 2 Height	73.5 cm
Package 2 width	80.0 cm
Package 2 Length	60.0 cm

Offer Sustainability


Sustainable offer status	Green Premium product
REACh Regulation	☑ REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EEU RoHS Declaration
Mercury free	Yes
RoHS exemption information	€Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty 18 months	
--------------------	--

Frame Size B

Dimensions



Precautions

Standards

The Altistart 22 soft starter is compliant with pollution Degree 2 as defined in NEMA ICS1-1 or IEC 60664-1.

For environment pollution degree 3, install the Altistart 22 soft starter inside a cabinet type 12 or IP54.

DANGER


HAZARD OF ELECTRIC SHOCK, EXPLOSION, OR ARC FLASH

ATS22 soft starters are open devices and must be mounted in a suitable enclosure.

Failure to follow these instructions will result in death or serious injury.

Air Circulation

Leave sufficient free space to help the air required for cooling purposes to circulate from the bottom to the top of the unit.




Overheating

To avoid the soft starter to overheat, respect the following recommendations:

- Mount the Altistart 22 Soft Starter within ± 10° of vertical.
- Do not locate the Altistart 22 Soft Starter near heat radiating elements.
- Electrical current through the Altistart 22 Soft Starter will result in heat losses that must be dissipated into the ambient air immediately surrounding the soft starter. To help prevent a thermal fault, provide sufficient enclosure cooling and/or ventilation to limit the ambient temperature around the soft starter.
- If several soft starters are installed in a control panel, arrange them in a row. Do not stack soft starters. Heat generated from the bottom soft starter can adversely affect the ambient temperature around the top soft starter.

Mounting

Connection Between the Fan and the Altistart 22 Soft Starter



- 1 Altistart 22 Soft Starter
- 2 Fan

Wall mounted or Floor-standing Enclosure with IP 23 Degree of protection


Introduction

To help proper air circulation in the soft starter, grilles and forced ventilation can be installed.

Ventilation Grilles





Forced Ventilation Unit



Power Terminal

Cage Style





1 Ground connection

Power connections, minimum and maximum wiring capabilities, tightening torque


			IEC cable	UL cable
Power supply and output to motor	Size/gauge	min	4 mm (a)	10 AWG (a)
max	50 mm	1/0 AWG		
Tightening torque	min	8 N.m	70 lb.in	
max	8 N.m	70 lb.in		•
Strip length		15 mm	0.6 in.	

Power connections, minimum required wiring section


IEC cable	UL cable
mm² (Cu 70°C/158°F) (1)	AWG (Cu 75°C/167°F) (1)
16	4

230 Vac control, logic Inputs (LI) 24 Vdc, 3-wire control

With Line Contactor, Freewheel or Controlled Stop



230 Vac control, logic Inputs (LI) 24 Vdc, 2-wire control, freewheel stop





Connection in the motor delta winding in series with each winding

Wiring

ATS22 soft starters connected to motors with the delta connections can be inserted in series in the motor windings.

The following wiring requieres particular attention. It is documented in the Altistart 22 Soft start - soft stop unit user manual. Please contact Schneider Electric commercial organisation for further informations.






Example

A 400 V - 110 kW motor with a line current of 195 A (nominal current for the delta connection). The current in each winding is equal to 195/1.5 or 130 A. The rating is determined by selecting the soft starter with a permanent nominal current (ICL) just above this current.

Motor Thermal Protection - Cold Curves

Curves



A Class 10

B Class 20

C Class 30

Trip time for a Standard Application (Class 10)

3.5 ln

32 s

Trip time for a Severe Application (Class 20)

3.5 ln


63 s

Trip time for a Severe Application (Class 30)

3.5 ln

95 s





- Class 10 Class 20 A B
- Class 30

Trip time for a Standard Application (Class 10)

3.5 ln 16 s

Trip time for a Severe Application (Class 20)

3.5 ln 32 s

Trip time for a Severe Application (Class 30)

3.5 ln 48 s