soft starter-ATS22-control110V-power 208V(25hp)/230V(30hp)/460V(60hp)/575V(75hp)





Main		
Range of product	Altistart 22	
Product or component type	Soft starter	
Product destination	Asynchronous motors	
Product specific application	Pumps and fans	
Component name	ATS22	
Network number of phases	3 phases	
[Us] rated supply voltage	208600 V - 1510 %	
Motor power hp	25 Hp 208 V 30 Hp 230 V 60 Hp 460 V 75 hp 575 V	
Factory setting current	77 A	
Power dissipation in W	66 W for standard applications	
Utilisation category	AC-53A	
Type of start	Start with torque control (current limited to 3.5 ln)	
IcL starter rating	88 A for connection in the motor supply line for standard applications	
IP degree of protection	IP20	

Complementary

Assembly style	With heat sink	
Function available	Internal bypass	
Supply voltage limits	177660 V	
Supply frequency	5060 Hz - 1010 %	
Network frequency	4566 Hz	
Device connection	In the motor supply line	
[Uc] control circuit voltage	110 V - 1510 % 50/60 Hz	
Control circuit consumption	20 W	
Discrete output number	2	
Discrete output type	Relay outputs R1 230 V running, alarm, trip, stopped, not stopped, starting, ready C/O	
	Relay outputs R2 230 V running, alarm, trip, stopped, not stopped, starting, ready C/O	
Minimum switching current	100 mA at 12 V DC (relay outputs)	
Maximum switching current	5 A 250 V AC resistive 1 relay outputs 5 A 30 V DC resistive 1 relay outputs 2 A 250 V AC inductive 0.4 20 ms relay outputs 2 A 30 V DC inductive 7 ms relay outputs	
Discrete input number	3	
Discrete input type	(LI1, LI2, LI3) logic, 5 mA 20 kOhm	
Discrete input voltage	110 V <= 121 V	
Discrete input logic	Positive logic LI1, LI2, LI3 at State 0: < 20 V and <= 15 mA at State 1: > 79 V, <= 2 mA	
Output current	0.41 lcl adjustable	
Communication port protocol	Modbus	
Connector type	1 RJ45	
Communication data link	Serial	

Physical interface	RS485 multidrop	
Transmission rate	4800, 9600 or 19200 bps	
Installed device	31	
Protection type	Phase failure: line Thermal protection: motor Thermal protection: starter	
Marking	CE	
Type of cooling	Forced convection	
Operating position	Vertical +/- 10 degree	
Height	295 mm	
Width	145 mm	
Depth	207 mm	
Net weight	12 kg	
	· · · · · · · · · · · · · · · · · · ·	

Environment

Electromagnetic compatibility	Conducted and radiated emissions level A conforming to IEC 60947-4-2	
	Damped oscillating waves level 3 conforming to IEC 61000-4-12	
	Electrostatic discharge level 3 conforming to IEC 61000-4-2	
	Immunity to electrical transients level 4 conforming to IEC 61000-4-4	
	Immunity to radiated radio-electrical interference level 3 conforming to IEC 61000-4-3	
	Voltage/current impulse level 3 conforming to IEC 61000-4-5	
Standards	EN/IEC 60947-4-2	
Product certifications	UL	
	CSA	
	GOST	
	C-Tick	
	CCC	
Vibration resistance	1 gn (f= 13200 Hz) conforming to EN/IEC 60068-2-6	
	1.5 mm (f= 213 Hz) conforming to EN/IEC 60068-2-6	
Shock resistance	15 gn for 11 ms conforming to EN/IEC 60068-2-27	
Noise level	45 dB	
Pollution degree	Level 2 conforming to IEC 60664-1	
Relative humidity	095 % without condensation or dripping water conforming to EN/IEC 60068-2-	
Ambient air temperature for operation	-1040 °C (without derating)	
	4060 °C (with current derating 2.2 % per °C)	
Ambient air temperature for storage	-2570 °C	
Operating altitude	<= 1000 m without derating	
	> 1000< 2000 m with current derating of 2.2 % per additional 100 m	

Packing Units

r acking Office	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	8.305 kg
Package 1 Height	31.0 cm
Package 1 width	36.0 cm
Package 1 Length	23.0 cm
Unit Type of Package 2	P06
Number of Units in Package 2	6
Package 2 Weight	64.72 kg
Package 2 Height	73.5 cm
Package 2 width	80.0 cm
Package 2 Length	60.0 cm

Offer Sustainability


Sustainable offer status	Green Premium product	
REACh Regulation	☑ REACh Declaration	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
Mercury free	Yes	
RoHS exemption information	€Yes	
China RoHS Regulation	☑ China RoHS Declaration	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End Of Life Information	
WEEE	The product must be disposed on European Union markets following s waste collection and never end up in rubbish bins	

Contractual warranty

Warranty 18 months	
--------------------	--

Frame Size B

Dimensions



Precautions

Standards

The Altistart 22 soft starter is compliant with pollution Degree 2 as defined in NEMA ICS1-1 or IEC 60664-1.

For environment pollution degree 3, install the Altistart 22 soft starter inside a cabinet type 12 or IP54.

DANGER


HAZARD OF ELECTRIC SHOCK, EXPLOSION, OR ARC FLASH

ATS22 soft starters are open devices and must be mounted in a suitable enclosure.

Failure to follow these instructions will result in death or serious injury.

Air Circulation

Leave sufficient free space to help the air required for cooling purposes to circulate from the bottom to the top of the unit.




Overheating

To avoid the soft starter to overheat, respect the following recommendations:

- Mount the Altistart 22 Soft Starter within ± 10° of vertical.
- Do not locate the Altistart 22 Soft Starter near heat radiating elements.
- Electrical current through the Altistart 22 Soft Starter will result in heat losses that must be dissipated into the ambient air immediately
 surrounding the soft starter. To help prevent a thermal fault, provide sufficient enclosure cooling and/or ventilation to limit the ambient
 temperature around the soft starter.
- If several soft starters are installed in a control panel, arrange them in a row. Do not stack soft starters. Heat generated from the bottom soft starter can adversely affect the ambient temperature around the top soft starter.

Mounting

Connection Between the Fan and the Altistart 22 Soft Starter



- 1 Altistart 22 Soft Starter
- 2 Fan

Wall mounted or Floor-standing Enclosure with IP 23 Degree of protection


Introduction

To help proper air circulation in the soft starter, grilles and forced ventilation can be installed.

Ventilation Grilles





Forced Ventilation Unit



Power Terminal

Cage Style





1 Ground connection


Power connections, minimum and maximum wiring capabilities, tightening torque

			IEC cable	UL cable
Power supply and output to motor	Size/gauge	min	4 mm (a)	10 AWG (a)
max	50 mm	1/0 AWG		
Tightening torque	min	8 N.m	70 lb.in	
max	8 N.m	70 lb.in		•
Strip length		15 mm	0.6 in.	


Power connections, minimum required wiring section

IEC cable	UL cable
mm² (Cu 70°C/158°F) (1)	AWG (Cu 75°C/167°F) (1)
35	2

110 Vac control, Logic Inputs (LI) 110 Vac, 3-wire control




110 Vac control, Logic Inputs (LI) 110 Vac, 2-wire control, freewheelstop



Motor Thermal Protection - Cold Curves

Curves



A Class 10 B Class 20

C Class 30

Trip time for a Standard Application (Class 10)

3.5 ln 32 s

Trip time for a Severe Application (Class 20)


3.5 ln 63 s

Trip time for a Severe Application (Class 30)

3.5 ln

95 s





Class 10 Class 20 A B C

Class 30

Trip time for a Standard Application (Class 10)

3.5 ln 16 s

Trip time for a Severe Application (Class 20)

3.5 ln 32 s

Trip time for a Severe Application (Class 30)

3.5 ln 48 s