


**A-series
A3C 2.5 OR**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com

**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

Type	A3C 2.5 OR
Order No.	1521830000
Version	Feed-through terminal, PUSH IN, 2.5 mm ² , 800 V, 24 A, Orange
GTIN (EAN)	4050118328226
Qty.	100 pc(s).

A-series A3C 2.5 OR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Width	5.1 mm	Width (inches)	0.201 inch
Height	66.5 mm	Height (inches)	2.618 inch
Depth	36.5 mm	Depth (inches)	1.437 inch
Depth including DIN rail	37 mm	Net weight	7.98 g

Temperatures

Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C
----------------------------------	--------	----------------------------------	--------

Material data

Material	Wemid	Colour	Orange
Colour of operational elements	Orange	UL 94 flammability rating	V-0

System specifications

End cover plate required	Yes	Number of potentials	1
Number of levels	1	No. of clamping points per level	3
Number of potentials per tier	1	PE connection	No
Mounting rail	TS 35	N-function	No
PE function	No	PEN function	No

Additional technical data

Installation advice	Mounting rail	Open sides	right
Snap-on	No	Type of fixing	Snap-on
Type of mounting	TS 35	With snap-in pegs	No

CSA rating data

Certificate No. (CSA)	200039-70089609	Current size B (CSA)	20 A
Current size C (CSA)	20 A	Current size D (CSA)	5 A
Voltage size B (CSA)	600 V	Voltage size C (CSA)	600 V
Voltage size D (CSA)	600 V	Wire cross section max. (CSA)	12 AWG
Wire cross section min. (CSA)	28 AWG		

A-series A3C 2.5 OR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Technische Daten

Conductors for clamping (rated connection)

Blade size	0.6 x 3.5 mm	Clamping range, rated connection, max.	2.5 mm ²
Clamping range, rated connection, min.	0.14 mm ²	Connection direction	top
Cross-section for connected conductor, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, min.	0.5 mm ²	Gauge to IEC 60947-1	A3
Number of connections	3	Stripping length	10 mm
Twin wire-end ferrules, max.	1.5 mm ²	Twin wire-end ferrules, min.	0.5 mm ²
Type of connection	PUSH IN	Wire connection cross section AWG, max.	AWG 12
Wire connection cross section AWG, min.	AWG 28	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max.	2.5 mm ²
Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min.	0.5 mm ²	Wire connection cross section, finely stranded, max.	2.5 mm ²
Wire connection cross section, solid core max. rated connection	2.5 mm ²	Wire connection cross section, solid core, min. rated connection	0.5 mm ²
Wire connection cross section, stranded, rated connection, max.	2.5 mm ²	Wire connection cross section, stranded, rated connection, min.	0.5 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, max.	2.5 mm ²	Wire connection cross-section, finely stranded, min.	0.5 mm ²

Rating data

Rated cross-section	2.5 mm ²	Rated voltage	800 V
Rated current	24 A	Current at maximum wires	24 A
Standards	IEC 60947-7-1	Volume resistance according to IEC 60947-7-x	1.33 mΩ
Rated impulse withstand voltage	8 kV	Pollution severity	3
Surge voltage category	III		

UL rating data

Certificate No. (cURus)	E60693	Conductor size Factory wiring max. (cURus)	12 AWG
Conductor size Factory wiring min. (cURus)	28 AWG	Conductor size Field wiring max. (cURus)	12 AWG
Conductor size Field wiring min. (cURus)	28 AWG	Current size B (cURus)	20 A
Current size C (cURus)	20 A	Current size D (cURus)	5 A
Voltage size B (cURus)	600 V	Voltage size C (cURus)	600 V
Voltage size D (cURus)	600 V		

Classifications

ETIM 5.0	EC000897	ETIM 6.0	EC000897
eClass 6.2	27-14-11-20	eClass 7.1	27-14-11-20
eClass 8.1	27-14-11-20	eClass 9.0	27-14-11-20
eClass 9.1	27-14-11-20		

Datenblatt**A-series
A3C 2.5 OR****Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com**Technische Daten****Approvals**

Approvals



ROHS

Conform

DownloadsApproval/Certificate/Document of
Conformity[DE_PT0101_20160614_042_ISSUE01.pdf](#)

Engineering Data

[EPLAN, WSCAD, Zuken E3.S](#)**Safety note**

Safety notice


[Safety Information](#)

Datenblatt

**A-series
A3C 2.5 OR**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com

Zeichnungen



A-series A3C 2.5 OR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Accessories

End plates



Spring connection with PUSH IN Technology

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
AEP 3C 2.5	1521510000	A-series, End plate	4050118328417 50 pc(s).	
AEP 3C 2.5	2052300000	A-series, End plate	4050118411966 50 pc(s).	
OR				
AEP 3C 2.5 BL	1521520000	A-series, End plate	4050118328356 50 pc(s).	

ZQV 2.5N



Spring connection with PUSH IN Technology

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
ZQV 2.5N/7	2108810000	Z-series, Cross-connector,	4050118448498 20 pc(s).	
RD		No. of poles: 7		
ZQV 2.5N/4	2108700000	Z-series, Cross-connector,	4050118448528 60 pc(s).	
RD		No. of poles: 4		
ZQV 2.5N/10	1527690000	Z-series, Cross-connector,	4050118447989 20 pc(s).	
		No. of poles: 10		
ZQV 2.5N/10	1527880000	Z-series, Cross-connector,	4050118448573 20 pc(s).	
BL		No. of poles: 10		
ZQV 2.5N/2	2108470000	Z-series, Cross-connector,	4050118448542 60 pc(s).	
RD		No. of poles: 2		
ZQV 2.5N/4	1527590000	Z-series, Cross-connector,	4050118448443 60 pc(s).	
		No. of poles: 4		
ZQV 2.5N/6	2108720000	Z-series, Cross-connector,	4050118448504 20 pc(s).	
RD		No. of poles: 6		
ZQV 2.5N/9	2108900000	Z-series, Cross-connector,	4050118448474 20 pc(s).	
RD		No. of poles: 9		
ZQV 2.5N/4	1527780000	Z-series, Cross-connector,	4050118448634 60 pc(s).	
BL		No. of poles: 4		
ZQV 2.5N/5	1527790000	Z-series, Cross-connector,	4050118448627 20 pc(s).	
BL		No. of poles: 5		

A-series A3C 2.5 OR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Accessories

ZQV 2.5N/20 1527720000	Z-series, Cross-connector, No. of poles: 20	4050118447972 20 pc(s).
ZQV 2.5N/20 1527890000 BL	Z-series, Cross-connector, No. of poles: 20	4050118448566 20 pc(s).
ZQV 2.5N/7 1527640000	Z-series, Cross-connector, No. of poles: 7	4050118448412 20 pc(s).
ZQV 2.5N/8 1527840000 BL	Z-series, Cross-connector, No. of poles: 8	4050118448597 20 pc(s).
ZQV 2.5N/8 2108870000 RD	Z-series, Cross-connector, No. of poles: 8	4050118448481 20 pc(s).
ZQV 2.5N/50 2109000000 RD	Z-series, Cross-connector, No. of poles: 50	4050118486001 5 pc(s).
ZQV 2.5N/9 1527680000	Z-series, Cross-connector, No. of poles: 9	4050118447996 20 pc(s).
ZQV 2.5N/6 1527630000	Z-series, Cross-connector, No. of poles: 6	4050118448429 20 pc(s).
ZQV 2.5N/6 1527820000 BL	Z-series, Cross-connector, No. of poles: 6	4050118448610 20 pc(s).
ZQV 2.5N/8 1527670000	Z-series, Cross-connector, No. of poles: 8	4050118448405 20 pc(s).
ZQV 2.5N/5 2108710000 RD	Z-series, Cross-connector, No. of poles: 5	4050118448511 20 pc(s).
ZQV 2.5N/3 1527770000 BL	Z-series, Cross-connector, No. of poles: 3	4050118448641 60 pc(s).
ZQV 2.5N/20 2108920000 RD	Z-series, Cross-connector, No. of poles: 20	4050118485899 20 pc(s).
ZQV 2.5N/2 1527540000	Z-series, Cross-connector, No. of poles: 2	4050118448467 60 pc(s).
ZQV 2.5N/9 1527870000 BL	Z-series, Cross-connector, No. of poles: 9	4050118448580 20 pc(s).
ZQV 2.5N/3 1527570000	Z-series, Cross-connector, No. of poles: 3	4050118448450 60 pc(s).
ZQV 2.5N/50 1527920000 BL	Z-series, Cross-connector, No. of poles: 50	4050118448559 5 pc(s).
ZQV 2.5N/2 1527740000 BL	Z-series, Cross-connector, No. of poles: 2	4050118448658 60 pc(s).
ZQV 2.5N/5 1527620000	Z-series, Cross-connector, No. of poles: 5	4050118448436 20 pc(s).
ZQV 2.5N/10 2108910000 RD	Z-series, Cross-connector, No. of poles: 10	4050118486018 20 pc(s).
ZQV 2.5N/50 1527730000	Z-series, Cross-connector, No. of poles: 50	4050118411362 5 pc(s).
ZQV 2.5N/7 1527830000 BL	Z-series, Cross-connector, No. of poles: 7	4050118448603 20 pc(s).
ZQV 2.5N/3 2108690000 RD	Z-series, Cross-connector, No. of poles: 3	4050118448535 60 pc(s).

A-series A3C 2.5 OR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Accessories

Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
WS 8/5 PLUS MC SDR	1038790000	WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, To customer specification	4032248768066	120 pc(s).
WS 8/5 MC SDR	1640750000	WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, To customer specification	4008190456627	144 pc(s).

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
WS 10/5 MC NE WS	1635000000	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, White	4008190261948	720 pc(s).
WS 10/5 MC NE RT	1773531686	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, Red	4032248141746	720 pc(s).
WS 10/5 M PLUS MC NE WS	2003770000	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, White	4050118424447	600 pc(s).

**A-series
A3C 2.5 OR**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Accessories

WS 10/5 MC 1773531693 NE BL	WS, Terminal marker, 10 x 4032248141814 720 pc(s). 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, Blue
WS 10/5 1046380000 PLUS MC NE WS	WS, Terminal marker, 10 x 4032248782086 600 pc(s). 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, White
WS 10/5 MC 1773531687 NE GE	WS, Terminal marker, 10 x 4032248141753 720 pc(s). 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, Yellow
WS 10/5 M 1792000000 MC NE WS	WS, Terminal marker, 10 x 4032248223862 720 pc(s). 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, White

WS 8/5



WS/ DEK

MultiMark DEK/WS connector markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Compatible with W, Z, P and SAK series terminal blocks
- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Space for multi-line printing

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
WS 8/5 MM	2007150000	WS, Terminal marker, 8 x 5	4050118392029 800 pc(s).	
WS		mm, Weidmueller, White		

A-series A3C 2.5 OR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Accessories

Digital multimeters




Multimeters are capable of measuring a number of variables. Each instrument can measure voltage and resistance, as well as performing continuity and diode testing as standard. In addition, the individual multimeters also feature extra measuring options such as current, frequency, capacitance and temperature. Digital multimeters have the advantage of a clear display which can be read easily and directly. With these instruments, mistakes arising from faulty conversion of the measuring ranges or misreading the display are a thing of the past.

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
ZUB MULTIMETER	9205270000	Multimeter	4032248723522	1 pc(s).

Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
DEK 5/5 S MC SDR	1341590000	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, To customer specification	4050118146042	80 pc(s).
DEK 5/5 PLUS MC SDR	1854500000	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, To customer specification	4032248393602	200 pc(s).
DEK 5/5 MC SDR	1609810000	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, To customer specification	4008190456597	200 pc(s).

A-series A3C 2.5 OR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Accessories

DEK 5/5



WS/ DEK

MultiMark DEK/WS connector markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Compatible with W, Z, P and SAK series terminal blocks
- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Space for multi-line printing

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
DEK 5/5 MM WS	2007110000	Dekafix, Terminal marker, 5 x 5 mm, Weidmueller, White	4050118391862	800 pc(s).

End brackets



Spring connection with PUSH IN Technology

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
AEB 35 SC/1	1991920000	A-series, End bracket	4050118376722	50 pc(s).

A-series A3C 2.5 OR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Accessories

V0



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.


Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
DEK 5/5 MC NE V0 WS	1388530000	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5,00 Weidmueller, White	4050118188622	1,000 pc(s).

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
WS 8/5 MC NE OR	1773521690	WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, Orange	4032248143092	720 pc(s).
WS 8/5 MC NE BL	1773521693	WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, Blue	4032248141715	720 pc(s).
WS 8/5 PLUS MC NE WS	1951870000	WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, White	4032248631605	600 pc(s).
WS 8/5 MC NE RT	1773521686	WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, Red	4032248141531	720 pc(s).

A-series A3C 2.5 OR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Accessories

WS 8/5 MC 1773521687 NE GE	WS, Terminal marker, 8 x 5 4032248141548 720 pc(s). mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, Yellow
WS 8/5 MC 1640740000 NE WS	WS, Terminal marker, 8 x 5 4008190279103 720 pc(s). mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, White

Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
WS 10/5 MC M SDR	1792010000	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, To customer specification	4032248223879	144 pc(s).
WS 10/5 M PLUS MC SDR	2007770000	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, To customer specification	4050118393279	120 pc(s).
WS 10/5 PLUS MC SDR	1046320000	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, To customer specification	4032248782024	120 pc(s).
WS 10/5 MC SDR	1635010000	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, To customer specification	4008190456634	144 pc(s).

A-series A3C 2.5 OR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Accessories

Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
DEK 5/5 PLUS MC NE GE	1907520000	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5,00 Weidmueller, Yellow	4032248532100	1,000 pc(s).
DEK 5/5 PLUS MC NE WS	1854490000	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5,00 Weidmueller, White	4032248393596	1,000 pc(s).

Test adapter



Spring connection with PUSH IN Technology

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

Type	Order No.	GTIN (EAN)	Qty.
ATPG 2.5/3	2041190000	4050118409604	25 pc(s).
ATPG 2.5 MI-R	1991960000	4050118376685	50 pc(s).
ATPG 1.5-10 L	1991890000	4050118376647	50 pc(s).
ATPG 2.5/5	2041180000	4050118409505	25 pc(s).

A-series A3C 2.5 OR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Accessories

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
DEK 5/5 MC NE VI	1249860000	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Violet	4050118042764	1,000 pc(s).
DEK 5/5 MC NE GR	1609801691	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Grey	4008190397159	1,000 pc(s).
DEK 5/5 MC NE RT	1609801686	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Red	4008190397128	1,000 pc(s).
DEK 5/5 MC NE BR	1249870000	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Brown	4050118051865	1,000 pc(s).
DEK 5/5 MC NE BL	1609801693	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Blue	4008190397166	1,000 pc(s).
DEK 5/5 MC NE GN	1609801688	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Green	4008190397142	1,000 pc(s).
DEK 5/5 S MC NE WS	1341620000	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, White	4050118145793	400 pc(s).
DEK 5/5 MC NE SW	1457550000	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Black	4050118263817	1,000 pc(s).
DEK 5/5 MC NE GE	1609801687	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Yellow	4008190397135	1,000 pc(s).
DEK 5/5 MC NE WS	1609801044	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, White	4008190397111	1,000 pc(s).
DEK 5/5 MC NE OR	1238340000	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Orange	4050118062632	1,000 pc(s).

**A-series
A3C 2.5 OR**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Accessories

End brackets



Spring connection with tension clamp Technology
 Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
ZEW 35	9540000000	Z-series, End bracket	4008190956264	20 pc(s).
ZEW 35 GR	1238040000	Z-series, End bracket	405011802440	120 pc(s).
ZEW 35 V0	1264170000	Z-series, End bracket	4050118137170	20 pc(s).