

# **IP Phone AX-400G**



# **Enterprise HD IP Phone - Gigabit Color AX-400G**

The mid-level AX-400G is fit for mid-size companies and executive offices alike. This Gigabit IP phone offers a colorful 2.8" TFT LCD display with 320x240 pixels and excellent HD audio.

This versatile phone provides flexibility for eight SIP accounts.

The elegant design complements the AX-400G's intuitive interface.













#### **Phone Features**

Up to 8 SIP accounts Call hold, mute, DND One-touch speed dial, hotline Call forward, call waiting, call transfer Redial, call return, auto answer, direct IP call 5-way conferencing Group listening, SMS, emergency call Ring tone selection/provisioning Set date time automatically or manually Dial plan per account RTCP-XR (RFC3611), VQ-RTCPXR (RFC6035) Electronic hook switch capable

## **Voice Codecs Features**

HD voice, HD handset, HD speaker Codecs: iLBC, G.722, G.711(A/μ), Opus G.723, G.729AB, G.726-32 DTMF: In-band, RFC 2833, SIP INFO Full-duplex hands-free speakerphone with AEC VAD, AGC, CNG, AEC, PLC, AJB

# **Directory**

Local phonebook up to 1000 entries XML/LDAP remote phonebook Intelligent search method Phonebook search/import/export Call history: dialed/received/missed/forwarded Black list

#### **IP-PBX Features**

Busy Lamp Field (BLF), bridged Line Appearance(BLA) Anonymous call, anonymous call rejection Message Waiting Indicator (MWI), voice mail Intercom, paging Call park, call pickup Music on hold Hot-desking

#### **Display and Indicator**

2.8" 320x240-pixel color display with backlight 16 bit depth color LED for call and message waiting indication Dual-color (white or orange) illuminated feature keys Intuitive user interface with icons and soft keys Wallpaper, national language selection Caller ID with name, number and photo

#### Interface

Dual-port Gigabit Ethernet Power over Ethernet (IEEE 802.3af), class 3 1xRJ9 (4P4C) handset port 1xRJ9 (4P4C) headset port

# **Feature keys**

6 line keys with LED 6 line keys can be programmed up to 20 various features (4-page view) 8 feature keys: voice mail, headset, mute, speaker, transfer, redial, 4 context-sensitive "soft" keys 6 navigation keys, volume control keys Illuminated speaker key/headset key/mute key

## **Physical Features**

Stand with 2 adjustable angles Wall mountable External universal AC adapter (optional): AC 100~240V input and DC 5V/1.2A output Power consumption (PSU): 1.8~4.4W Power consumption (PoE): 2.3~5.3W Operating humidity: 10~95% Operating temperature: -10~50°C

# **Management**

Configuration: browser/LCD-Menu/auto-provision Auto provision via HTTP/HTTPS FTP/TFTP Auto-provision with PnP Reset to factory, restart, reboot Local tracing log export, system log Phone lock for personal privacy protection

# **Network and Security**

SIP v1 (RFC2543), v2 (RFC3261) SIP server/proxy redundancy NAT Traversal: STUN mode DHCP/static/PPPoE/IEEE802.1X/open VPN HTTP/HTTPS web server Time and date synchronization by SNTP DNS-NAPTR/DNS-SRV(RFC 3263) QoS: 802.1p/Q tagging (VLAN), Layer 3 ToS DSCP TLS(Transport Layer Security), SRTP, ZRTP HTTPS certificate manager AES encryption for configuration file Digest authentication using MD5/MD5-sess IPv6 supported

#### Package content

Axtel AX-400G phone Handset with handset cord Stand Quick Reference guide Ethernet cable (1,5m Cat 5E)





