



Main

Device application	Distribution
Range	Acti 9
Range of product	IC60
Product name	Acti 9 iC60
Product or component type	Miniature circuit-breaker
Device short name	IC60H
Poles description	2P
Number of protected poles	2
[In] rated current	1 A
Network type	AC DC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity code	H
Breaking capacity	70 kA Icu conforming to EN/IEC 60947-2 - 220...240 V AC 50/60 Hz 70 kA Icu conforming to EN/IEC 60947-2 - 12...60 V AC 50/60 Hz 70 kA Icu conforming to EN/IEC 60947-2 - 100...133 V AC 50/60 Hz 70 kA Icu conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz 10000 A Icn conforming to EN/IEC 60898-1 - 400 V AC 50/60 Hz 15 kA Icu conforming to EN/IEC 60947-2 - <= 125 V DC 70 kA Icu conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz
Utilisation category	Category A conforming to EN 60898-1 Category A conforming to IEC 60898-1
Suitability for isolation	Yes conforming to EN 60947-2 Yes conforming to IEC 60947-2 Yes conforming to EN 60898-1 Yes conforming to IEC 60898-1
Standards	EN 60898-1 EN 60947-2 IEC 60898-1 IEC 60947-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	12...133 V AC 50/60 Hz 72...125 V DC 220...240 V AC 50/60 Hz 380...415 V AC 50/60 Hz 400 V AC 50/60 Hz 440 V AC 50/60 Hz
Magnetic tripping limit	8 x In +/- 20 %
[Ics] rated service breaking capacity	7500 A 75 % x Icu conforming to EN 60898-1 - 400 V AC 50/60 Hz 7500 A 75 % x Icu conforming to IEC 60898-1 - 400 V AC 50/60 Hz 15 kA 100 % x Icu conforming to IEC 60947-2 - 72...125 V DC 15 kA 100 % x Icu conforming to EN 60947-2 - 72...125 V DC 70 kA 100 % x Icu conforming to IEC 60947-2 - 12...133 V AC 50/60 Hz 70 kA 100 % x Icu conforming to EN 60947-2 - 12...133 V AC 50/60 Hz 70 kA 100 % x Icu conforming to EN 60947-2 - 220...240 V AC 50/60 Hz 70 kA 100 % x Icu conforming to IEC 60947-2 - 220...240 V AC 50/60 Hz 70 kA 100 % x Icu conforming to EN 60947-2 - 380...415 V AC 50/60 Hz 70 kA 100 % x Icu conforming to IEC 60947-2 - 380...415 V AC 50/60 Hz 70 kA 100 % x Icu conforming to EN 60947-2 - 440 V AC 50/60 Hz 70 kA 100 % x Icu conforming to IEC 60947-2 - 440 V AC 50/60 Hz
Limitation class	3 conforming to EN 60898-1 3 conforming to IEC 60898-1
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to IEC 60947-2 500 V AC 50/60 Hz conforming to EN 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to EN 60947-2 6 kV conforming to IEC 60947-2
Contact position indicator	Yes
Control type	Toggle
Local signalling	Trip indicator
Mounting support	DIN rail
Connection pitch	18 mm Between phases
9 mm pitches	4
Height	91 mm
Width	36 mm
Depth	78.5 mm
Product weight	0.25 kg
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Connections - terminals	Double terminal, top or bottom rigid wire(s) 1...25 mm <sup>2</sup> max Double terminal, top or bottom flexible wire(s) 1...16 mm <sup>2</sup> max
Wire stripping length	14 mm top or bottom
Tightening torque	2 N.m top or bottom
Earth-leakage protection	Separate block
Compatibility code	IC60
Market segment	Residential Small commercial

## Environment

IP degree of protection	IP20 conforming to EN 60529 IP20 conforming to IEC 60529
Pollution degree	3
Overvoltage category	IV
Tropicalisation	2
Relative humidity	95 % ( 55 °C )
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1650 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------