

PRODUCT-DETAILS

CP-T 24/20.0

CP-T 24/20.0 Power supply In: 3x400-500VAC
Out: 24VDC/20.0A



General Information

Extended Product Type	CP-T 24/20.0
Product ID	1SVR427056R0000
EAN	4016779662376
Catalog Description	CP-T 24/20.0 Power supply In: 3x400-500VAC Out: 24VDC/20.0A
Long Description	CP-T 24/20.0 Power supply In: 3x400-500VAC Out: 24VDC/20.0A

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044090

Popular Downloads

Data Sheet, Technical Information	2CDC114069D0201
Instructions and Manuals	1SVC427051M0000

Dimensions

Product Net Width	150 mm
Product Net Height	131 mm
Product Net Depth /	119 mm

Length

Product Net Weight	1.657 kg
--------------------	----------

Container Information

Package Level 1 Width	200 mm
Package Level 1 Depth / Length	190 mm
Package Level 1 Height	190 mm
Package Level 1 Gross Weight	1.922 kg
Package Level 1 EAN	4016779662376
Package Level 1 Units	box 1 piece

Technical

Function	Switch mode power supply
Number of Phases	3
Rated Input Voltage (U_{IN})	3x 400 ... 500 V AC
Input Voltage (U_{in})	3 x 340 ... 575 V AC 480 ... 820 V DC
Rated Frequency (f)	50 Hz
Rated Frequency Limits	47 ... 63 Hz
Characteristic of Output	U/I characterisitc curve or Hiccup-mode selectable
Rated Output Power	480 W
Output Power	480 W
Rated Output Voltage	24 V DC
Output Voltage (U_{out})	24 V DC
Rated Output Current	20 A
Output Current	20 A
Rated Impulse Withstand Voltage (U_{imp})	Input Circuit / Output Circuit 6 kV Input Circuit / PE 4 kV Input Circuit / Relay Contact 4 kV Output Circuit / PE 0.8 kV
Rated Insulation Voltage (U_i)	Input Circuit / Output Circuit 500 V Input Circuit / PE 500 V Input Circuit / Relay Contact 500 V Output Circuit / PE 50 V
Degree of Protection	Housing IP20 Terminals IP20
Pollution Degree	2
Connecting Capacity Input Circuit	Flexible with Ferrule 0.2 ... 4 mm ² Rigid 0.2 ... 6 mm ²
Connecting Capacity Output Circuit	Flexible with Ferrule 0.2 ... 4 mm ² Rigid 0.2 ... 6 mm ²
Tightening Torque	Input Circuit 1 N·m Output Circuit 0.6 N·m
Wire Stripping Length	Auxiliary Circuit 8 mm Input Circuit 8 mm Output Circuit 8 mm
Minimum Mounting Distance	Electrical Conductive Board, Horizontal 25 mm Electrical Conductive Board, Vertical 25 mm Other Device Same Type, Horizontal 25 mm Other Device Same Type, Vertical 25 mm
Mounting Position	1
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Standards	ANSI/ISA-12.12 CAN/CSA C22.2 No.107.1 CAN/CSA C22.2 No.213 CAN/CSA C22.2 No.60950

IEC/EN 63000
IEC 60950-1
IEC/EN 61000-6-2
IEC/EN 61000-6-3
UL 508
UL 60950

Environmental

Ambient Air Temperature	Operation -30 ... +70 °C Storage -40 ... +85 °C
Maximum Operating Altitude Permissible	5000 m
RoHS Status	Following EU Directive 2011/65/EU

Technical UL/CSA

Connecting Capacity Input Circuit UL/CSA	Rigid 24-10 AWG
Connecting Capacity Output Circuit UL/CSA	Rigid 24-10 AWG
Tightening Torque UL/CSA	Input Circuit 9 in-lb Output Circuit 5.5 in-lb

Electromagnetic Compatibility

Electrostatic Discharge (ESD Immunity) acc. to IEC 61000-4-2	Level 4 Air Discharge 15 kV Level 4 Contact Discharge 8 kV
Radiated Electromagnetic Field Immunity acc. to IEC 61000-4-3	Level 3 10 V/m
Electrical Fast Transient (Burst Immunity) acc. to IEC 61000-4-4	Level 4 Power Supply Port Signal 4 kV
Surge Immunity acc. to IEC 61000-4-5	Level 3 Line-to-Line 2 kV Level 4 Line-to-Line 4 kV
Conducted Disturbances Immunity acc. to IEC 61000-4-6	Level 3 10 V
Electromagnetic Compatibility (EMC)	Immunity - Class B Emission - Environment B

Certificates and Declarations (Document Number)

cUL Certificate	cUL508_E174460
cUR Certificate	cUR60950_E196145 cUR_ANSI_E317914
Declaration of Conformity - CE	1SVD982037-00
Declaration of Conformity - UKCA	1SVD982037-10
EAC Certificate	EAC_RU_C-DE.ME77.B.00768_20
Instructions and Manuals	1SVC427051M0000
RoHS Information	1SVD982006-0001
UL Certificate	UL508_E174460
UR Certificate	UR60950_E196145 UR_ANSI_E317914

Classifications

Object Classification Code	T
ETIM 4	EC002540 - DC-power supply
ETIM 5	EC002540 - DC-power supply
ETIM 6	EC002540 - DC-power supply
ETIM 7	EC002540 - DC-power supply
ETIM 8	EC002540 - DC-power supply
eClass	V11.0 : 27040701
UNSPSC	39121004
E-Number (Finland)	2712073
E-Number (Sweden)	5218721

Categories

Low Voltage Products and Systems → Control Products → Power Supplies → CP-T

