

A Donaldson Company

A WORLD LEADER IN FUME EXTRACTION TECHNOLOGY



V 200 ELECTRONICS

Last Updated on 13.04.2021

Single arm fume extraction system for electronics hand soldering processes.

BOFA's V 200 extraction unit has been designed to effectively capture and remove the potentially harmful fumes generated during hand soldering tasks. This portable system comes complete with an extraction arm and installation kit that contain everything required to set up one operator.

With a choice of arms, low noise levels and fast and easy installation, this unit can be moved with the work bench when factory layouts need changing due to production demands. The unit's fully comprehensive 3 stage filtration capabilities make it perfect for today's electronics manufacturing environments.

Technology



HEPA filter



Advanced carbon filter (ACF) technology ProTECT service plan



SureCHECK quality standard

Key features of the V 200

Filter blocked indicator Standard

99.997% HEPA filtration Standard

Single 1.4m extraction arm Optional Granulated carbon gas filter (ACF) technology Standard


1 x table mount installation kit and extraction arm Optional

Selection of arms Optional

Contact BOFA at https://bofainternational.com/en/contact/

https://bofainternational.com/en/portal/datasheets/v200-2/





- **1.** Filter condition display light
- nt 2. On / off switch
- 3. Hose inlet connection -50mm

4. Exhaust outlet

5. Power cable inlet


6. Lid latches

7. Feet

0

4





Technical data

	EU	US
Dimensions (HxWxD)	420 x 290 x 270mm	16.54 x 11.42 x 10.63"
Cabinet construction	Powder coated mild steel	Powder coated mild steel
Airflow / pressure	90m³/hr / 20mbar	53cfm / 20mbar
Electrical data	230v Single-phase 1~ 50/60Hz Full load current: 0.45 amps / 90w	115v 60/50Hz Full load current: 0.85 amps / 107w
Noise level	< 54dBA (at typical operating speed)	< 54dBA (at typical operating speed)
Weight	10kg	22lbs
Duct size	50mm	2"
Max duct run	3mtrs	9.8ft
Approvals	UKCA and CE	UKCA and CE

Pre-filter specifications		
Filter media	Borosilicate	
Filter media construction	Pad	
Filter efficiency	F7 (96% @ 2 microns)	

Combined filter specifications		
HEPA filter media	Borosilicate	
HEPA media construction	Pleated with glue bead spacers	
Gas filter	Treated activated carbon	
Filter housing	Zintec mild steel	
Filter efficiency	9.997% @ 0.3 microns	

Unit part numbers			
Model	Option	Voltage	Part number
V 200 powder coated	Unit only (no install kit)	230V	E0742A0001
V 200 powder coated	Unit only (no install kit)	115V	E0741A0001
V 200 powder coated	Table mount installation kit and extraction arm	230V	E0742A0000
V 200 powder coated	Table mount installation kit and extraction arm	115V	E0741A0000
V 200 powder coated	Single 1.4m extraction arm	230V	E0742A0002
V 200 powder coated	Single 1.4m extraction arm	115V	E0741A0002

Replacement filters		
Description	Part number	
Pre-filter (Pack of 5)	A1030102	
Combined filter	A1030099	

Unit options



Single arm volume extraction unit designed to extract fumes for one operator. Ideal for factories with changing demands and production layout changes.

1 - Unit only	2 - Table mount installation kit and extraction arm	3 - Single 1.4m extraction arm
Filter blocked Indicator	50mm x 650mm ESD Stay Put extraction arm	50mm x 1.4m ESD Stay Put extraction arm
Granulated carbon gas filter - ACF	Unique flip top flush sealing mounting plate	Filter blocked Indicator
99.997% HEPA filtration	Installation flex and table bracket	Granulated carbon gas filter - ACF
	Filter blocked Indicator	99.997% HEPA filtration
	Granulated carbon gas filter - ACF	
	99.997% HEPA filtration	

Arm accessories



Arm accessories		
Number reference to photo	Description	Part number
1	32mm ESD Stay put arm with funnel	A1020044
2	32mm ESD Stay put arm with nozzle	A1020046
3	50mm ESD Stay put arm with funnel	A1020045
4	50mm ESD Stay put arm with nozzle	A1020047
5	50mm ESD Stay put arm with slot	A1020049
6	38mm Stainless steel stay put arm with nozzle	A1020160
7	38mm Stainless steel stay put arm with funnel	A1020184
8	50mm ESD stay put arm with plenum funnel	A1020179
9	Light arm - White	A1020168
10	Light arm - Black	A1020169

Replacement unit mounted arm		
Number reference to photo	Description	Part number
11	Replacement arm - 50mm x 1.4m arm with nozzle (unit mounted)	A1020331

Unit/Arm accessory hose kit		
Number reference to photo	Description	Part number
12	50mm arm installation kit without arm	A1020177

Other languages

V 200 datasheet <u>Spanish</u> V 200 datasheet

<u>German</u>

V 200 datasheet <u>Russian</u> V 200 datasheet <u>French</u> V 200 datasheet <u>Italian</u>

Datasheet correct at time of publishing.

Where applicable, the carbon used in BOFA units is capable of removing a wide range of VOC's, however it is the responsibility of the user to ensure the carbon is suitable for their application. For specific applications, please contact us for details.

Think before you print! Please consider the environment before printing this document.