

# Stick lamps/ handheld lamps

## BENEFITS

- Very long service life
- Flexible use
- Including suspension hooks
- Sturdy handle
- Shock-resistant
- Minimal heat generation

### Battery-powered LED handheld lamp

- · Magnetic holder
- · Plastic
- $\cdot$  230 V~ mains adapter
- · Automotive charging device
- $\cdot$  With switch
- $\cdot$  Individually packed in blister packaging

· Diameter 6 cm

Battery-powered LED handheld lamp         394.188       60 LEDs, 3.6W   With 1 magnetic holder   Length: 42 cm         394.190       160 LEDs, 9.6W   With 2 magnetic holders   Length: 53.5 cm         PROFESSIONAL battery-powered LED handheld lamp         394.191       60 + 17 LEDs for torch function   With 2 magnetic holders   Length: 45.5 cm	#			
394.190 160 LEDs, 9.6 W   With 2 magnetic holders   Length: 53.5 cm PROFESSIONAL battery-powered LED handheld lamp	Battery-pov	Battery-powered LED handheld lamp		
PROFESSIONAL battery-powered LED handheld lamp	394.188	60 LEDs, 3.6W   With 1 magnetic holder   Length: 42 cm		
	394.190	160 LEDs, 9.6 W   With 2 magnetic holders   Length: 53.5 cm		
394.191 60 + 17 LEDs for torch function   With 2 magnetic holders   Length: 45.5 cm	PROFESSIONAL battery-powered LED handheld lamp			
	394.191	60 + 17 LEDs for torch function   With 2 magnetic holders   Length: 45.5 cm		







394.184

#### **Stick lamp**

- $\cdot$  8W fluorescent lamp
- $\cdot$  Not changeable, with integrated reflector
- $\cdot$  Electronic ballast unit built into the handle, 50 Hz
- $\cdot$  Plastic version with shock resistant protection tube and rotary hook
- $\cdot$  5.0 m H05RN-F 2x0.75 mm² supply cable with 2.5 A Euro plug
- $\cdot$  IP20, including light bulb

#	
394.184	Black   Diameter 1.5 cm   Length without hook: 46.5 cm

## Professional stick lamp with energy saving lamp

- · 11W/250V~, IP54
- · Interchangeable, anti-glare, pleasant light
- $\cdot$  Oil-resistant rubber version with shock-resistant protection tube
- Integrated reflector and robust suspension hooks
- 5.0 m H05RN-F 2 x 1.00 mm<sup>2</sup> rubber cable with contour plug
- $\cdot$  Splash-proof and dust-proof design
- · Including light bulb (Dulux S 11 watts)

#	Ĩ	Sec.
720.006	Black   Protection class II   Dual-insulated   Length: 40 cm	720.006

#### **Rubber handheld lamp**

- · E 27 holder, max. 100W/250V~
- · Interchangeable, with protective glass
- $\cdot$  Oil-resistant rubber design
- $\cdot$  Metal basket with integrated hook, light bulbs not included
- $\cdot$  Length: 27 cm

#	
394.183	5.0 m H05RN-F 2x 1.0 mm <sup>2</sup> supply cable with plug   IP44   Protection class II   Dual-insulated   Black
394.187	Without cable   IP40   Black
910.1011	Replacement glass   Protective glass

