



Product: [7965ENH](#)

Cat 6 Cable, U/UTP, LSZH, 4 Pair, AWG 23, Indoor CPR Eca

Product Description

CAT6 (250MHz), 4-Pair, U/UTP Unshielded, Premise Horizontal Cable, 23 AWG solid bare copper conductors, Polyethylene insulation, Nonbonded-Pair, LSZH jacket, CPR Eca

Technical Specifications

Product Overview

Suitable Applications:	Horizontal and building backbone cable; Support current and future Category 6 and 5e applications, such as: 1000Base - T (Gigabit Ethernet), 100 Base - T, 10 Base - T, FDDI, ATM
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

Insulation

Type	Material	Nominal Diameter
Dielectric	PO - Polyolefin	0.96 mm

Bonded-Pair:	No
--------------	----

Color Chart

Number	Color
Pair 1	White/Blue & Blue
Pair 2	White/Green & Green
Pair 3	White/Orange & Orange
Pair 4	White/Brown & Brown

Outer Jacket Material

Material	Nominal Diameter	Diameter +/- Tolerance
LSZH - Low Smoke Zero Halogen (Flame Retardant)	5.4 mm	0.3 mm

Construction and Dimensions

Min Elongation at Breakof Conductors:	10 %
Min Elongation at Breakof Insulation:	100 %
Min Elongation at Breakof Jacket:	100 %
Min Tensile Strength of Jacket:	9 MPa

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max DCR Unbalanced Between Pairs [%]	Max. DCR Unbalanced Within Pair [%]
95 Ohm/km	4 %	2 %

Capacitance

Max. Capacitance Unbalance	Max. Mutual Capacitance
1,600 pF/m	56 pF/m

Impedance

Nominal Characteristic Impedance
100 Ohm

Delay

Max. Delay Skew
40 ns/100m

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.1 dB/100m	75.3 dB	72.3 dB	73.2 dB	70.2 dB	70 dB	67 dB	20 dB	40 dB	35 dB
4 MHz	3.8 dB/100m	66.3 dB	63.3 dB	62.4 dB	59.4 dB	58 dB	55 dB	23 dB	34 dB	23 dB
10 MHz	6 dB/100m	60.3 dB	57.3 dB	54.3 dB	51.3 dB	50 dB	47 dB	25 dB	30 dB	15 dB
16 MHz	7.6 dB/100m	57.2 dB	54.2 dB	49.6 dB	46.6 dB	45.9 dB	42.9 dB	25 dB	28 dB	10.9 dB
20 MHz	8.5 dB/100m	55.8 dB	52.8 dB	47.3 dB	44.3 dB	44 dB	41 dB	25 dB	27 dB	9 dB
31.2 MHz	10.7 dB/100m	52.9 dB	49.9 dB	42.1 dB	39.1 dB	40.1 dB	37.1 dB	23.6 dB	25.1 dB	5.1 dB
62.5 MHz	15.5 dB/100m	48.4 dB	45.4 dB	32.9 dB	29.9 dB	34.1 dB	31.1 dB	21.5 dB	22 dB	
100 MHz	19.9 dB/100m	45.3 dB	42.3 dB	25.4 dB	22.4 dB	30 dB	27 dB	20.1 dB	20 dB	
155 MHz	25.3 dB/100m	42.4 dB	39.4 dB	17.1 dB	14.1 dB	26.2 dB	23.2 dB	18.8 dB	18.1 dB	
200 MHz	29.1 dB/100m	40.8 dB	37.8 dB	11.6 dB	8.6 dB	24 dB	21 dB	18 dB	17 dB	
250 MHz	33 dB/100m	39.3 dB	36.3 dB	6.3 dB	3.3 dB	22 dB	19 dB	17.3 dB	16 dB	

Table Notes:	Limits below 4 MHz are for information only. Reference standard: IEC 61156-5
General Electrical Parameters Notes:	Reference standard: ISO/IEC 61156-5
Coupling Attenuation Class:	Type III
Segregation class according EN50174-2:	a

Current

Max. Recommended Current [A]
1.5 Amps per Conductor

Voltage

Voltage Rating [V]
72 V

Temperature Range

Installation Temp Range:	0°C To +50°C
Operating Temp Range:	-30°C To +60°C

Mechanical Characteristics

Bulk Cable Weight:	37 kg/km
Max. Pull Tension:	80 N
Min Bend Radius During Installation:	46 mm
Min Bend Radius During Operation:	23 mm

Standards

IEC Compliance:	ISO/IEC 11801-1
CPR Euroclass:	Eca
CENELEC Compliance:	EN 50173-1
Data Category:	Category 6
ANSI Compliance:	ANSI/TIA 568.2-D (2018)
IEEE Compliance:	PoE: IEEE 802.3bt Type 1, Type 2, Type 3, Type 4

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Eca
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01

Flammability, LS0H, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
Burning Load:	455 kJ/m
IEC 60754-1 (EN50267-1)- Halogen Amount:	Zero
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 (EN 61034-2) (VDE 0482-1034) - Smoke Density Min. Transmittance:	IEC 61034-2

Part Number

Variants

Item #	Color	Putup Type	Length	EAN
7965ENH.00B100	Blue	Flat Box	100 m	8719605017185
7965ENH.00305	Blue	Reel	305 m	8719605017147
7965ENH.00A305	Blue	Reel-in-Box	305 m	8719605017178
7965ENH.00500	Blue	Reel	500 m	8719605017161
7965ENH.001000	Blue	Reel	1,000 m	8719605017130
7965ENH.01305	Gray	Reel	305 m	8719605017208
7965ENH.01A305	Gray	Reel-in-Box	305 m	8719605017239
7965ENH.01500	Gray	Reel	500 m	8719605017222
7965ENH.011000	Gray	Reel	1,000 m	8719605017192
7965ENH.003050	Gray	Reel	3,050 m	8719605017154
7965ENH.06305	Green	Reel	305 m	8719605017314
7965ENH.06A305	Green	Reel-in-Box	305 m	8719605017321
7965ENH.05A305	Orange	Reel-in-Box	305 m	8719605017307
7965ENH.03A305	Purple	Reel-in-Box	305 m	8719605017277
7965ENH.03305	Purple	Reel	305 m	8719605017253
7965ENH.03500	Purple	Reel	500 m	8719605017260
7965ENH.04A305	White	Reel-in-Box	305 m	8719605017291
7965ENH.041000	White	Reel	1,000 m	8719605017284
7965ENH.07305	Yellow	Reel	305 m	8719605170149

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system.
--------	--

History

Update and Revision:	Revision Number: 0.245 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.