



# SIMPLE INSTALLATION. SOPHISTICATED LOOK.

## A NEW DESIGN FOR YOUR OLD DRIVE

Upgrade your used 7mm 2.5" HDD or SSD with a bold and durable look. The Bolt B75 Pro enclosure permits great heat dissipation through its aluminum body, while its 3D ridges provide an aesthetically wondrous barrier from scratches and fingerprints. Furthermore, its 12.2mm-thick casing is military-grade shockproof - but don't let that fool you - it's extremely lightweight at only 0.07 kilogram.



## SUPER SPEED FOLLOWS PERFECT FORM

This sleek and slim aluminum enclosure is not only shockproof and scratchproof - the inside is just as impressive, too. Equipped with a USB 3.2 Gen 2 interface, it can transfer data up to a lightning-fast 10Gbp/s. That's twice as fast as its predecessor, USB 3.1 Gen 1. What makes it so quick? The answer is full-duplex communication, which means that information can be transferred and received simultaneously.



## 2.5" SATA III to USB 3.2 Gen 2 Bolt B75 Pro Enclosure

### Features

- Super-speed data transfer with USB 3.2 Gen 2 interface (up to 10Gbp/s)
- Durable, shockproof construction for worry-free, on-the-go usage
- 3D ridged design for protection against scratches and fingerprints
- Made of lightweight aluminum with superior heat dissipation
- Slim L-shaped LED status light that can be seen from top and front angles

### Package Contents

- 1x 2.5" SATA III to USB 3.2 Gen 2 Bolt B75 Pro Enclosure
- 1x USB Type-C (Bolt B75 Pro) to Type-A (PC) cable
- 5x Mounting screws

\* SSD/HDD not included

### Specifications

- Connection Interface: USB 3.2 Gen 2 Type-C (USB 3.1, USB 3.0, USB 2.0 backwards-compatible)
- Internal Interface: 7mm 2.5" SATA III SSD or HDD
- Dimensions: 124.4mm x 82.0mm x 12.2mm
- Weight: 72g
- Material: Aluminum
- Color: Black
- OS Compatibility: Windows 10/8.1/8/7/Vista/XP, Mac OS 10.3.x or later, Linux 2.6.x or later, Android OS 6.0 or later
- Operating Temperature: 5°C - 55°C
- Storage Temperature: -40°C - 70°C
- Power Support: DC 5V
- Certification: CE, FCC, BSMI, Green dot, WEEE, RoHS, KCC
- Warranty: 2 years

