



## The sturdy AG Neovo CMP-01 ceiling mount pole designed for demanding public environments.


The combination of the CMP-01 and a variety of AG Neovo display mount kits provides comprehensive ceiling mount solutions for small- to large-sized professional displays. The adjustable height and 360 degree of pole swivel function can achieve various viewing angles with WMK-03, LMK-01 and LMK-02 tilt mounts. Designed for public environments, the CMP-01 ensures safety and reliability with the durable steel.

- > Ceiling mounting solution contains CMP-01 with optional WMK-03, LMK-01 and LMK-02 based on display sizes
- > Robust steel design guarantees durability
- > Cables are managed within the pole for concise appearance
- > 50 cm of height adjustment
- > Swivel left and right for 360°
- > Weight capacity: 60 kg per side\*

## Specifications

Mounting	VESA Standard	Depends on AG Neovo display mount kits
Loading	Weight Capacity	60 kg (132.3 lbs) per side*
Adjustment	Swivel	360°
	Height	924 mm ~ 1424 mm (36.4" ~ 56.1")
Exterior	Material	Steel
	Colour	Black
Dimensions	Net (W x H x D)	172 x 1424 x 200 mm
		(6.8" x 56.1" x 7.9")
	Packing (W x H x D)	975 x 270 x 229 mm
		(38.4" x 10.6" x 9.0")
Weight	Net Weight	6.7 kg (14.8 lbs)
	Gross Weight	7.7 kg (17.0 lbs)
Packing	1 Carton	1 set
	1 Pallet	35 sets

 $^{*}$   $\Delta$  60 kg for display and display mount per side.



Ø56.5 mm