

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Cordless Combi

GSB 18V-110 C



Extremely powerful and robust 18 V impact drill driver – with brushless motor and impact drilling function

The most important data

Torque (soft/hard/max.)	47/85/110 Nm
No-load speed (1st gear / 2nd gear)	0 – 480 / 0 – 2,100 rpm
Max. screw diameter	12 mm

Part Number 0 601 9G0 30A[> More product information](#)

Technical data

Technical data

Torque (max)	110 Nm
Torque (soft/hard/max.)	47/85/110 Nm
No-load speed (1st gear / 2nd gear)	0 – 480 / 0 – 2,100 rpm
Battery type	Lithium-ion
Max. impact rate	31,500 bpm
Chuck capacity, min./max.	1.5 / 13 mm
Battery voltage	18.0 V
Weight excl. battery	1.9 kg
Torque settings	25+2
Packaging dimensions (width x length x height)	360 x 442 x 155 mm

Drilling diameter

Max. drilling diameter in wood	82 mm
Max. drilling diameter in steel	13 mm
Max. drilling diameter in masonry	16 mm

Screw diameter

Max. screw diameter	12 mm
---------------------	-------

Noise/vibration information

Drilling in metal

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

Impact drilling in masonry

Vibration emission value ah	15.5 m/s ²
Uncertainty K	1.5 m/s ²



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- 110 Nm maximum torque and brushless motor make the tool extremely strong
- Full-metal chuck for high durability make the impact drill driver capable of handling even the toughest applications on the jobsite
- Bluetooth Connectivity option to connect directly to a smartphone for additional tool control

