

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Rotary Hammer with SDS plus

GBH 2-26 F



All-round performance rotary hammer with quick-change chuck in the SDS plus category

The most important data

Rated input power	830 W
Impact energy (according to EPTA 05/2016)	2.7 J
Drilling dia. concrete, hammer drill bits	4 – 26 mm

Part Number 0 611 2A4 060 920[> More product information](#)

Technical data

Performance data

Impact rate at rated speed	0 – 4,000 bpm
Rated speed	0 – 900 rpm

Technical data

Rated input power	830 W
Impact energy (according to EPTA 05/2016)	2.7 J
Tool holder	SDS plus
Packaging dimensions (width x length x height)	362 x 443 x 118 mm
Voltage, electrical	110 V
Weight	2.9 kg

Drilling range

Drilling dia. concrete, hammer drill bits	4 – 26 mm
Opt. appl. range concrete, hammer drill bits	8 – 16 mm
Drilling diameter in concrete with core cutters	16 – 68 mm
Max. drilling diameter in metal	13 mm
Max. drilling diameter in wood	30 mm

Noise/vibration information

Hammer drilling in concrete

Vibration emission value ah	15.3 m/s ²
Uncertainty K	1.5 m/s ²

Chiselling in concrete

Vibration emission value ah	11.5 m/s ²
Uncertainty K	1.5 m/s ²



Product data sheet

Power tools for trade & industry

Advantages:

- Delivers 2.7 J of impact energy for fast drilling and high chisel removal performance
- High-quality components ensure robustness, reliability, and long lifetime
- Optional chisel mode and quick-change chuck enable use in wide range of applications

