


**20x20**

A = 1,6 cm<sup>2</sup>  
 $I_x = 0,7 \text{ cm}^4$   
 $I_y = 0,7 \text{ cm}^4$   
 $W_x = 0,7 \text{ cm}^3$   
 $W_y = 0,7 \text{ cm}^3$   
 m = 0,4 kg/m




19168

Cover cap	Color	ESD	No.
20x20 (1x)	Signal gray		100 <b>3 842 548 742</b>
20x20 (1x)	Black		20 <b>3 842 548 743</b>
Material:	PP		

**20x20 1N**

A = 1,9 cm<sup>2</sup>  
 $I_x = 0,8 \text{ cm}^4$   
 $I_y = 0,8 \text{ cm}^4$   
 $W_x = 0,8 \text{ cm}^3$   
 $W_y = 0,8 \text{ cm}^3$   
 m = 0,5 kg/m




19169

Cover cap: See 20x20

**20x20 2N**

A = 1,8 cm<sup>2</sup>  
 $I_x = 0,7 \text{ cm}^4$   
 $I_y = 0,8 \text{ cm}^4$   
 $W_x = 0,7 \text{ cm}^3$   
 $W_y = 0,8 \text{ cm}^3$   
 m = 0,5 kg/m



19170

Cover cap: See 20x20

20x20	L (mm)	No.
1 pcs	50 ... 3000	<b>3 842 992 888 / L</b>
1 pcs M6	50 ... 3000	<b>3 842 993 230 / L</b>
1 pcs M6  M6	70 ... 3000	<b>3 842 993 231 / L</b>
1 pcs M6  D8	70 ... 3000	<b>3 842 993 494 / L</b>
1 pcs D8	50 ... 3000	<b>3 842 993 493 / L</b>
1 pcs D8  D8	50 ... 3000	<b>3 842 993 495 / L</b>
1 pcs D8  D8V	50 ... 3000	<b>3 842 993 496 / L</b>
20 pcs	3000	<b>3 842 517 179</b>

**Quick & Easy** (p. 2-8, see fold-out section)

20x20	No.
20x20	<b>3 842 993 694 / ...</b>
Length L (mm)	50 ... 3000
Standard profile finishing (note minimum length, p. 2-11)	M6 / D5.8 / D8 / DB8
Customized profile finishing (L <sub>max</sub> = 2300 mm)	DI / DIS / MT / MTS / MI / MIS / DG <sup>1)</sup>

<sup>1)</sup> DG<sub>max</sub> = 45°; L<sub>min1</sub> / L<sub>min2</sub> = 335 / 370 mm

20x20 1N	L (mm)	No.
1 pcs	50 ... 3000	<b>3 842 993 421 / L</b>
20 pcs	3000	<b>3 842 536 475</b>

**Quick & Easy** (p. 2-8, see fold-out section)

20x20 1N	No.
20x20 1N	<b>3 842 993 690 / ...</b>
Length L (mm)	50 ... 3000
Standard profile finishing (note minimum length, p. 2-11)	M6 / D5.8 / D8 / DB8
Customized profile finishing (L <sub>max</sub> = 2300 mm)	DI / DIS / MT / MTS / MI / MIS / DG <sup>1)</sup>

<sup>1)</sup> DG<sub>max</sub> = 45°; L<sub>min1</sub> / L<sub>min2</sub> = 335 / 370 mm


20x20 2N	L (mm)	No.
1 pcs	50 ... 3000	<b>3 842 993 422 / L</b>
20 pcs	3000	<b>3 842 536 478</b>

**Quick & Easy** (p. 2-8, see fold-out section)

20x20 2N	No.
20x20 2N	<b>3 842 993 691 / ...</b>
Length L (mm)	50 ... 3000
Standard profile finishing (note minimum length, p. 2-11)	M6 / D5.8 / D8 / DB8
Customized profile finishing (L <sub>max</sub> = 2300 mm)	DI / DIS / MT / MTS / MI / MIS / DG <sup>1)</sup>

<sup>1)</sup> DG<sub>max</sub> = 45°; L<sub>min1</sub> / L<sub>min2</sub> = 335 / 370 mm

**20x40**  
 $A = 2,9 \text{ cm}^2$   
 $I_x = 4,6 \text{ cm}^4$   
 $I_y = 1,2 \text{ cm}^4$   
 $W_x = 2,5 \text{ cm}^3$   
 $W_y = 1,4 \text{ cm}^3$   
 $m = 0,8 \text{ kg/m}$




19174

Cover cap	Color	ESD	No.
20x20 (2x)	Signal gray		100 <b>3 842 548 742</b>
20x20 (2x)	Black		20 <b>3 842 548 743</b>

Material: PP

**20x60**  
 $A = 3,5 \text{ cm}^2$   
 $I_x = 14,2 \text{ cm}^4$   
 $I_y = 1,7 \text{ cm}^4$   
 $W_x = 4,7 \text{ cm}^3$   
 $W_y = 1,7 \text{ cm}^3$   
 $m = 0,9 \text{ kg/m}$




19175

Cover cap	Color	ESD	No.
20x60 (1x)	Signal gray		20 <b>3 842 548 828</b>
20x60 (1x)	Black		20 <b>3 842 548 829</b>

Material: PP

**20x40x40**  
 $A = 4,2 \text{ cm}^2$   
 $I_x = 6,0 \text{ cm}^4$   
 $I_y = 6,0 \text{ cm}^4$   
 $W_x = 2,6 \text{ cm}^3$   
 $W_y = 2,6 \text{ cm}^3$   
 $m = 1,1 \text{ kg/m}$



19176

Cover cap	Color	ESD	No.
20x20 (3x)	Signal gray		100 <b>3 842 548 742</b>
20x20 (3x)	Black		20 <b>3 842 548 743</b>

Material: PP

20x40	L (mm)	No.
1 pcs	50 ... 3000	<b>3 842 992 891 / L</b>
1 pcs	50 ... 3000	<b>3 842 993 497 / L</b>
1 pcs	50 ... 3000	<b>3 842 993 499 / L</b>
1 pcs	50 ... 3000	<b>3 842 993 500 / L</b>
1 pcs	50 ... 3000	<b>3 842 993 498 / L</b>
1 pcs	50 ... 3000	<b>3 842 993 501 / L</b>
24 pcs	3000	<b>3 842 537 816</b>

Profile finishing: D8: in slots B/F, C/E  
 D8V: in slots A/D

**Quick & Easy** (p. 2-8, see fold-out section)

20x40	No.
<b>3 842 993 696 / ...</b>	
Length L (mm)	50 ... 3000
Standard profile finishing (note minimum length, p. 2-11)	M6 / D5.8 / D8 / DB8
Customized profile finishing (L <sub>max</sub> = 2300 mm)	DI / DIS / MT / MTS / MI / MIS / DG <sup>1)</sup>

<sup>1)</sup> DG<sub>max</sub> = 45°; L<sub>min1</sub> / L<sub>min2</sub> = 370 / 440 mm

20x60	L (mm)	No.
1 pcs	50 ... 3000	<b>3 842 992 992 / L</b>
16 pcs	3000	<b>3 842 537 819</b>

**Quick & Easy** (p. 2-8, see fold-out section)

20x60	No.
<b>3 842 993 698 / ...</b>	
Length L (mm)	50 ... 3000
Standard profile finishing (note minimum length, p. 2-11)	M6 / D5,8 (B,C,E,F) <sup>1)</sup> / D8 (B,C,E,F) <sup>1)</sup> / DB8
Customized profile finishing (L <sub>max</sub> = 2300 mm)	DI / DIS / MT / MTS / MI / MIS / DG <sup>2)</sup>

<sup>1)</sup> For the specified slots

<sup>2)</sup> DG<sub>max</sub> = 45°; L<sub>min1</sub> / L<sub>min2</sub> = 404 / 508 mm

20x40x40	L (mm)	No.
1 pcs	50 ... 3000	<b>3 842 992 991 / L</b>
16 pcs	3000	<b>3 842 537 818</b>

**Quick & Easy** (p. 2-8, see fold-out section)

20x40x40	No.
<b>3 842 993 697 / ...</b>	
Length L (mm)	50 ... 3000
Standard profile finishing (note minimum length, p. 2-11)	M6 / D5.8 / D8 / DB8
Customized profile finishing (L <sub>max</sub> = 2300 mm)	DI / DIS / MT / MTS / MI / MIS / DG <sup>1)</sup>

<sup>1)</sup> DG<sub>max</sub> = 45°; L<sub>min1</sub> / L<sub>min2</sub> = 370 / 440 mm