





**Cutting discs – Metal**


- ▶ **Appropriate for** hand-held angle grinders
- ▶ Maximum circumferential speed: 80 m/s (depending on rpm and disc diameter)

Product properties	Ordering information										
	Specification	Diameter mm	Bore diameter mm	Thickness mm	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
 <p>Diagram showing dimensions: d (bore diameter), k (thickness), b (cutting edge width), D (outer diameter), and k (total thickness).</p>	Straight										
	<b>A 30 R BF</b>	100	16.00	2.8	<b>2 608 600 091</b>	U0	1	25	049375	GAA	0.73
	<b>A 30 S BF</b>	115	22.23	2.5	<b>2 608 600 318</b>	U0	1	25	149402	GAA	0.82
	<b>A 30 S BF</b>	125	22.23	2.5	<b>2 608 600 394</b>	U0	1	25	181846	GAA	0.94
	<b>A 30 S BF</b>	180	22.23	3.0	<b>2 608 600 321</b>	U0	1	25	149433	GAA	1.19
	<b>A 30 S BF</b>	230	22.23	3.0	<b>2 608 600 324</b>	U0	1	25	149495	GAA	1.52
<b>A 30 R BF</b>	300	22.23	3.2	<b>2 608 600 649</b>	U0	1	10	252829	GAA	4.13	

 <p>Diagram showing dimensions: d (bore diameter), k (thickness), b (cutting edge width), D (outer diameter), and c (depressed centre diameter).</p>	With depressed centre										
	<b>A 30 S BF</b>	115	22.23	2.5	<b>2 608 600 005</b>	U0	1	25	031196	GAA	0.99
	<b>A 30 S BF</b>	125	22.23	2.5	<b>2 608 600 221</b>	U0	1	25	116428	GAA	1.14
	<b>A 30 S BF</b>	180	22.23	3.0	<b>2 608 600 316</b>	U0	1	25	149389	GAA	1.50
	<b>A 30 S BF</b>	230	22.23	3.0	<b>2 608 600 226</b>	U0	1	25	116473	GAA	2.04

 <p>Diagram showing dimensions: d (bore diameter), k (thickness), b (cutting edge width), and D (outer diameter).</p>	Straight <b>Appropriate for</b> chop saws / stationary pendulum action cutters/grinders Maximum drive power of 3 bhp/2.4 kW										
	<b>A 36 R BF</b>	350	25.40	2.8	<b>2 608 600 543</b>	U0	1	10	218658	GAA	4.69

 <p>Diagram showing dimensions: d (bore diameter), k (thickness), b (cutting edge width), and D (outer diameter).</p>	Straight <b>Appropriate for</b> petrol-driven freehand cutting machines										
	<b>A 24 R BF</b>	300	20.00	3.5	<b>2 608 600 706</b>	U0	1	10	262071	GAA	2.81

 <p>Diagram showing dimensions: d (bore diameter), k (thickness), b (cutting edge width), and D (outer diameter).</p>	Straight <b>Appropriate for</b> Cordless Angle Grinder GWS 14,4 V Professional with SDS-pro fitting										
	<b>A 46 Q BF</b>	100	22.23	1.2	<b>2 608 600 700</b>	U0	1	25	261449	GAA	1.14

### Grinding discs – Metal

- ▶ Grinding disc for metal
- ▶ **Appropriate for** hand-held angle grinders
- ▶ Maximum circumferential speed: 80 m/s (depending on rpm and disc diameter)



Specification	Diameter mm	Bore diameter mm	Thickness mm	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
<b>Product properties</b>			<b>Ordering information</b>							
A 30 T BF	115	22.23	6.0	<b>2 608 600 218</b>	U0	1	10	116398	GAA	1.39
A 30 T BF	125	22.23	6.0	<b>2 608 600 223</b>	U0	1	10	116442	GAA	1.57
A 30 T BF	180	22.23	6.0	<b>2 608 600 315</b>	U0	1	10	149372	GAA	2.33
A 30 T BF	230	22.23	6.0	<b>2 608 600 228</b>	U0	1	10	116497	GAA	2.98
A 24 S BF	100	16.00	6.0	<b>2 608 600 017</b>	U0	1	10	049344	GAA	1.12

### Grinding discs – Inox

- ▶ High-quality grinding disc for Inox
- ▶ **Appropriate for** hand-held angle grinders
- ▶ Maximum circumferential speed: 80 m/s (depending on rpm and disc diameter)
- ▶ Fe/S/Cl < 0.1%



AS 30 S INOX BF	125	22.23	6	<b>2 608 602 488</b>	U0	1	10	523042	GAA	2.40
AS 30 S INOX BF	150	22.23	6	<b>2 608 602 489</b>	U0	1	10	523059	GAA	2.96



Straight – Inox  
**Appropriate for** Cordless Angle Grinder GWS 14,4 V Professional with SDS-pro fitting

A 30 Q BF	100	22.23	4	<b>2 608 600 702</b>	U0	1	10	261463	GAA	2.15
-----------	-----	-------	---	----------------------	----	---	----	--------	-----	------