



RACK PDU, BASIC, HALF HEIGHT, 100-240V/20A, 220-240V/16A, (14) C13

AP6003A

Call for More Information 0800 2799254

- Includes: Installation guide, Safety guide

| Output | |
|----------------------------|------------------------------------|
| Nominal Output Voltage | 100V, 120V, 200V, 208V, 230V, 240V |
| Maximum Total Current Draw | 20 |
| Output Connections | (14) IEC 60320 C13 |

| Input | |
|--|---------------|
| Nominal Input Voltage | 230V |
| Input frequency | 50/60 Hz |
| Input Connections | IEC 60320 C20 |
| Acceptable Input Voltage | 100 - 240VAC |
| Load Capacity | 3300VA |
| Maximum Input Current | 20A |
| Maximum Line Current | 20A |
| Regulatory Derated Input Current (North America) | 16A |

| Physical | |
|-----------------|---------------|
| Maximum Height | 523MM, 52.3CM |
| Maximum Width | 56MM, 5.6CM |
| Maximum Depth | 47MM, 4.7CM |
| Net Weight | 1.88KG |
| Shipping weight | 2.55KG |
| Shipping Height | 612MM, 61.2CM |

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

Technical Specifications

RACK PDU, BASIC, HALF HEIGHT, 100-240V/20A, 220-240V/16A, (14) C13 | AP6003A | Downloaded on 02/25/2022 (EST)

| Physical | |
|------------------|---------------|
| Shipping Width | 123MM, 12.3CM |
| Shipping Depth | 107MM, 10.7CM |
| Color | Black |
| Units per Pallet | 96.0 |

| Environmental | |
|-----------------------------|-----------------|
| Operating Temperature | 0 - 50 °C |
| Operating Relative Humidity | 5 - 95 % |
| Operating Elevation | 0 - 3048meters |
| Storage Temperature | -15 - 65 °C |
| Storage Relative Humidity | 5 - 95 % |
| Storage Elevation | 0 - 15240meters |

| Conformance | |
|-------------------|---------------------------|
| Approvals | cUL listed, UL listed |
| Standard warranty | 2 years repair or replace |

| Sustainable Offer Status | |
|--------------------------|-----------|
| RoHS | Compliant |

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.