

# ALIENWARE TRI-MODE WIRELESS GAMING MOUSE – AW720M



## **UNMATCHED CAPABILITIES**

Enjoy unprecedented performance with 26,000 DPI, tracking of up to 650 IPS and sensors capable of handling up to 50G of max acceleration.<sup>1</sup> Plus, reduce debounce time, boost precision and enhance accuracy with long-lasting optical switches and uniquely-designed, magnetically sprung, independent L/R keyplates that are faster, stiffer and more durable than traditional spring mechanisms.

## **GAME UNINTERRUPTED**

Connect via a USB-C Wireless Dongle and get up to 140-hrs of robust, lag-free gaming. Alternatively, get up to 420 hours with a Bluetooth connection.<sup>2</sup>

Magnetic snap-on charging is easy to connect and disconnect, enabling you to keep your mouse powered up, without compromising performance.

When every minute counts, fast-charging provides up to 20 hours of gameplay, with only a five-minute charge.<sup>2</sup>

## **TRI-MODE CONNECTIVITY**

Experience a silky-smooth, wired-like performance with our 2.4GHz USB-C Wireless Dongle with 1000Hz Wireless Polling. Or connect the AW720M via Bluetooth 5.1, ideal for use with a laptop or mobile device. And for a traditional wired experience, connect to a PC with the included USB-A to USB-C cable.

## **ONE-OF-A-KIND DESIGN**

Eight programmable buttons and 3D-sculpted thumb grips pair with a slimmer, more symmetrical design for an enhanced, ambidextrous grip.

When it comes to looks, the AW720M is in a class of its own, thanks to iconic Alienware design and AlienFX RGB lighting that syncs with the Alienware Command Center.

The stunning Lunar Light and Dark Side of The Moon color option compliments a surface that's smooth to the touch and stain resistant—for a gaming experience as stunning as it is powerful.

# FEATURES AND TECHNICAL SPECIFICATIONS



## ALIENWARE TRI-MODE WIRELESS GAMING MOUSE AW720H

CONNECTIVITY	2.4GHz Gaming Wireless Bluetooth 5.1 Connectivity USB Wired
GAMING POLLING	1000Hz over Wired & 2.4GHz Gaming Wireless
BATTERY LIFE <sup>2</sup>	140 Hours - 2.4GHz Gaming Wireless 420 Hours - Bluetooth
FAST CHARGING <sup>2</sup>	5 minutes charge for 20 hours of gameplay
SENSOR MAX SENSITIVITY	Native 26,000 DPI
SENSOR MAX SPEED	650 IPS
SENSOR MAX ACCELERATION <sup>1</sup>	50G
NUMBER OF BUTTONS	8 Fully Programmable buttons, arranged
CLICK LIFESPAN	70 Million for L/R Buttons
WEIGHT	~89g
LIGHTING	1 Zone 16.8 Million RGB, AlienFX
CABLE TYPE	2m Light Ultra-flexible Braided Cable
COLORS	Lunar Light Dark Side of the Moon
KEYPLATE STRUCTURE	Magnetically Assisted
CHARGING CONNECTOR	Magnetic Snap Charging Adapter USB-A to USB-C Cable



<sup>1</sup>Max Acceleration vs Windows Mouse Acceleration. Max Acceleration describes the fastest rate of change of speed that the sensor can handle. Windows Mouse Acceleration (or Enhance pointer precision) is a legacy feature in the Windows OS where reported DPI count is multiplied. Used for low DPI mice on growing monitor resolutions.

<sup>2</sup>20 hours continuous play without LEDs after charging dead battery for 5 minutes.

*Technical specifications subject to change without prior notice.*

Product availability varies by country. Please contact your Dell representative for more information.