

# Emergency stop/emerg. switching off button, classic,mushroom,38mm,pull-to-release function,2 N/C,cable (black) with m12a plug, 5p, 0.2 m $\,$



Part no. C22-PV-K02-P10 Article no. 185184

Delivery program			
Product range			RMQ compact solution
Basic function			Controlled stop pushbuttons/emergency-stop buttons
Single unit/Complete unit			Complete unit
Design			Mushroom-shaped
Diameter	Ø	mm	38
Illumination			Non-illuminated
			Pull-to-release function
Connection type			Cable (black) with M12A plug, 5 pole
Cable Length		m	0.2
Description			Tamper-proof according to ISO 13850, EN 418
Colour			
Mushroom head			Red
Base			yellow
Degree of Protection			IP66, IP67, IP69K (front) IP65 (on rear)
Connection to SmartWire-DT			no
Contacts			
N/C = Normally closed			2 NC →
Notes			e safety function, by positive opening to IEC/EN 60947-5-1
Actuator travel and actuation force as per DIN EN 60947-5-1, K.5.4.1			
	mm		4.65
Maximum travel	mm		5.7
Minimum force for positive opening	N		30
Contact sequence			1 5
Contact travel = Contact closed = Contact open			
Contact diagram			0 2.2 5.5 Zw = 4.5 mm

## **Technical data**

General			
Standards			IEC/EN 60947-5-5 VDE 0660
Certifications			CE, UL, CSA
Lifespan, mechanical	Operations	x 10 <sup>6</sup>	>1
Operating frequency	Operations/h		≦ <sub>300</sub>
Actuating force		n	≦ <sub>50</sub>
Plug tightening torque		N/m	1
Tightening torque Threaded ring		Nm	2
Climatic proofing			Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
Degree of Protection			IP66, IP67, IP69K (front) IP65 (on rear)
Mounting position			As required
Mechanical shock resistance, shock duration 11 ms		g	> 30
Contacts			
Rated impulse withstand voltage	$U_{\text{imp}}$	V AC	4000
Rated insulation voltage	Ui	V	250
Overvoltage category/pollution degree			III/3
Control circuit reliability			
At 17 V DC/7 mA	H <sub>F</sub>		N/C contact: statistically determined 1 failure per 0.9 $\times$ 10 $^6$ Operations
Max. short-circuit protective device			
Fuse	gG/gL	Α	4
Rated conditional short-circuit current	Iq	kA	1
Switching capacity			
Rated operational current	I <sub>e</sub>	Α	
AC-15			
24 V	I <sub>e</sub>	Α	4
DC-13			
24 V	I <sub>e</sub>	Α	3
Cable characteristics			
Design			M12A
Cable Length		m	0.2
Material characteristic			PUR

### Design verification as per IEC/EN 61439

Technical data for design verification		
Operating ambient temperature min.	°C	-25
Operating ambient temperature max.	°C	70

mm

4.7

#### **Technical data ETIM 6.0**

Diameter

Low-voltage industrial components (EG000017) / Emergency stop complete (EC002034)

Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / EMERGENCY-STOP pushbutton, complete device (ecl@ss8.1-27-37-12-44 [ACN986008])

Ø

(ecl@ss8.1-27-37-12-44 [ACN986008])		
Unlocking method		Pull release
Number of contacts as normally closed contact		2
Number of contacts as normally open contact		0
Degree of protection (IP)		-
Mounting method		Built-in
With lighting		No
Hole diameter	mm	22
Connection type auxiliary circuit		-
Diameter cap	mm	38

### **Dimensions**

