# M20142104

# Q14 series

Ø14 mm panel mount LED indicators



# **DISTINCTIVE FEATURES**

10 mm colored diffused epoxy lens or 10 mm water clear super bright LEDs

Prominent and flush bezel styles

(2.8 x 0.8) solder lug/faston terminals, pins or (200 mm long) wire terminations

Custom engraving available

Available in RGB



# **ENVIRONMENTAL SPECIFICATIONS**

- IP67 sealing option (EN60529)
- Operating & Storage Temperature Range:
   Rear plastic body: -30 °C to +65° C (-22 °F to +149 °F)
   Rear epoxy body: -40 °C to +85° C (-40 °F to +185 °F)



# **GENERAL SPECIFICATIONS**

- Max Reverse Voltage: 5 V
- Viewing Angle: 30–100° (dependant on model)
- Life Expectancy: 100,000 hours
- Torque: 75 cNm
- Maximum panel thickness 11 mm
- Insulation resistance : 4,000  $M\Omega$  at 500 VDC



## **MATERIALS**


 Plated brass bezel finished in bright chrome, black or satin grey and molded polycarbonate rear body



# **MOUNTING**







The company reserves the right to change specifications without notice.

All LED characteristics are dependent upon environmental conditions. Therefore published data should be considered nominal and subject to variations.





Ø14 mm panel mount LED indicators



# **ELECTRICAL SPECIFICATIONS**

### STANDARD LED INTENSITY

LED COMPONENT SPECIFICATIONS			
	Prominent and Recessed	Flush	Forward Voltage
HE Red	380 mcd	10 mcd	2.0 V
Green	60 mcd	5 mcd	2.2 V
Yellow	50 mcd	4 mcd	2.1 V
Blue	540 mcd	100 mcd	3.3 V
White	1000 mcd	150 mcd	3.3 V
Orange	80 mcd	200 mcd	2.2 V
Bi-color (Typical) (Red/Green)	220/150 mcd	14/10 mcd	2.0V/2.2 V
Tri-color (Typical) (Red/Green/Yellow)	60/50/50mcd	15/10/30 mcd	2.0 V/2.2 V/2.1 V

Bi-color - The color is changed by reversing the polarity of the supply voltage.

Tri-color - The indicator has red and green LEDs, when both connected yellow is produced.

### SUPER BRIGHT LED INTENSITY

LED COMPONENT SPECIFICATIONS			
	Prominent and Recessed	Flush	Forward Voltage
HE Red	17,000 mcd	2,000 mcd	2.2 V
Green	11,000 mcd	680 mcd	3.3 V
Yellow	12,000 mcd	350 mcd	2.0 V
Blue	2,500mcd	250 mcd	3.3 V
White	4,400 mcd	250 mcd	3.3 V
Orange	2,800 mcd	300 mcd	2.2 V

### HYPER BRIGHT LED INTENSITY

LED COMPONENT SPECIFICATIONS			
	Prominent and Recessed	Flush	Forward Voltage
HE Red	2,800 mcd	800 mcd	2.1 V
Green	2,200 mcd	250 mcd	3.2 V
Yellow	1,300 mcd	250 mcd	2.0 V
Orange	850 mcd	200 mcd	2.1 V

## RGB LED INTENSITY

ITEM	SYMBOL	CONDITION	TYP.
DC Forward Voltage	V <sub>F</sub> (R)	IF=20 mA	2.1
	V <sub>F</sub> (B/G)	IF=20 mA	3.1
Luminous Intensity	Iv (Red)		220 mcd
	Iv (Green)		500 mcd
	Iv (Blue)		100 mcd

Voltage	Operating Voltage	Operating Current
	(Min to Max)	(Typical All Types)
02 (No Resistor)	1.8 to 3.3 VDC	20 mA max
6 VDC	5.4 to 6.6 VDC	20 mA
12 VDC	10.8 to 13.2 VDC	20 mA
24 VDC	21.6 to 26.4 VDC	20 mA
28 VDC	25.2 to 30.8 VDC	20 mA
110 VAC	99 to 121 VAC	6 mA
220 VAC	207 to 235 VAC	3 mA
* Customer to supply resistor for desired operating		

\* Customer to supply resistor for desired operating current.


### ADDITIONNAL INFORMATION ON LED COMPONENTS

- The operating voltage must not be exceeded by more that 10% as this will result in reduced life expectancy
- Luminous intensity is measured at 20 mA on a discrete led unless otherwise stated.
- Luminous intensities and color shades of white LEDs may vary within a batch.
- Luminous intensity will be reduced with lower operating current.
- Recommended usage:
  - Standard: Homogenous light output that is good for indoor applications.
  - Hyper Bright: Homogenous light output that is good for outside viewing and is daylight visible.
  - Super Bright: A water clear LED that is good for long distance viewing and is daylight visible.




# CONNECTIONS

REAR EPOXY WIRES FOR RGB OPTION



# Ø14 mm panel mount LED indicators





# **ABOUT THIS SERIES**

- Notice: please note that not all combinations of above numbers are available.
  - Gold faston terminal denotes anode (+), silver terminal denotes cathode (-)
  - Standard wire length is 200 mm, 22 AWG UL1061, red wire denotes anode (+), black wire denotes cathode (-) for other wire lengths consult APEM
  - For LEDs with alternative voltages and mutlit-voltage options consult APEM
  - 110 VAC and 220 VAC, only available with terminal options 1, 3 and 5
  - Bi-color leds, by connecting the gold faston (+) one color is produced, by reversing the supply voltage another color is produced bi-colors are available up to 28 VDC
  - Take care when soldering to the faston terminals (recommended solder temperature 300 °C 3 sec)

• Body options 2, 4 and 6 are only available without integral resistor (02).

110 VAC

220 VAC

110

220

\* Terminals option 5 and common anode only


- The Tri-color LED has red and green LEDs when both are connected yellow is produced
- Standard tri-color faston terminals are two anodes (+) and one cathode (-)
- Tri-color wires are one red (+) and one green (+) anode and one black (-) cathode
- Tri-color pins are center (-) cathode, shortest (+) anode pin green, longest (+) anode pin red
- We recommend using Hyperbright or Superbright LEDs for use at 110 VAC and 220 VAC

Ø14 mm panel mount LED indicators


# **PROMINENT BEZEL**




### WIRES




### REAR EPOXY WIRES




## SHORT BODY WIRES




### SOLDER LUG/FASTON




### **PINS**



### REAR EPOXY PINS



## SHORT BODY PINS



# APEM


# Q14 series

Ø14 mm panel mount LED indicators


## **FLUSH BEZEL**




### WIRES




### REAR EPOXY WIRES




## SHORT BODY WIRES




### SOLDER LUG/FASTON




### PINS



### **REAR EPOXY PINS**



## SHORT BODY PINS




Ø14 mm panel mount LED indicators


# **RECESSED BEZEL**




### WIRES




### REAR EPOXY WIRES




# SHORT BODY WIRES




### SOLDER LUG/FASTON




### **PINS**



### REAR EPOXY PINS



## SHORT BODY PINS



# Ø14 mm panel mount LED indicators



# **CUSTOM ENGRAVING**

Some common codes are listed above, for your custom requirements please contact APEM. Unless specified standard engraving with white infill will be supplied. Suffix the part number with legend code:















High beam



Rear fog -027

Front fog -026

Windscreen wiper

Windscreen washer -022

Ventilator fan -023















Turn Signal

Side lights

-041

Hazard warning -013 Heating -018

-0BU















-0GP

Windscreen heating

-020

-086

Engine coil -0EL

Seat belt

USB connection -0UB



Steam -0ST



-0EU



Side step -0AD



-012



-040



Boot/Trunk Release -0BR











# CABLE LENGTH AND CONNECTOR







For custom cable length and connectors contact APEM.