PRODUCT DATASHEET CA17723_EMERALD-AP1-PC

EMERALD-AP1-PC

Asymmetric beam for anti-panic lighting. Assembly with installation tape.

SPECIFICATION:

Dimensions Ø 21.6 mm
Height 6.9 mm
Fastening glue, pin
ROHS compliant yes ①



MATERIALS:

ComponentTypeMaterialColourFinishEMERALD-AP1-PCSingle lensPCclearHEIDI-TAPETapeAcrylic foamblack


ORDERING INFORMATION:

» Box size: 480 x 280 x 300 mm

ComponentQty in boxMOQMPQBox weight (kg)CA17723_EMERALD-AP1-PCSingle lens34562881445.6



PRODUCT CA17723_EMERALD-AP1-PC



See also our general installation guide: www.ledil.com/installation_guide


OPTICAL RESULTS (SIMULATED):

CREE \$\text{LED}

LED J Series 5050 Round LES

 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 116.0° / 136.0° Efficiency 91 % Peak intensity 0.4 cd/lm LEDs/each optic Light colour White

Required components:




CREE - LED

XHP35 HD LED FWHM / FWTM Asymmetric Efficiency 91 % Peak intensity 0.3 cd/lm LEDs/each optic 1

White

Required components:


Light colour



CREE \$\(\preceq\) LED

LED XHP35 HI FWHM / FWTM Asymmetric Efficiency 91 % Peak intensity 0.4 cd/lm LEDs/each optic 1

Light colour White Required components:




CREE - LED

XHP35.2 HD FWHM / FWTM 128.0° / 143.0°

Efficiency 84 % Peak intensity 0.3 cd/lm LEDs/each optic White Light colour

Required components:





OPTICAL RESULTS (SIMULATED):

White




LED XP-G3 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ Asymmetric Efficiency 89 %

Peak intensity 0.4 cd/lm LEDs/each optic

Required components:

Light colour




CREE - LED

LED XT-E

FWHM / FWTM 118.0° / 155.0° Efficiency 89 % Peak intensity 0.5 cd/lm

LEDs/each optic 1 White Light colour

Required components:




OSRAM Opto Semiconductor

OSLON Square CSSRM2/CSSRM3 LED

FWHM / FWTM Asymmetric Efficiency 91 % Peak intensity 0.5 cd/lm LEDs/each optic 1 White

Light colour Required components:



Published: 18/01/2021



PRODUCT DATASHEET CA17723_EMERALD-AP1-PC

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Salo, Finland Hong Kong, China

Distribution Partners

5/5

www.ledil.com/ where_to_buy