# MacBook Pro



# Finish



Silver

Space Gray

# Chip



Apple M1 Pro chip

8-core CPU with 6 performance cores and 2 efficiency cores

14-core GPU

16-core Neural Engine

200GB/s memory bandwidth

# Media engine

Hardware-accelerated H.264, HEVC, ProRes, and ProRes RAW

Video decode engine

Video encode engine

ProRes encode and decode engine



Apple M1 Pro chip

10-core CPU with 8 performance cores and 2 efficiency cores

16-core GPU

16-core Neural Engine

200GB/s memory bandwidth

#### Media engine

Hardware-accelerated H.264, HEVC, ProRes, and ProRes RAW

Video decode engine

Video encode engine

ProRes encode and decode engine

#### Configurable to:

M1 Pro with 10-core CPU and 14-core GPU, M1 Pro with 10-core CPU and 16-core GPU, M1 Max with 10-core CPU and 24-core GPU, or M1 Max with 10-core CPU and 32-core GPU

#### Configurable to:

M1 Max with 10-core CPU and 24-core GPU or M1 Max with 10-core CPU and 32-core GPU

# Display

#### Liquid Retina XDR display

14.2-inch (diagonal) Liquid Retina XDR display; 3024-by-1964 native resolution at 254 pixels per inch



# XDR (Extreme Dynamic Range)

Up to 1000 nits sustained (full-screen) brightness, 1600 nits peak brightness 1,000,000:1 contrast ratio

#### Color

1 billion colors Wide color (P3) True Tone technology

#### **Refresh rates**

ProMotion technology for adaptive refresh rates up to 120Hz Fixed refresh rates: 47.95Hz, 48.00Hz, 50.00Hz, 59.94Hz, 60.00Hz

Memory	16GB		
	16GB unified memory		
	Configurable to:		
	32GB (M1 Pro or M1 Max) or 64GB (M1 Max)		
Battery and Power	Up to 17 hours Apple TV app movie playback		
	Up to 11 hours wireless web		
	70-watt-hour lithium-polymer battery		
	67W USB-C Power Adapter (included with M1 Pro with 8-core CPU)		
	96W USB-C Power Adapter (included with M1 Pro with 10-core CPU or M1 Max, configurable with M1 Pro with 8-core CPU)		
	USB-C to MagSafe 3 Cable		
	Fast-charge capable with 96W USB-C Power Adapter		

Storage	<b>512GB</b> 512GB SSD	<b>1TB</b> 1TB SSD
	Configurable to: 1TB, 2TB, 4TB, or 8TB	Configurable to: 2TB, 4TB, or 8TB
Charging and Expansion	SDXC card slot HDMI port 3.5 mm headphone jack	

HDMI port
3.5 mm headphone jack
MagSafe 3 port
Three Thunderbolt 4 (USB-C) ports with support for:
Charging
DisplayPort
Thunderbolt 4 (up to 40Gb/s)
USB 4 (up to 40Gb/s)

	SDXC Thunderbolt 4 HDMI
MagSafe 3 Headphone jack	
Thunderbolt 4	

# **Video Support**

# Simultaneously supports full native resolution on the built-in display at 1 billion colors and:

Up to two external displays with up to 6K resolution at 60Hz at over a billion colors (M1 Pro) or Up to three external displays with up to 6K resolution and one external display with up to 4K resolution at 60Hz at over a billion colors (M1 Max)

#### Thunderbolt 4 digital video output

Native DisplayPort output over USB-C

VGA, HDMI, DVI, and Thunderbolt 2 output supported using adapters (sold separately)

#### HDMI digital video output

Support for one display with up to 4K resolution at 60Hz

DVI output using HDMI to DVI Adapter (sold separately)

# Keyboard and<br/>TrackpadBacklit Magic Keyboard with:<br/>78 (U.S.) or 79 (ISO) keys including 12 full-height function keys and 4 arrow keys<br/>in an inverted-T arrangementTouch IDAmbient light sensorForce Touch trackpad for precise cursor control and pressure-sensing<br/>capabilities; enables Force clicks, accelerators, pressure-sensitive drawing, and<br/>Multi-Touch gestures



Force Touch trackpad

Wireless	Wi-Fi
	802.11ax Wi-Fi 6 wireless networking IEEE 802.11a/b/g/n/ac compatible
	Bluetooth
	Bluetooth 5.0 wireless technology
Camera	1080p FaceTime HD camera Advanced image signal processor with computational video
0	
Audio	High-fidelity six-speaker sound system with force-cancelling woofers Wide stereo sound
	Support for spatial audio when playing music or video with Dolby Atmos on built-in speakers
	Spatial audio with dynamic head tracking when using AirPods (3rd generation), AirPods Pro, and AirPods Max
	Studio-quality three-mic array with high signal-to-noise ratio and directional beamforming
	3.5 mm headphone jack with advanced support for high-impedance headphones

 Operating
 Line voltage: 100V to 240V AC

 Requirements
 Frequency: 50Hz to 60Hz

 Operating temperature: 50° to 95° F (10° to 35° C)

Storage temperature: -13° to 113° F (-25° to 45° C) Relative humidity: 0% to 90% noncondensing Operating altitude: tested up to 10,000 feet Maximum storage altitude: 15,000 feet Maximum shipping altitude: 35,000 feet

# Size and Weight

Height 0.61 inch (1.55 cm) Width: 12.31 inches (31.26 cm) Depth: 8.71 inches (22.12 cm) Weight: 3.5 pounds (1.6 kg)



# Operating System

# macOS

macOS is the most advanced desktop operating system in the world. macOS Monterey introduces powerful new features to help you connect, share, and create like never before.

# Accessibility

Accessibility features help people with disabilities get the most out of their new MacBook Pro. With built-in support for vision, hearing, mobility, and learning, you can create and do amazing things.

# Features include:

Voice Control	Increase Contrast	Switch Control
VoiceOver	Reduce Motion	Closed Captions
Zoom	Siri and Dictation	Text to Speech

# In the Box

14-inch MacBook Pro

67W USB-C Power Adapter (M1 Pro with 8-core CPU) or 96W USB-C Power Adapter (M1 Pro with 10-core CPU or M1 Max)

USB-C to MagSafe 3 Cable (2 m)





