
iPhone 12 mini

iPhone 12



Weight: 4.76 ounces (135 grams)

Weight: 5.78 ounces (164 grams)

Display



Super Retina XDR display 5.4-inch (diagonal) all-screen OLED display 2340-by-1080-pixel resolution at 476 ppi

The iPhone 12 mini display has rounded corners that follow a beautiful curved design, and these corners are within a standard rectangle. When measured as a 5.42 inches diagonally (actual viewable area is less).



Super Retina XDR display 6.1-inch (diagonal) all-screen OLED display 2532-by-1170-pixel resolution at 460 ppi

The iPhone 12 display has rounded corners that follow a beautiful curved design, and these corners are within a standard rectangle. When measured as a standard rectangular shape, the screen is 6.06 inches diagonally (actual viewable area is less).

standard rectangular shape, the screen is

Both models:

HDR display True Tone Wide color (P3) Haptic Touch 2,000,000:1 contrast ratio (typical) 625 nits max brightness (typical); 1200 nits max brightness (HDR) Fingerprint-resistant oleophobic coating Support for display of multiple languages and characters simultaneously

Splash, Water, and **Dust Resistant**

Rated IP68 (maximum depth of 6 meters up to 30 minutes) under IEC standard 60529

Chip



A14 Bionic chip Next-generation Neural Engine

Camera

- Dual 12MP camera system: Ultra Wide and Wide cameras Ultra Wide: £/2.4 aperture and 120° field of view Wide: *f*/1.6 aperture 2x optical zoom out Digital zoom up to 5x Portrait mode with advanced bokeh and Depth Control Portrait Lighting with six effects (Natural, Studio, Contour, Stage, Stage Mono, High-Key Mono) Optical image stabilization (Wide) Five-element lens (Ultra Wide); seven-element lens (Wide) Brighter True Tone flash with Slow Sync Panorama (up to 63MP) Sapphire crystal lens cover 100% Focus Pixels (Wide) Night mode (Ultra Wide, Wide) Deep Fusion (Ultra Wide, Wide) Smart HDR 3 with Scene Detection Wide color capture for photos and Live Photos Lens correction (Ultra Wide) Advanced red-eye correction Auto image stabilization Burst mode Photo geotagging
- Image formats captured: HEIF and JPEG

Video Recording

HDR video recording with Dolby Vision up to 30 fps 4K video recording at 24 fps, 30 fps, or 60 fps 1080p HD video recording at 30 fps or 60 fps 720p HD video recording at 30 fps Optical image stabilization for video (Wide) 2x optical zoom out Digital zoom up to 3x Audio zoom Brighter True Tone flash QuickTake video Slo-mo video support for 1080p at 120 fps or 240 fps Time-lapse video with stabilization Night mode Time-lapse Extended dynamic range for video up to 60 fps Cinematic video stabilization (4K, 1080p, and 720p) Continuous autofocus video

Take 8MP still photos while recording 4K video Playback zoom Video formats recorded: HEVC and H.264 Stereo recording

TrueDepth Camera

12MP camera

£/2.2 aperture Portrait mode with advanced bokeh and Depth Control Portrait Lighting with six effects (Natural, Studio, Contour, Stage, Stage Mono, High-Key Mono) Animoji and Memoji Night mode Deep Fusion Smart HDR 3 with Scene Detection HDR video recording with Dolby Vision up to 30 fps 4K video recording at 24 fps, 30 fps, or 60 fps 1080p HD video recording at 30 fps or 60 fps Slo-mo video support for 1080p at 120 fps Time-lapse video with stabilization Night mode Time-lapse Extended dynamic range for video up to 30 fps Cinematic video stabilization (4K, 1080p, and 720p) QuickTake video Wide color capture for photos and Live Photos Lens correction Retina Flash Auto image stabilization Burst mode

Face ID	Enabled by TrueDepth camera for facial recognition
Apple Pay	Pay with your iPhone using Face ID in stores, within apps, and on the web Send and receive money in Messages
	Complete purchases made with Apple Pay on your Mac
	Pay for your ride using Express Transit

Apple Card

Credit card created by Apple, designed for iPhone Use the Wallet app to apply for, manage, and use Apple Card Pay with Apple Pay using Face ID in stores, within apps, and on the web Titanium, laser-etched physical credit card for use where Apple Pay is not accepted yet


Cellular and Wireless	Model A2172	5G NR (Bands n1, n2, n3, n5, n7, n8, n12, n20, n25, n28, n38, n40, n41, n66, n71, n77, n78, n79)
		5G NR mmWave (Bands n260, n261)
		FDD-LTE (Bands 1, 2, 3, 4, 5, 7, 8, 12, 13, 14, 17, 18, 19, 20, 25, 26, 28, 29, 30, 32, 66, 71)
		TD-LTE (Bands 34, 38, 39, 40, 41, 42, 46, 48)
		CDMA EV-DO Rev. A (800, 1900 MHz)
		UMTS/HSPA+/DC-HSDPA (850, 900, 1700/2100, 1900, 2100 MHz)
		GSM/EDGE (850, 900, 1800, 1900 MHz)
	Model A2176	5G NR (Bands n1, n2, n3, n5, n7, n8, n12, n20, n25, n28, n38, n40, n41, n66, n71, n77, n78, n79)
		5G NR mmWave (Bands n260, n261)
		FDD-LTE (Bands 1, 2, 3, 4, 5, 7, 8, 12, 13, 14, 17, 18, 19, 20, 25, 26, 28, 29, 30, 32, 66, 71)
		TD-LTE (Bands 34, 38, 39, 40, 41, 42, 46, 48)
		CDMA EV-DO Rev. A (800, 1900 MHz)
		UMTS/HSPA+/DC-HSDPA (850, 900, 1700/2100, 1900, 2100 MHz)
		GSM/EDGE (850, 900, 1800, 1900 MHz)
	All models	5G (sub-6 GHz and mmWave)
		Gigabit LTE with 4x4 MIMO and LAA
		Wi-Fi 6 (802.11ax) with 2x2 MIMO
		Bluetooth 5.0 wireless technology
		Ultra Wideband chip for spatial awareness
		NFC with reader mode
		Express Cards with power reserve

Location

Built-in GPS, GLONASS, Galileo, QZSS, and BeiDou Digital compass Wi-Fi Cellular iBeacon microlocation

Video Calling	FaceTime video calling over cellular or Wi-Fi FaceTime HD (1080p) video calling over 5G or Wi-Fi
Audio Calling	FaceTime audio Voice over LTE (VoLTE) Wi-Fi calling
Audio Playback	Audio formats supported: AAC-LC, HE-AAC, HE-AAC v2, Protected AAC, MP3, Linear PCM, Apple Lossless, FLAC, Dolby Digital (AC-3), Dolby Digital Plus (E-AC-3), Dolby Atmos, and Audible (formats 2, 3, 4, Audible Enhanced Audio, AAX, and AAX+) Spatial audio playback User-configurable maximum volume limit
Video Playback	Video formats supported: HEVC, H.264, MPEG-4 Part 2, and Motion JPEG HDR with Dolby Vision, HDR10, and HLG Up to 4K HDR AirPlay for mirroring, photos, and video out to Apple TV (2nd generation or later) or AirPlay 2–enabled smart TV Video mirroring and video out support: Up to 1080p through Lightning Digital AV Adapter and Lightning to VGA Adapter (adapters sold separately)
Siri	Use your voice to send messages, set reminders, and more Get intelligent suggestions on your Lock Screen and in Messages, Mail, QuickType, and more Activate hands-free with only your voice using "Hey Siri" Use your voice to run shortcuts from your favorite apps

External Buttons and Connectors



Power and Battery

Video playback: Up to 15 hours

Video playback (streamed): Up to 10 hours

Audio playback: Up to 50 hours

Both models:

Built-in rechargeable lithium-ion battery

MagSafe wireless charging up to 15W

Qi wireless charging up to 7.5W

Charging via USB to computer system or power adapter

Fast-charge capable: Up to 50% charge in 30 minutes with 20W adapter or higher (sold separately)

MagSafe

Wireless charging up to 15W Magnet array Alignment magnet Accessory Identification NFC Magnetometer Video playback: Up to 17 hours

Video playback (streamed): Up to 11 hours

Audio playback: Up to 65 hours

Sensors

Face ID Barometer Three-axis gyro Accelerometer Proximity sensor Ambient light sensor

Operating System

iOS 14

iOS is the world's most personal and secure mobile operating system, packed with powerful features and designed to protect your privacy.

Accessibility

Accessibility features help people with disabilities get the most out of their new iPhone. With built-in support for vision, hearing, mobility, and learning, you can fully enjoy the world's most personal device.

Features include:

Dual SIM (nano-SIM and eSIM)

- Voice Control
- VoiceOver
- Zoom
- Magnifier

- RTT and TTY support
- Siri and Dictation
- Type to Siri
- Switch Control
- Closed Captions
- AssistiveTouch
- Speak Screen
- Back Tap

SIM Card

iPhone 12 and iPhone 12 mini are not compatible with existing micro-SIM cards.

Rating for Hearing Aids

M3, T4

System Requirements	Apple ID (required for some features) Internet access Syncing to a Mac or PC requires: • macOS Catalina 10.15 or later using the Finder
	 macOS El Capitan 10.11.6 through macOS Mojave 10.14.6 using iTunes 12.8 or later Windows 7 or later using iTunes 12.10.10 or later
Environmental	Operating ambient temperature: 32° to 95° F (0° to 35° C)
Requirements	Nonoperating temperature: -4° to 113° F (-20° to 45° C)
	Relative humidity: 5% to 95% noncondensing
	Operating altitude: tested up to 10,000 feet (3000 m)

In the Box

iPhone with iOS 14 USB-C to Lightning Cable Documentation