Product data sheet Characteristics

CA3KN22BD3

TeSys K control relay - 2 NO + 2 NC - <= 690 V -24 V DC standard coil





Main

IVIAIII		
Range of product	TeSys K control relay	
Range	TeSys	
Product name	TeSys CAK	
Product or component type	Control relay	
Device short name	САЗК	
Contactor application	Control circuit	
Utilisation category	DC-13 AC-15	
Pole contact composition	2 NO + 2 NC	
[Ue] rated operational voltage	<= 690 V <= 400 Hz	
Control circuit type	DC standard	
[Uc] control circuit voltage	24 V DC	

Complementary

Main		
Range of product	TeSys K control relay	-
Range	TeSys	_
Product name	TeSys CAK	-
Product or component type	Control relay	_
Device short name	САЗК	_
Contactor application	Control circuit	
Utilisation category	DC-13 AC-15	- 100 C
Pole contact composition	2 NO + 2 NC	
[Ue] rated operational voltage	<= 690 V <= 400 Hz	_
Control circuit type	DC standard	_
[Uc] control circuit voltage	24 V DC	_
Complementary Coil technology [Ith] conventional free air thermal current	Built-in bidirectional peak limiting diode suppressor 10 A at <= 50 °C	
Irms rated making capacity	110 A conforming to IEC 60947	—
Associated fuse rating	10 A gG conforming to IEC 60947 10 A gG conforming to VDE 0660	
[Ui] rated insulation voltage	600 V conforming to CSA C22.2 No 14 690 V conforming to BS 5424 690 V conforming to IEC 60947 750 V conforming to VDE 0110 group C	
Mounting support	Rail Plate	
Connections - terminals	Screw clamp terminals 1 cable(s) 1.54 mm ² - cable stiffness: solid Screw clamp terminals 2 cable(s) 1.54 mm ² - cable stiffness: solid Screw clamp terminals 2 cable(s) 0.754 mm ² - cable stiffness: flexible - without cable end Screw clamp terminals 1 cable(s) 0.754 mm ² - cable stiffness: flexible - with cable end Screw clamp terminals 1 cable(s) 0.341.5 mm ² - cable stiffness: flexible - with cable end	



	Screw clamp terminals 2 cable(s) 0.341.5 mm ² - cable stiffness: flexible - without cable end
Tightening torque	1.3 N.m - on screw clamp terminals - with screwdriver Philips No 2 6 mm 1.3 N.m - on screw clamp terminals - with screwdriver flat $Ø$ 6 mm
Control circuit voltage limits	0.81.15 Uc at 50 °C operational 0.10.75 Uc at 50 °C drop-out
Operating time	10 ms coil de-energisation and NO opening 15 ms coil de-energisation and NC closing 2535 ms coil energisation and NC opening 3040 ms coil energisation and NO closing
Mechanical durability	20 Mcycles
Operating rate	10000 cyc/h
Immunity to microbreaks	2 ms
Inrush power in W	3 W at 20 °C
Hold-in power consumption in W	3 W at 20 °C
Heat dissipation	3 W
Minimum switching voltage	17 V
Minimum switching current	5 mA
Non overlap distance	0.5 mm
Insulation resistance	> 10 MOhm
Height	58 mm
Width	45 mm
Depth	57 mm
Product weight	0.225 kg
Compatibility code	САЗК

Environment

Standards	BS 5424	
	IEC 60947	
	VDE 0660	
	NF C 63-140	
Product certifications	CSA	
	UL	
IP degree of protection	IP2x	
Protective treatment	TC conforming to IEC 60068	
Ambient air temperature for operation	-2550 °C	
Ambient air temperature for storage	-5080 °C	
Operating altitude	2000 m without derating in temperature	
Flame retardance	V1 conforming to UL 94	
	Requirement 2 conforming to NF F 16-101	
	Requirement 2 conforming to NF F 16-102	
Mechanical robustness	Vibrations contactor closed 4 Gn, 5300 Hz IEC 60068-2-6	
	Vibrations contactor open 2 Gn, 5300 Hz IEC 60068-2-6	
	Shocks contactor open 10 Gn for 11 ms IEC 60068-2-27	
	Shocks contactor closed 15 Gn for 11 ms IEC 60068-2-27	

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0825 - Schneider Electric declaration of conformity
	Schneider Electric declaration of conformity
REACh	Reference not containing SVHC above the threshold
	Reference not containing SVHC above the threshold
Product environmental profile	Available
	Product environmental
Product end of life instructions	Available
	End of life manual

Contractual warranty	
Warranty period	18 months