

**BRADY B-7593 DURABLE POLYESTER NAMEPLATE**

TDS No. B-7593  
Effective Date: 17/05/2021

**Description:**

**GENERAL**

**Print Technology:** Thermal transfer

**Material Type:** Polyester

**Finish:** Gloss

**Colors:** White, yellow, green, red, silver and black

**Adhesive:** Permanent acrylic, foam backed

**APPLICATIONS**

B-7593 durable polyester nameplate labels are designed for patch panel identification in identifying external push-buttons, switches and internal connection points. B-7593 is also used as rating and serial plates using alphanumeric characters that require name plate quality

**RECOMMENDED RIBBONS**

Brady Series R6000 Halogen Free

Brady Series R4400 (colors red, blue, green and white)

**REGULATORY APPROVALS**

For information on the Weee-RoHS compliance status for a Brady Product go to one of the following websites:

In Canada: [www.bradycanada.ca/weee-rohs](http://www.bradycanada.ca/weee-rohs)

In Europe: [www.bradyeurope.com/rohs](http://www.bradyeurope.com/rohs)

In Japan: [www.brady.co.jp/products/labelsuse/rohs](http://www.brady.co.jp/products/labelsuse/rohs)

All other regions: [www.bradyid.com/weee-rohs](http://www.bradyid.com/weee-rohs)

**Details:**

PHYSICAL PROPERTIES	TEST METHODS	AVERAGE RESULTS
Thickness	ASTM D 1000 - Substrate - Foam tape - Total (excluding liner)	0.200 mm (0.0079 inch) 0.450 mm (0.0177 inch) 0.650 mm (0.0256 inch)
Adhesion to:	ASTM D 1000	
- Stainless Steel	20 minutes dwell 24 hour dwell	107 N/100 mm (98 oz/inch) 200 N/100 mm (183 oz/inch)
- Smooth ABS	20 minutes dwell 24 hour dwell	83 N/100mm (76 oz/inch) 112 N/100 mm (102 oz/inch)
- Powdercoated surface	20 minutes dwell 24 hour dwell	120 N/100mm (109 oz/inch) 182 N/100 mm (166 oz/inch)
- Polyethylene	20 minutes dwell 24 hour dwell	34 N/100mm ( 24 oz/inch) 36 N/100 mm (31 oz/inch)
Drop Shear	PSTC-7 (except use 1/2" x 1" sample)	35 hours
Tack	ASTM D2979 Polyken™ Probe Tack ( 1 s dwell, 1 cm/s separation )	468 g

PERFORMANCE PROPERTIES	TEST METHODS	TYPICAL RESULTS White B-7593/R6000 Halogen Free	TYPICAL RESULTS Black B-7593/R4410W	TYPICAL RESULTS Silver B-7593/R6000 Halogen Free
High Service Temperature	1000 hours at 100°C (212°F)	No visual effect	No visual effect	No visual effect
Low Service	1000 hours at -40°C	No visual effect	No visual effect	No visual effect

Temperature	(-40°F)			
Humidity Resistance	1000 hours at 37°C (100°F), 95% R.H.	No visual effect	No visual effect	No visual effect
UV Light Resistance	1000 hours in Q-Sun Xe-1 test chamber	No visual effect	No visual effect	No visual effect
Weatherability	1000 hours in QUV (ASTM G-53)	No visual effect	No visual effect	No visual effect
Abrasion Resistance	Method 5306 US Federal test 191A CS 10 + 500 g/arm	Number of cycles until print is illegible 175 cycles	Number of cycles until print is illegible 75 cycles	Numbers of cycles until print is illegible 175 cycles

<b>PERFORMANCE PROPERTY</b>	<b>CHEMICAL RESISTANCE</b>
-----------------------------	----------------------------

Samples were printed with the Brady Series R6000 Halogen Free ribbon and dwelled 24 hours prior to test. Testing consisted of 5 cycles of 10 minute immersions in the specified chemical reagent followed by 30 minute recovery periods. After final immersion, samples rubbed 10 times with cotton swab saturated with test fluid.

<b>White B-7593 / R6000 Halogen Free</b>		
<b>CHEMICAL REAGENT</b>	<b>APPEARANCE OF THE PRINTING BEFORE RUBBING</b>	<b>APPEARANCE OF THE PRINTING AFTER RUBBING</b>
Isopropyl alcohol	1	1
Methyl ethyl ketone	5	5
Alcohol Mix*	1	2
Gasoline	1	5
Diesel	1	1
Skydrol® 500B-4	1	5
Mil 5606 Oil	1	1
5% sodium hydroxide	1	1
10% Sulphuric Acid Solution	1	1
Deionized Water	1	1
10% Salt Water Solution	1	1
n-hexane	1	1
Iso-octane	1	1
Ethanol	1	1
ASTM#3 oil	1	1
Acetone	1	5

\* Alcohol Mix is 50% ethanol, 30% methanol, and 20% water by volume.

Samples printed with the Brady Series R4400 white ribbon and dwelled 24 hours prior to test. Testing consisted of 5 cycles of 10 minute immersions in the specified chemical reagent followed by 30 minute recovery periods. After final immersion, samples rubbed 10 times with cotton swab saturated with test fluid.

<b>Black B-7593 / R4400W</b>		
<b>CHEMICAL REAGENT</b>	<b>APPEARANCE OF THE PRINTING BEFORE RUBBING</b>	<b>APPEARANCE OF THE PRINTING AFTER RUBBING</b>
Isopropyl alcohol	1	5
Methyl ethyl ketone	NP	NP
Alcohol Mix*	1	1
Gasoline	1	5
Diesel	1	1
Skydrol® 500B-4	NP	NP
Mil 5606 Oil	1	1
5% sodium hydroxide	1	1
10% Sulphuric Acid Solution	1	1
Deionized Water	1	1
10% Salt Water Solution	1	1
n-hexane	1	1
Iso-octane	1	1
Ethanol	1	4
ASTM#3 oil	1	4
Acetone	NP	NP

\* Alcohol Mix is 50% ethanol, 30% methanol, and 20% water by volume.

**Rating Scale:**

- 1 = no visible effect
- 2 = slight smear or print removal, detectable but minimal smear
- 3 = moderate smear or print removal (print still legible)
- 4 = severe smear or print removal (print legible or just barely legible)
- 5 = complete print and/or topcoat removal
- NP = print removed prior to rub

**Shelf Life:**

Shelf life is two years from the date of receipt for this product as long as this product is stored in its original packaging in an environment below 80° F (27° C) and 60% RH. It remains the responsibility of the user to assess the risk of using this product. We encourage customers to develop testing protocols that will qualify a product's fitness for use in their actual application.

**Trademarks:**

ASTM: American Society for Testing and Materials (U.S.A.)  
Polyken™ is a trademark of Testing Machines Inc.  
S. I.: International System of Units  
Skydrol® is a registered trademark of the Monsanto Company

**Note:** All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

**WARRANTY**

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2021 W.H. Brady, N.V. | All Rights Reserved  
Material may not be reproduced or distributed in any form without written permission.

---

Brady Europe | Industriepark C3 Lindestraat 20 | B9240 Zele | Belgium | Tel: +32 52.45.7811 | Fax: +32 52.45.7812