


PRODUCT DATA SHEET

PL10SL Series (Bi-colour 3 wire)
Ø10mm stainless steel panel lights

Product Configuration





Example Part Number

PL10SL083

Panel indicator 10mm diameter, stainless steel bezel, lead wire terminated, flat lens, Red/Green + Com, 24V.

Outline Dimensions (mm) - Not to scale



Colour	Typ. Wave length (Nm)	Typ. Colour Temp (K)	Viewing Angle (°)		Typ. Luminous Intensity (mcd)	
			Rnd	Flat	Rnd	Flat
Red	625	N/A	140	140	1000	600
Green	520	N/A	140	140	2200	1300

Notes:

- | | | |
|----|----------------------------|--|
| 1 | Optical Data | Applies to component LED @ 25°C, 20mA |
| 2 | Body Material | Bezel - Stainless Steel 304, Housing – PA6 |
| 3 | Wire Gauge | 24 AWG |
| 4 | LED Life (Average) | 50000 Hrs |
| 5 | Operating Current | AC/DC |
| 6 | Current Rating | ≤ 20mA |
| 7 | Protection | IP67 |
| 8 | Environmental | RoHS & REACH SVHC compliant |
| 9 | Marking | Voltage, colour, CE/UKCA (110V, 240V only) |
| 10 | Operating Temp | -25°C~+65°C |
| 11 | Max Panel Thickness | Advised 5mm, Absolute 6.5mm. |