



CP2E-E14DR-A

CP2E series compact PLC - Essential Type; 8 DI, 6DO; Relay output; Power supply 220 VAC; 4 kStep Program memory

Specifications

Supply voltage type	AC
Input type	PNP/NPN
Number of digital inputs	8
Output type	Relay
Number of digital outputs	6
Program capacity	8 K steps
Data memory capacity	4 K words
Logic execution time	0.23 μ s
Communication port(s)	Serial RS-232C, USB
Number of Ethernet ports	0
Number of USB ports	1
Number of RS-232 ports	1
Number of RS-485 ports	0
Communication option(s)	None
Number of encoder input channels	6
Max. encoder input frequency	100 kHz
Max. number of PTP axes	0
Max. pulse output frequency	0 kHz
Function Block programming	✓
Battery-free memory backup	✓
Real-time clock	✗
Analogue option boards	✗
Max. number of analogue I/O channels	0

Max. number of local I/O points	14
Max. number of expansion units	0
Built-in auxiliary 24 VDC output	0 mA
Operating temperature range	-20-60 °C
Product Height (unpacked)	90 mm
Product Width (unpacked)	86 mm
Product Depth (unpacked)	80 mm

Accessories



CP1W-CN221

USB Programming cable, A-type male to B-type male, 1.8 m




CXONE-LT01-EV4

CX-One Lite v4.x software, for Windows 2000/XP/Vista, single-user licence only, (requires CDs, CXOne-LTCD-EV4), limited to program the CPx PLC platform

Downloads

CAD Library



CP1E/CP2E CPU Unit Instructions

Reference Manual

EN PDF 9.96 MB



CP2E

Brochure


EN PDF 2.44 MB



CP2E

Datasheet

EN PDF 8.66 MB



CP2E Hardware Users Manual

EN PDF 24.5 MB



CP2E Software Users Manual

EN PDF 36 MB



NB Faceplate 3.0 - Multilanguage Software

EN ZIP 79.7 MB

