

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Cordless Combi

GSB 18V-90 C



Powerful cordless impact drill with compact head length and perfect tool control

The most important data

Torque (soft/hard/max.)	36/64/- Nm
No-load speed (1st gear / 2nd gear)	0 – 630 / 0 – 2,100 rpm
Max. screw diameter	12 mm

Part Number 0 601 9K6 102[> More product information](#)

Technical data

Technical data

Torque (soft/hard/max.)	36/64/- Nm
No-load speed (1st gear / 2nd gear)	0 – 630 / 0 – 2,100 rpm
Chuck capacity, min./max.	1.5 / 13 mm
Battery voltage	18.0 V
Weight excl. battery	1.2 kg
Torque settings	21
Packaging dimensions (width x length x height)	357 x 442 x 151 mm

Drilling diameter

Max. drilling diameter in wood	68 mm
Max. drilling diameter in steel	13 mm

Screw diameter

Max. screw diameter	12 mm
---------------------	-------

Noise/vibration information

Drilling in metal

Vibration emission value ah	1.5 m/s ²
Uncertainty K	1.2 m/s ²

Impact drilling in masonry

Vibration emission value ah	11.8 m/s ²
Uncertainty K	1.5 m/s ²



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Powerful brushless motor delivers high power with 64 Nm and 2,100 rpm maximising your efficiency on the job site
- 13-mm metal chuck ensures increased robustness and great torque transfer for every job
- Switchable Kickback Control and switchable Precision Clutch ensure perfect control and high protection for user and tool

