

Enameled copper wire  
**CUL 100/1,12**



Picture shows CUL 100/0,22

## Advantages

Insulating varnish basis min, polyurethane, mod.

Grade 1, TJ min. 302 °F / 155 °C

Solderable

## Applications

Enameled copper wire for the production of coils and windings and for general laboratory needs. Please consider the relevant standards.

## Approvals



## Enameled copper wire **CUL 100/1,12**

Type

CUL 100/1,12

Type

CUL 100/1,12



Electrical data



Mechanical data

### Operating data

Current rating 3.5 A

### Environment

Heat resistance 311 °F (CLF)

Insulating varnish min. Polyurethan, mod.

Tin-plate >662 °F

### Measures and weights

Length m (min.) 9

Wire diameter 0.044 inch

Weight 0.22 lbs

Subject to change.