

Enameled copper wire  
**CUL 50/0,08**



Picture shows CUL 100/0,22

## Advantages

Insulating varnish basis min. polyurethane, mod.

Grade 1, TJ min. 302 °F / 155 °C

Solderable

## Applications

Enameled copper wire for the production of coils and windings and for general laboratory needs. Please consider the relevant standards.

## Approvals



## Enameled copper wire **CUL 50/0,08**

Type

CUL 50/0,08

Type

CUL 50/0,08



Electrical data



Mechanical data

Operating data

Current rating 0.02 A

Environment

Heat resistance 311 °F (CLF)

Insulating varnish min. Polyurethan, mod.

Tin-plate >662 °F

Measures and weights

Length m (min.) 856

Wire diameter 0.003 inch

Weight 0.11 lbs

Subject to change.