

Desktop & Instrument Cases

8000 Series Euro Desk Cases


ABS desktop cases with removable base plates for ease of access and flush fitting aluminium front panels.

- Moulded in high impact ABS
- Aluminium lid mounted by 4x M3 screws
- Removable base plate for ease of access and fast assembly
- Gloss finish for ease of cleaning
- Integral side PCB slots in enclosure body
- PCB pillars in base


SPECIFICATION


Materials	Body and base plate high impact ABS as standard UL-94 V0 ABS to order Panel 1mm thick aluminium
Operating temperature	Resistant to temperatures up to 85°C
Protection class	IP40
Standard colours	Body & base plate grey & black as standard, white to order Aluminium panel grey
Standard unit includes	Body & base plate Aluminium panel 8/10x M3 fixing screws 4x rubber feet

BLACK	GREY	LENGTH	WIDTH	HEIGHT
BIM8005-BLK/PG	BIM8005-GY/PG	127mm	170mm	70mm
BIM8007-BLK/PG	BIM8007-GY/PG	187mm	243mm	103mm



desktop &
instrument
cases



UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS		DO NOT SCALE DRAWING		REVISION. O	
		TITLE: ASSEMBLY DRG FOR 8005			
FINISH. SMOOTH		DWG NO. 8005 A4			
MATERIAL. VAR					
PROJECTION. 		SCALE. 1 : 3		SHEET 1 OF 1	


A4

OVERALL ASSEMBLY DIMENSIONS:







SECTION A-A

EXT - 242.50 x 187 x 103 max/ 65 min

INT - 235.70 x 180.20 x 95 max/ 60 min




ISO VIEW
1:8



BODY

BASE

LID



UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETERS

DO NOT SCALE DRAWING

REVISION. O

FINISH.

SMOOTH

TITLE:

ASSEMBLY DWG FOR 8007

DRAWN	NAME	SIGNED	DATE
CHK'D	SUBKHANKULOVA	LS	13/05/09

MATERIAL.

VAR

DWG NO.

8007

A4

PROJECTION.

SCALE. 1 : 5

SHEET 1 OF 1