ELLA-30-M

~28° wide beam

**SPECIFICATION:** 

**Dimensions** 

Height

ROHS compliant

Ø 29.6 mm

17.2 mm

yes 🕕



Component

ELLA-30-M

Type

Material

Reflector HTPC

**Colour** metal

LEDiL

**Finish** 

Coating

HMDS

### **ORDERING INFORMATION:**

Component

C17247\_ELLA-30-M

» Box size: 480 x 280 x 300 mm


Qty in box MOQ MPQ Box weight (kg)

1320 264 88 4.4

Published: 13/12/2019



# PRODUCT DATASHEET C17247\_ELLA-30-M



See also our general installation guide: www.ledil.com/installation\_guide

2/7






LED V4 HD Gen 7 FWHM / FWTM 28.0° / 63.0°

Efficiency 94 %
Peak intensity 2.8 cd/lm

LEDs/each optic 1
Light colour White

Required components:




#### bridgelux

LED V6 HD Gen 7 FWHM / FWTM 28.0° / 64.0°

Efficiency 93 %
Peak intensity 2.8 cd/lm
LEDs/each optic 1

White

Required components:



#### bridgelux


Light colour

LED V8 Gen7
FWHM / FWTM 29.0° / 62.0°

Efficiency 92 %
Peak intensity 2.8 cd/lm

LEDs/each optic 1
Light colour White

Required components:




# **CITIZEN**

LED CLU7A2/7A3 FWHM / FWTM 18.0° / 36.0°

Efficiency 89 %
Peak intensity 5.6 cd/lm
LEDs/each optic 1

Light colour White Required components:



Published: 13/12/2019



# **CITIZEN**

LED CLU7B2

FWHM / FWTM 16.0° / 34.0°


Efficiency 90 %

Peak intensity 6.3 cd/lm

LEDs/each optic 1

Light colour White

Required components:



### CREE \$\(\phi\) LED

LED CMA1303

FWHM / FWTM 20.0° / 40.0°


Efficiency 90 %

Peak intensity 5 cd/lm

LEDs/each optic 1

Light colour White

Required components:



### CREE + LED

LED CXA/B 13xx


FWHM / FWTM 26.0° / 54.0°

Efficiency 89 %

Peak intensity 3.4 cd/lm LEDs/each optic 1

Light colour White

Required components:



### CREE - LED


LED CXA/B 15xx

FWHM / FWTM 33.0° / 64.0°

Efficiency 86 %
Peak intensity 2.2 cd/lm

LEDs/each optic 1

Light colour White Required components:




4/7



## CREE . LED

Required components:


LED XHP35.2 HD  $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 19.0° / 38.0° Efficiency 83 % Peak intensity 4.9 cd/lm LEDs/each optic Light colour White



### **ELUMINUS**

LED CXM-3 FWHM / FWTM 16.0° / 34.0° Efficiency 90 % Peak intensity 6.3 cd/lm LEDs/each optic 1 White Light colour


Required components:



### **WNICHIA**

LED NFMW48xA FWHM / FWTM 28.6° / 59.0° Efficiency 95 % Peak intensity 3 cd/lm LEDs/each optic Light colour White


Required components:



# **TRIDONIC**

SLE SNC8 LES06 FWHM / FWTM 24.0° / 54.0° Efficiency 88 % Peak intensity 3.4 cd/lm LEDs/each optic White Light colour

Required components:



Published: 13/12/2019




White

# **XICATO**

LED XOB 6 mm
FWHM / FWTM 24.0° / 53.0°
Efficiency 90 %
Peak intensity 3.5 cd/lm
LEDs/each optic 1

Required components:


Light colour



# **XICATO**

LED XOB 9.8 mm
FWHM / FWTM 34.0° / 66.0°
Efficiency 88 %
Peak intensity 2.2 cd/lm
LEDs/each optic 1
Light colour White

Required components:





# PRODUCT DATASHEET C17247\_ELLA-30-M

#### **GENERAL INFORMATION:**

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

### **MATERIALS:**

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

#### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

### **LEDIL Oy**

Joensuunkatu 13 FI-24240 SALO Finland

#### LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

# Ledil Optics Technology (Shenzhen) Co., Ltd.

# 405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

# Local sales and technical support

www.ledil.com/ where\_to\_buy

#### **Shipping locations**

Salo, Finland Hong Kong, China

#### **Distribution Partners**

www.ledil.com/ where\_to\_buy