Energy Management Energy Meter Type EM330





- Easy connection or wrong current direction detection
- Certified according to MID Directive (option PF only): see "how to order" below
- Compliant with the international accuracy standard IEC/EN62053-21, and the IEC/EN61557-12 performance requirements (active power and active energy).
- Other versions available (not certified, option X): see "how to order" on the next page

- Three phase energy meter
- · Class 1 (kWh) according to EN62053-21
- Class B (kWh) according to EN50470-3
- Accuracy ±0.5% RDG (current/voltage)
- Current measurement via CT
- Backlit LCD display (3x 8-digit) with integrated touch key-pad
- · Energy readout on display: 8 digit
- · Variable readout on display: 4 digit
- Energy measurement: kWh and kvarh (imported/ exported); kWh+ by 2 tariffs; kWh per phase
- System variables: kW, kvar, kVA, VLL, VLN, PF, Hz, kWdmd, kWdmd peak
- Phase variables: kW, kvar, kVA, VLL, VLN, A, PF
- Auxiliary power supply
- Dimensions: 3-DIN module
- Protection degree (front): IP51
- Pulse output (optional, by open collector PNP)
- RS485 Modbus port (optional)
- M-Bus port (optional)
- Run hour meter
- Neutral current calculation
- · Digital input (for tariff management)

Product description

Three-phase energy meter with backlit LCD display with integrated touch keypad. Particularly indicated for active energy metering and for cost

allocation (CT connection), with dual tariff management availability. It can measure imported and exported energy or be programmed to consider only the imported one. Housing for DIN-rail mounting, with IP51 front degree protection. The meter is optionally provided with pulse output proportional to the active energy being measured, RS485 Modbus port or M-Bus port. Available for legal metrology (PF option, only for imported energy).

Certified according to MID Directive, Module B and Module D of Annex II, for legal metrology relevant to active electrical energy meters (see Annex V, MI003, of MID). Can be used for fiscal

(see Annex V, MI003, of MID). Can be used for fiscal (legal) metrology.

Type Selection

Range code **System** Power supply Output AV5: 400 VLL AC - 5(6)A 3-phase, 3 or 4 wire H: auxiliary power supply 01: pulse output 100 to 240 V ac/dc (CT connection) **S1**: RS485 Modbus port M1: M-Bus port

Option

PF: Certified according to MID Directive. Can be used for fiscal (legal) metrology.

Measurement

- A: The power is always integrated (both in case of positive imported and negative exported power) and the total energy meter is certified according to MID.
- **B**: Only the total positive energy meter is certified according to MID.

STANDARD

Not certified according to MID Directive. Cannot be used for fiscal (legal) metrology.

How to order	EM330 DIN AV5 3 H O1 X
Model —	
Range code ———	
System —	
Power supply ———	
Output —	
Option —	

Type Selection

Range code		System		Power supply		Output	
AV5:	400 to 480 VLL ac - 5(6)A (CT connection) 230 to 277 VLN ac - 5(6)A (CT connection)	3:	3-phase, 3- or 4-wire; 2-phase 3-wire, 1-phase 2 wire	H:	auxiliary power sup- ply 100 to 240V ac/dc	O1: S1: M1:	pulse output RS485 Modbus port M-Bus port

Option

X: none

Input specifications

Rated Inputs	
Current type	3-phase loads, CT
Ourse out on	connection
Current range	5(6)A
Nominal voltage	AV5: 400 to 480 VLL ac
Max CTxVT	AV5: 1000
Accuracy	
(@25°C ±5°C, R.H. ≤60%, 45 to 65 Hz)	
40 10 00 112)	AV5: Imin=0.25A; In: 5A,
	Imax: 6A; Un: 230 to 277
	VLN (400 to 480 VLL)
Current	From 0.04In to 0.2In:
Garrone	±(0.5%RDG+1DGT)
	From 0.2In to Imax:
	±(0.5%RDG)
Phase-neutral voltage	In the range Un: ±(0.5% RDG
Phase-phase voltage	In the range Un: ±(1% RDG)
Frequency	From 45 to 65 Hz: ±(0.2%
•	RDG).
Active power	From 0.05 In to Imax,
	within Un range, PF=1:
	±(1% RDG)
	From 0.1 In to Imax, within
	Un range, PF=0.5L or 0.8C
Davier feater	±(1% RDG)
Power factor	±[0.001+1%(1.000 - "PF RDG")]
Reactive power	From 0.05 In to Imax,
	within Un range, sinphi=1: ±(2% RDG)
	From 0.1 In to Imax, within
	Un range, sinphi=0.5L or
	0.8C: ±(2% RDG)
Energies	5.55. <u>–</u> (270 1155)
Active energy	Class 1 according to
3)	EN62053-21 and
	Class B
	according to
	EN50470-3
Reactive energy	Class 2 according to
	EN62053-23
Start-up current:	10mA
Start-up voltage	90VLN
Resolution	Display
Current	0.1 A 0.1 V
Voltage Power	0.1 v 0.01 kW or kvar
Frequency	0.01 KW OF KVAF
PF	0.01
Energies (positive)	0.01 kWh or kvarh
Energies (positive)	0.01 kWh or kvarh
9 (9)	Serial communication
Current	0.001 A
Voltage	0.1 V
Power	0.1 W or var
Frequency	0.1Hz
PF	0.001
Energies (positive)	0.001 kWh or kvarh
Energies (negative)	0.001 kWh or kvarh

Temperature drift	≤200ppm/°C
Sampling rate	4096 samples/s @ 50Hz 4096 samples/s @ 60Hz
Display and touch key-pad	
Туре	Backlit LCD, 3 rows by
	8-digit each, h 7 mm
Read-out	0 4:-:4
Energy: Variables:	8 digit. 4 digit
Touch key	3 (DOWN, Enter and UP).
Max. and Min. indication	,
Energies	Max. 99 999 999
\/ -	Min. 0.01
Variables	Max. 9999 Min. 0.01
Memory	IVIIII. U.U I
Energy	10^12 cycles. Energy value
0,	is saved every time the less
	significant digit increases.
Programming parameters	10^12 cycles. When a parameter is modified, only
	the relevant memory cell is
	overwritten
LEDs	
Flashing red light pulses	Proportional to the product
	of the CT and VT ratios
Weight (pulses/kWh) 1	> 700,1 (CT x VT)
Weight (pulses/kWh) 10	70.1-700 (CT x VT)
Weight (pulses/kWh) 100	7.1-70 (CT x VT)
Weight (pulses/kWh) 1000	< 7.1 (CT x VT)
Duration	90ms
Fix orange light	wrong current direction
3 3	(only with PFB option or
	with "B" measurement
	selection in case of X
	option)
Current overloads	
Continuous	6A, @ 50Hz
For 500ms Voltage Overloads	5 ln
Continuous	1.2 Un
For 500ms	2 Un
Input impedance	
230VL-N	1.2 Mohm
5(6) A	< 0.072 VA per channel
Wrong connection detection	Installation guide to indicate if connections are
	correctly carried out. Can
	be disabled.
Phase sequence	Indicates if the phase
	sequence is not the correct
Correct current direction	one (L1-L2-L3) Indicates if the current
Correct Current Uncollor	direction is not the right one
	(only with PFB option or
	with type "B" measurement
	selection in case of X

Input specifications (cont.)

option).
Load conditions The wro

The wrong connection detection works in case of

loads with:

- PF>0.766 (<40°) if inductive or PF>0.996 (<5°)

if capacitive

- a current at least equal to 10% rated current

in every measuring interval the single phase

energies with positive sign are summed to increase the total postive energy totalizer (kWh+), while the others increase the total negative totalizer (kWh-). Ex.

P L1 = +2kW, P L2 = +2kW,

P L3 = -3 kW

Integration time = 1 hour +kWh = $(2+2) \times 1h = 4 \text{ kWh}$ -kWh = 3 x 1h= 3kWh

Digital input specifications

Digital inputs

Energy metering

Function

Number of inputs Contact measurement voltage Input impedance Free of voltage contact Tariff management (switch between t1-t2)

5 V 1kohm Contact resistance

Overload

≤1kohm, close contact ≥100kohm, open contact In case a voltage is erroneously applied to the digital input, the input is not damaged up to 30 V ac/dc.

Output specifications

0110
RS485 by screw
connection.
For communication
of measured data,
programming parameters
ModBus RTU (slave
function)
9.6, 19.2, 38.4, 57.6, 115.2
kbaud,
even or no parity,
1 to 247 (default: 01)
1/8 unit load. Maximum 24
devices on the
same bus.
1s
50 words available in 1
read command
Rx segment on display
is shown when a valid
Modbus command is sent
to that specific meter
Tx segment on display
is shown when a valid
Modbus reply is sent back
to the master
M-Bus by screw
connection.
For communication of
measured data
M-Bus according to

EN13757-1

0.3, 2.4, 9.6 kbaud

Meters in the M-Bus network 250 Primary address Selectable Secondary address Univocally defined in each unit from 9000 0000 to 9999 Identification number range Other Available functions: wild card, header, initialisation SND NKE, and req udr management. Management of primary address modification via M-Bus VIF, VIFE, DIF and DIFE: see protocol

Static output Purpose

Pulse rate (imp/kWh)

For pulse output proportional to the active energy (kWh) Selectable according to pulse ON duration (Ton) 1-1500 (Ton = 30 ms) 1-500 (Ton = 100 ms) **Note**: max CTxVT x pulse ratio 20000 (e.g.: if pulse ratio is set to 1000, CTxVT max = 20)

Baud rate

Output specifications

Note 2: in MID models, the Pulse ON duration Selectable: 30 ms or 100 ms pulse rate is automatically according to EN62053-31 set according to CT x VT Output type Open collector PNP ${
m V}_{
m ON}$ 1 V dc max. 100mA ${
m V}_{
m OFF}$ 80 V dc max. ratio: Load Weight (pulses/kWh) 1 $> 700,1 (CT \times VT)$ Weight (pulses/kWh) 10 $70.1 - 700 (CT \times VT)$ Weight (pulses/kWh) 100 7.1-70 (CT x VT) Weight (pulses/kWh) 1000 < 7.1 (CT x VT)

General specifications

_			
Operating temperature	-25 to +65 °C (-13 to 149° F) (X option), -25 to +55 °C (-13 to 131 °F) (PF option), indoor, (R.H. from 0 to 90% non-condensing @ 40°C)	Standard compliance Safety Metrology	EN62052-11 (X option models), EN50470-1 (PF option models) EN62053-21 (X option
Storage temperature	-30°C to +80°C (-22 to 176° F) (R.H. < 90% non condensing @ 40°C)	o,	models), EN50470-3 (PF option models) IEC/EN61557-12 (active
Overvoltage category	Cat. III		power and active energy, MID models only)
Insulation (for 1 minute)	4000 V ac RMS between measuring inputs and	Approvals	CE, MID (PF option only), cULus (UL61010-1)
	digital/serial output (see table) 4000 V ac RMS	Connections Cable cross-section area	Voltage inputs: max. 4
Dielectric strength	4000 V ac RMS for 1 minute		mm², min. 1 mm² with/ without metallic cable
EMC Immunity and emissions	According to EN62052-11 (X option models) According to EN50470-1 (PF option models)	Other terminals	ferrule; Max. screw tightening torque: 0.6 Nm 1.5 mm², Min./Max. screws tightening torque: 0.4 Nm
		Housing Dimensions (WxHxD) Material Sealing covers	54 x 90 x 63 mm Polycarbonate, self- extinguishing Included
		Mounting	DIN-rail
		Protection degree Front	IP51
		Screw terminals	IP20
		Weight	Approx. 240 g (packing included)

Power supply specifications


Auxiliary power supply	H: 100 to 240 Vac/dc ±10%	Power consumption	≤ 1W, ≤ 8VA

Insulation (for 1 minute) between inputs and outputs


	Measuring input	Digital or serial output	Digital input
Measuring input	-	4 kV	4 kV
Digital or serial output	4 kV	-	0 kV
Digital input	4 kV	0 kV	-

Accuracy (according to EN50470-3 and EN62053-23)

 $\pmb{kWh}, \ accuracy \ (RDG) \ depending \ on \ the \ current$



kvarh, accuracy (RDG) depending on the current



Measurement accuracy according to IEC/EN61557-12 (MID versions)

Active power	Performance class 1	Active energy	Performance class 2

Display pages

1 st row	2 nd row	3 rd row	"Full" mode	"Easy" mode	Note
kWh+ (imported)		kW system	Х	Х	In case of Measurement set to "A", total energy without considering the current direction.
kWh- (exported)		kW system	Х	Х	Only with Measurement set to "B"
kWh+ (imported)		V L-L system	Х	Х	
kWh+ (imported)		V L-N system	Х	Х	
kWh+ (imported)		PF system	Х		
kWh+ (imported)		Hz	Х		
kvarh+ (imported)		Kvar system	Х	Х	In case of Measurement set to "A": total positive reactive energy without considering the current direction.
kvarh- (exported)		Kvar system	Х	Х	Only with Measurement set to "B"
kWh+ (imported)		kVA system	Х		
kWh+ (imported)	kWdmd peak	kWdmd	Х		
kWh (t1)	"t1"	kW system	Х	Х	Only relevant to kWh+, with Tariff menu set to ON.
kWh (t2)	"t2"	kW system	Х	Х	Only relevant to kWh+, with Tariff menu set to ON.
kWh L1	kWh L2	kWh L3	Х		In case of Measurement set to "A", total energy without considering the current direction. In case of Measurement set to "B", only imported energy.
kVA L1	kVA L2	kVA L3	Х		
kvar L1	kvar L2	kvar L3	Х		
PF L1	PF L2	PF L3	Х		
V L1-N	V L2-N	V L3-N	Х		
V L1-2	V L2-3	V L3-1	Х		
run hour meter		An	Х		
A L1	A L2	A L3	Х	Х	
kW L1	kW L2	kW L3	Х		


X= available


Additional available information on the display


Page	Display	Description
Info 1	YEAr (2015)	Year of production
Info 2	SErIAL n (dddnnnA)	Serial number (ddd= day of the year; nnn=progressive number; A= production line, internal use only)
Info 3	rEVISIon (A.01)	Firmware revision
Info 4	PuLS LEd	Pulse rate of front LED (pulse/kWh)
P3	SYStEM	System type
P4	CT ratio	current transformer ratio
P5	VT ratio	voltage transformer ratio
P6	MEASurE (only X option)	Measurement type
P7	InStALL	Wrong connection detection function
P8	P Int	Integration time for Wdmd calculation
P9	ModE	Set of variables on display
P10	tArIFF	Tariff enabling (and current tariff if enabled)
P11	HoME (only X option)	Selected home page
P12-1	PuLSE (O1 option)	Selection of pulse ON duration of output
P12-2	PuLrAtE (O1 option)	Selection of the pulse rate of output
P13	Prl Add (M1 option)	M-Bus primary address
P14	AddrESS (S1 option)	Modbus serial address
P15	bAud (M1 or S1)	M-Bus or Modbus baud rate
P16-1	PArltY (S1)	Modbus parity
P16-2	StoP blt (S1)	Stop bit (in case of No parity only)
Info 5	Secondary address (M1)	M-Bus secondary address





Wiring diagrams
























Wiring diagrams (cont.)








Additional instruments with RS485 are connected in parallel. The serial output must only be terminated on the last network device connecting terminals A- and T. For connections longer than 1000 m use a signal repeater. Maximum 247 transceivers on the same bus.



Front panel description



Display Backlit LCD display with touch key-pad.

2. LED LED proportional to kWh reading

3. Serial number

Area reserved to serial number and MID-relevant data in PF versions

Dimensions

