

# CHERRY DW 9500 SLIM

The rechargeable designer desktop for demanding users



Models may vary from the image shown

The CHERRY DW 9500 SLIM desktop set meets even the highest demands. It inspires with state-of-the-art technology, best build quality and extra flat design. The design has a minimalist character and still shines with function and style.

Connect the extra flat design desktop set optionally via Bluetooth® or with the wireless USB receiver via 2.4 GHz radio. A slide switch on the mouse and keyboard makes switching child's play. For example, a notebook can be operated via Bluetooth® and a PC via wireless with the same desktop. The interference-free transmission with a range of up to 10 m is AES-128 encrypted - for keyboard and mouse alike.

The stylish keyboard and mouse set is powered by powerful lithium batteries. They last for weeks without needing to be recharged and are then supplied with new energy via a USB-A to USB-C cable. While charging, you can continue working with the wireless keyboard set without complications. Turn off the CHERRY DW 9500 SLIM wireless keyboard regularly when not in use to get even longer battery life.

For working comfort and maximum productivity, CHERRY SX scissor technology. The inimitable typing feel will put a smile on your face right from the first time you plug it in: the flat key travel with

clearly defined resistance enables fast and error-free typing.

If the six additional keys are not enough, the free CHERRY KEYS software is the right choice. With its help, special and F keys can be freely programmed. The included magnetic bar also has a positive effect on the flexibility. It can be mounted in seconds if a steeper angle is desired.

The wireless keyboard has built-in status LEDs directly in the relevant keys. So you can see at a glance if the raise, roll or num lock key is active or if the battery is running low. The ergonomic Bluetooth® mouse also scores with a two-color LED. This shows the battery status of the wireless computer mouse. Furthermore, it provides information about the charging status, the selected connection and the set resolution of the wireless mouse.

The 6-button mouse is worth a closer look. It has a scroll wheel and many technical extras. The ergonomic wireless mouse is particularly pleasant to use. The high-quality metal surface lies perfectly in the hand thanks to the large gliding pads, the mouse glides smoothly over the table. The generous thumb rest really pampers the hand and can counteract fatigue. The high-precision sensor works flawlessly on all surfaces - even glass tables are no problem. The resolution can be set to 600, 1000, 1600 or 3000 dpi in 4 steps by pressing the DPI button. Thus, the wireless computer mouse is also ideally suited for use on high-resolution 4K monitors.

The CHERRY DW 9500 SLIM is THE stylish companion for upscale demands - whether you work from home or in the office. Characteristic for the wireless desktop set is that it combines everything that CHERRY stands for: proven quality with sophisticated technology and chic design. Another plus point for the environment: The packaging does not use any plastic at all!

## FUNCTION AND PERFORMANCE

- Connection either via Bluetooth or 2.4 GHz wireless
- AES-128 encryption for mouse and keyboard
- Rechargeable lithium batteries
- Rechargeable by USB-C
- Status LEDs show low residual battery charge, charging status and mouse resolution
- Status LEDs integrated directly in the keys for the CAPS LOCK, NUM and SCROLL keys
- Extra-small nano receiver for wireless operation
- 6 mouse buttons and scroll wheel
- Precise sensor with resolution adjustable in four stages up to 3000 dpi
- Long-lasting key labels
- Precise CHERRY SX scissor mechanism for an ideal operating feeling
- Solid metal plate in the keyboard for maximum stability
- Removable magnetic strip for height adjustment

## TECHNICAL DATA

Weight main product:	675 g
Dimensions product without packaging:	440 mm x 130 mm x 15 mm
Storage temperature:	-20 °C - 60 °C
Working temperature:	0 °C - 40 °C
Produktzulassungen:	<ul style="list-style-type: none"> <li>• BQB</li> <li>• CE</li> <li>• China RoHS</li> <li>• UKCA</li> <li>• Windows Hardware Compatibility</li> <li>• FCC</li> </ul>
System Requirements-Hardware:	<ul style="list-style-type: none"> <li>• Bluetooth 4.0 or higher</li> <li>• USB-A</li> </ul>
Operating system:	<ul style="list-style-type: none"> <li>• Windows 7</li> <li>• Windows 8</li> <li>• Windows 10</li> <li>• Windows 11</li> </ul>

- Scope of delivery:
- Keyboard
  - Mouse
  - Manual
  - Nano-USB-Receiver
  - Magnetic support bar
  - USB-A to USB-C Cable
  - Pouch

Reliability:	MTBF > 80.000 Stunden
Software support:	CHERRY KEYS
USB dongle:	yes
2.4 Ghz wireless connection:	yes
Encryption in wireless mode:	yes
Wireless range (m):	10 m
Connection via Bluetooth:	yes
Encryption in Bluetooth mode:	yes
Bluetooth protocol:	Bluetooth 4.2
Bluetooth range (m):	10 m
Number of batteries:	1
Batterie Art:	Li-Ion
Batterie Bauform:	Special
Battery rechargeable:	yes
Battery replaceable:	no
Service life per key (in million strokes):	10 mio. actuations
Switching characteristics:	standard
Max. current consumption (mA) of keyboard:	5 mA
Keyboard format:	Full-size (100%)
Integrated metal plate:	yes
N-key rollover:	not specified
Anti-ghosting:	not specified
Key encryption:	AES-128
Internal memory:	no
Tastenkopf Beschriftung:	Pad Printing + UV coating
Palm rest:	Palm rest not available
USB hub:	no

- Special key functions:
- Browser
  - PC lock
  - Unmute/Mute
  - Volume down
  - Volume up
  - Calculator

Illumination:	no
Adjustable feet:	yes
Status LEDs:	in keys
Key technology:	Scissor
Keycap material:	ABS
Model-Number:	JG-91

## TECHNICAL DATA (MOUSE)

Color:	black/grey
Dimensions mouse without packaging:	120 mm x 79 mm x 44,5 mm
Weight of product:	123 g
Number of keys:	6
Thumb buttons:	yes
Sensor:	PixArt PAW3805EK
Max. resolution (dpi):	3.000 dpi
dpi switch:	yes
dpi levels:	4
Max. Current consumption (mA)	
Mouse:	10 mA
Switch type:	clicky

2.4 Ghz wireless connection:	yes
Wireless range (m):	10 m
Encryption in wireless mode:	AES-128
Connection via Bluetooth:	yes
Encryption in Bluetooth mode:	AES-128
Bluetooth protocol:	Bluetooth 4.2
Bluetooth range (m):	10 m
Number of batteries in mouse:	1
Batterie Art:	Li-Ion
Batterie Bauform:	Special
Battery rechargeable:	yes
Battery replaceable:	no
Battery charging socket:	USB-C
Battery life (h):	2

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

Actual battery life is strongly depending on individual user behavior and hardware setup.

Designation

CHERRY DW 9500 SLIM

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.