

### **ADELIA-75-M**

~24° medium beam

### **SPECIFICATION:**

Dimensions Ø 74.7 mm
Height 42.8 mm
Fastening snaps
ROHS compliant yes 1



### **MATERIALS:**

ComponentTypeMaterialADELIA-75-MReflectorAluminium

ColourFinishCoatingmetalglossAnodized

### **ORDERING INFORMATION:**

Component


C18428\_ADELIA-75-M

» Box size: 400 x 300 x 300 mm

**Qty in box MOQ MPQ Box weight (kg)** 840 70 70 14.1



# PRODUCT DATASHEET C18428\_ADELIA-75-M



See also our general installation guide: www.ledil.com/installation\_guide

Published: 23/06/2022




## **OPTICAL RESULTS (SIMULATED):**

### bridgelux

LED V18 Gen 8  $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 26.0° / 60.0° Efficiency 79 % Peak intensity 2.7 cd/lm LEDs/each optic Light colour White

Required components:


C18432\_ADELIA-ADAPTER-C Bender Wirth: 639b Hekla XL



#### bridgelux.

LED V22 Gen 8 FWHM / FWTM 28.0° / 62.0° Efficiency 75 % Peak intensity 2.4 cd/lm LEDs/each optic 1 White Light colour Required components:

C18432\_ADELIA-ADAPTER-C Bender Wirth: 631b Hekla XL




#### bridgelux

LED V6 HD Gen 7 FWHM / FWTM 17.1° / 32.2 + 31.2°

Efficiency 93 % Peak intensity 6.7 cd/lm LEDs/each optic 1 Light colour White

Required components:

F15253\_HEKLA-SOCKET-A




### CREE & LED

CXA/B 15xx FWHM / FWTM 18.0° / 34.0° Efficiency 87 % Peak intensity 5.5 cd/lm LEDs/each optic White Light colour

Required components: F17436 HEKLA-G2-D

C18432\_ADELIA-ADAPTER-C



Published: 23/06/2022




### **OPTICAL RESULTS (SIMULATED):**

### CREE \$\(\phi\) LED

LED CXA/B 1830
FWHM / FWTM 22.0° / 52.0°
Efficiency 85 %
Peak intensity 3.8 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C18432\_ADELIA-ADAPTER-C Bender Wirth: 637b Hekla



# **SAMSUNG**

LED LC003D / LC006D / LC009D / LC013D

FWHM / FWTM 18.0° / 36.0°

Efficiency 87 %


Peak intensity 5.3 cd/lm

LEDs/each optic 1

Light colour White

Required components:

F17435\_HEKLA-G2-C C18432\_ADELIA-ADAPTER-C




## **SAMSUNG**

LED LC003D / LC006D / LC009D / LC013D

FWHM / FWTM 20.1° / 36.2 + 37.2°

Efficiency 90 %
Peak intensity 5.2 cd/lm
LEDs/each optic 1
Light colour White

Required components: F17435\_HEKLA-G2-C



# **SAMSUNG**

LED LC016D / LC019D / LC026D / LC033D

FWHM / FWTM 24.0° / 56.0°

Efficiency 85 %


Peak intensity 3.3 cd/lm

LEDs/each optic 1

Light colour White

Required components: F17438\_HEKLA-G2-I

C18432\_ADELIA-ADAPTER-C





### **OPTICAL RESULTS (SIMULATED):**


# **SAMSUNG**

LED LC016D / LC019D / LC026D / LC033D

FWHM / FWTM 24.1° / 56.3 + 55.3°

Efficiency 88 %
Peak intensity 3.5 cd/lm
LEDs/each optic 1
Light colour White

Required components: F17438\_HEKLA-G2-I





# PRODUCT DATASHEET C18428\_ADELIA-75-M

#### **GENERAL INFORMATION:**

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

### **MATERIALS:**

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

### **LEDIL Oy**

Joensuunkatu 13 FI-24240 SALO Finland

#### LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

# Ledil Optics Technology (Shenzhen) Co., Ltd.

# 405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

# Local sales and technical support

www.ledil.com/ where\_to\_buy

#### **Shipping locations**

Salo, Finland Hong Kong, China

#### **Distribution Partners**

www.ledil.com/ where\_to\_buy