

# Emergency stop/emerg. switching off button, classic, palmtree, 45mm, turn-to-release function, 1 N/C, 1 N/O, cable (black) with nonterminated end, 4p, 3.5 m $\,$



Part no. C22-PVT45P-K11-P65 Article no. 185161

Delivery program			
Product range			RMQ compact solution
Basic function			Controlled stop pushbuttons/emergency-stop buttons
Single unit/Complete unit			Complete unit
Design			Palm-tree shape
Diameter	Ø	mm	45
Illumination	_		Non-illuminated
mummanon			Turn-to-release function
Connection type			Cable (black) with non-terminated end, 4 pole
Cable Length		m	3.5
Description			Tamper-proof according to ISO 13850, EN 418
Colour			
Mushroom head			Red
Base			yellow
Degree of Protection			IP66, IP67, IP69K (front) IP65 (on rear)
Connection to SmartWire-DT			no
Contacts			
N/C = Normally closed			1 NC →
N/O = Normally open			1 N/O
Notes			= safety function, by positive opening to IEC/EN 60947-5-1
Actuator travel and actuation force as per DIN EN 60947-5-1, K.5.4.1			
	mm		4.65
Maximum travel	mm		5.7
Minimum force for positive opening	N		20
Contact sequence			BN WH  I L  BK BU
Contact travel = Contact closed = Contact open			
Contact diagram			3.15 0 2.2 5.5 Zw = 4.5 mm

Positive opening (ZW)

### **Technical data**

### General

General			
Standards			IEC/EN 60947-5-5 VDE 0660
Certifications			CE, UL, CSA
Operating frequency	Operations/h		≤ <sub>300</sub>
Actuating force		n	≦ <sub>50</sub>
Tightening torque Threaded ring		Nm	2
Climatic proofing			Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
Degree of Protection			IP66, IP67, IP69K (front) IP65 (on rear)
Mounting position			As required
Mechanical shock resistance, shock duration 11 ms		g	> 30
Contacts			
Rated impulse withstand voltage	U <sub>imp</sub>	V AC	4000
Rated insulation voltage	$U_{i}$	V	250
Overvoltage category/pollution degree			III/3
Control circuit reliability			
At 17 V DC/7 mA	H <sub>F</sub>		N/O contact: statistically determined 1 failure per 17 $\times$ 106 operations N/C contact: statistically determined 1 failure per 0.9 $\times$ 10 <sup>6</sup> Operations
Max. short-circuit protective device			
Fuse	gG/gL	Α	4
Rated conditional short-circuit current	Iq	kA	1
Switching capacity			
Rated operational current	le	Α	
AC-15			
24 V	l <sub>e</sub>	Α	4
DC-13			
24 V	I <sub>e</sub>	Α	3
Cable characteristics			
Design			Cable end open
Cable Length		m	3.5
Material characteristic			PUR

## Design verification as per IEC/EN 61439

Technical data for design verification		
Operating ambient temperature min.	°C	-25
Operating ambient temperature max.	°C	70

mm

4.7

## **Technical data ETIM 6.0**

Diameter

Low-voltage industrial components (EG000017) / Emergency stop complete (EC002034)

Ø

(ecl@ss8.1-27-37-12-44 [ACN986008])				
Unlocking method			Turn unlatching mechanism	
Number of contacts as normally closed contact			1	
Number of contacts as normally open contact			1	
Degree of protection (IP)			-	
Mounting method			Built-in	
With lighting			No	
Hole diameter	n	mm	22	
Connection type auxiliary circuit			-	
Diameter cap	n	mm	45	

## **Dimensions**

