


### **Draw wire mechanics** for outdoor applications

#### Draw wire encoder D120

### Measuring length up to 10 m Linearity up to ±0.1 %



Their extremely robust construction, their high IP69k protection level and their wide temperature range make these new draw wire encoders particularly reliable and durable. Their flexibility and adaptability reflects in the wide range of housing and wire types, the long measuring range and the various interfaces. The possibility of redundancy must be particularly pointed out.



Analog













Long service

Wide temperaturerange

High protection

#### **Robust**

- Protection level up to IP69k and wide temperature range from -40°C ... +85°C.
- The titanium-anodized aluminum housing and the stainless steel wires allow using the mechanics even in harsh conditions.
- Wire diameter (stainless steel, V4A) up to Ø 1.5 mm ideal for outdoor applications.

#### **Versatile**

- . Measuring length up to 10 m.
- · Redundant outputs (mA, V, R, CANopen).
- . The right measuring wire and the right wire fastening for every application.
- Linearity up to  $\pm 0.1$  % of the measuring range.
- · Various constructions: open, closed housing or housing with perforated sheet steel cover.

#### Order code

#### D8.D120 XXX X 0000 **e**

Standard variants are represented bold underlined

- Measuring length
- $3 = 3 \, \text{m}$
- $4\,=4\,m$
- 5 = 5 m
- $6 = 6 \, \text{m}$
- 7 = 7 m
- 8 = 8 m $9 = 9 \, \text{m}$
- A = 10 m
- Wire types 1)
- 1 = V4A, Ø 0.5 mm
- 2 = V4A, ø 1.0 mm (measuring length 3 ... 8 m)
- 3 = V4A, ø 1.5 mm (measuring length 3 ... 6 m)

- C Linearity
- 1 = 0.5 %
- 2 = 0.25 %
- 3 = 0.1 %
- **d** Housing
- 1 = open housing, open wire guide
- 3 = housing with perforated sheet metal cover, open wire guide
- 4 = housing with perforated sheet metal cover, closed wire guide
- 6 = closed housing, closed wire guide

e Sensor type

A11 = 4 ... 20 mA / 12 ... 30 VDC

A22 = 0 ... 10 V / 12 ... 30 VDC

A33 = 1  $k\Omega$  / max. 30 VDC

CC1 = CANopen 2)

 $R11 = 2 \times 4 \dots 20 \text{ mA} / 12 \dots 30 \text{ VDC}$ 

 $R22 = 2 \times 0 \dots 10 \text{ V} / 12 \dots 30 \text{ VDC}$ R33 =  $2 \times 1 \text{ k}\Omega$  / max. 30 V

 $RC1 = 2 \times CANopen^{2}$ 

1 Type of connection / protection level sensor

1 = radial cable, 2 m [6.56'] TPE / IP69k 3)

3 = radial M12 connector / IP67

4-pin for sensor type A11 ... A33 8-pin for sensor type R11 ... R33

<sup>1)</sup> Wire type availability depends on the selected measuring range, refer to the technical data.

<sup>2)</sup> In preparation, samples available Q4/2017, series availability planed for Q1/2018.


<sup>3)</sup> Other cable length on request



# Draw wire mechanics for outdoor applications

### Draw wire encoder D120

# Measuring length up to 10 m Linearity up to $\pm 0.1$ %



### Technical data

General technical data						
Linearity	±0.5 %					
Improved linearity	±0.25 % or ±0.1 %					
Resolution	see electrical characteristics					
Sensor element	potentiometer					
Output signal (others on request)	4 20 mA, 0 10 V, potentiometer, CANopen (in preparation)					
Redundant output signal	optional for: 4 20 mA, 0 10 V, potentiometer, CANopen (in preparation)					
Connection	radial M12 connector or radialer cable outlet (TPE cable), standard length 2 m					
Protection	IP67, optional IP69k (only with cable outlet)					
Humidity	max. 90 % relative, no condensing					
Wire pull-out speed	max. 3.0 m/s					
Acceleration	max. 50 m/s <sup>2</sup>					
Weight	1300 1600 g [45.87 56.44 oz] depending on measuring range					
Housing	aluminum, spring housing PA6					
Spring force	min. 7 N / max. 13 N $^{1)}$					

Characteristics measuring wire						
V4A, ø 0.5 mm	measuring range no. breaking force TK	3 10 m 1.4401 280 N 16 x 10 <sup>-6</sup> K <sup>-1</sup>				
V4A, ø 1.0 mm	measuring range no. breaking force TK	3 8 m 1.4401 942 N 16 x 10 <sup>-6</sup> K <sup>-1</sup>				
V4A, ø 1.5 mm	measuring range no. breaking force TK	3 6 m 1.4401 1.890 N 16 x 10 <sup>-6</sup> K <sup>-1</sup>				

#### **Operating principle**


#### Construction

The core of a draw wire device is a drum mounted on bearings, onto which a wire is wound.

Winding takes place via a spring-loaded device. The single-layer wire winding ensuring the best linearity possible is a specific feature of Kübler draw wire encoders.

#### Note

Exceeding the maximum extension length of the draw wire will lead to damage to the wire and the mechanics.



<sup>1)</sup> Depends on the measuring length.



## **Draw wire mechanics** for outdoor applications

### **Draw wire encoder D120**

### Measuring length up to 10 m Linearity up to ±0.1 %

Electrical characteristics (analog se	ensor, scaled to measuring range)			
Version	A11 / R11	A22 / R22	A33 / R33	
Output	4 20 mA	0 10 V	1 kΩ, potentiometer	
Output current	max. 50 mA in case of a failure	max. 10 mA, min. load 10 kΩ	-	
Max. current consumption	-	22.5 mA (non load)	-	
Power supply	12 30 V DC	12 30 V DC	max. 30 V DC	
Response time	< 1 ms from 0 100 % and 100 0 %	< 3 ms from 0 100 % and 100 0 %	=	
Resolution	limited by the noise	limited by the noise	theoretically unlimited	
Noise	0.03 mA $_{pp}$ = 6 mV $_{pp}$ at 200 $\Omega$	typ. 3 mV $_{pp}$ , max. 37 mV $_{pp}$	depending on the supply voltage	
Recommended slider current	_	-	< 1 μΑ	
Reverse polarity protection	yes	yes	=	
Working temperature	-20°C +85°C [-4°F +185°F] -40°C +85°C [-40°F +185°F]	-20°C +85°C [-4°F +185°F] -40°C +85°C [-40°F +185°F]	-20°C +85°C [-4°F +185°F] -40°C +85°C [-40°F +185°F]	
Short circuit proof	_	yes, sustained short-circuit proof	-	
Temperature coefficient	0.0079 %/K	0.0037 %/K	±0.0025 %/K	
Connection diagrams	V* + A out	V+ + V	V+ + V Out Out	
Electromagnetic compatibility	acc. to EN 61326-1:2006	acc. to EN 61326-1:2006	-	
CE compliant acc. to	EMC guideline 2014/30/EU RoHS guideline 2011/65/EU			

Options	
Protection class IP69k	All relevant sensor components are entirely encapsulated. Suitable for steam and high-pressure cleaning (only in connection with cable outlet).
Extended temperature range	The use of special components allows an operating temperature of -40°C +85°C [-40°F +185°F]
Redundant output signal	The use of a double potentiometer allows the sensor to provide two independent output signals:  • $2 \times 4 \dots 20 \text{ mA}$ • $2 \times 0 \dots 10 \text{ V}$ • $2 \times 1 \text{ k}\Omega$ • $2 \times \text{CANopen (in preparation)}$
Wire fastening (with swivel, on ball bearing)	<ul> <li>eyelet, internal diameter 20 mm (standard)</li> <li>M4 thread, length 22 mm</li> <li>wire clip</li> </ul>
Wire cleaner	In preparation

Order code – extensions for the following options					
Wire fastening M4 1)	D8.D120.xxxx.xxxx.xxxx. <b>S001</b>				
Wire fastening clip	D8.D120.xxxx.xxxx.xxxx. <b>S002</b>				
Extended temperature range -40 +85°C [-40°F +185°F]	D8.D120.xxxx.xxxx.xxxx. <b>\$003</b>				
Wire fastening M4 and -40 +85°C [-40°F +185°F]	D8.D120.xxxx.xxxx.xxxx. <b>S004</b>				
Wire fastening clip and -40 +85°C [-40°F +185°F]	D8.D120.xxxx.xxxx.xxxx. <b>S005</b>				

www.kuebler.com



Draw wire mechanics		Measuring length up to 10 m
for outdoor applications	Draw wire encoder D120	Linearity up to ±0.1 %

### **Terminal assignment**

Type of connection	Sensor type	M12 connec	M12 connector, 4-pin					
	A11 (4 20 mA)	Signal:	+V	n.c.	Signal	n.c.	Ť	
2	A22 (0 10 V)	Signal:	+V	Signal	0 V	0 V Signal	Ť	
3	A33 (1 kΩ)	Signal:	+V	Slider	0 V	n.c.	Ť	
		Pin:	1	2	3	4	PH	

	Type of connection	Sensor type	M12 connec	A12 connector, 8-pin								
		R11 (4 20 mA)	Signal:	+V <sub>1</sub>	n.c.	Signal 1	n.c.	+V 2	n.c.	Signal 2	n.c.	Ť
	2	R22 (0 10 V)	Signal:	+V <sub>1</sub>	Signal 1	0 V <sub>1</sub>	0 V Signal 1	+V 2	Signal 2	0 V <sub>2</sub>	0 V Signal 2	Ť
3	R33 (1 kΩ)	Signal:	+V <sub>1</sub>	Slider 1	0 V <sub>1</sub>	n.c.	+V 2	Slider 2	0 V <sub>2</sub>	n.c.	Ť	
			Pin:	1	2	3	4	5	6	7	8	PH

Type of connection	Sensor type	Cable (isolate unused wires individually before initial start-up)						
	A11 (4 20 mA)	Signal:	+V	n.c.	Signal	n.c.	Ť	
	A22 (0 10 V)	Signal:	+V	Signal	0 V	0 V Signal	Ť	
1	A33 (1 kΩ)	Signal:	+V	Slider	0 V	n.c.	Ť	
		Core color:	BN	WH	BU	SW	shield	

Type of connection	Sensor type	Cable (isolat	able (isolate unused wires individually before initial start-up)								
	R11 (4 20 mA)	Signal:	+V <sub>1</sub>	n.c.	Signal 1	n.c.	+V 2	n.c.	Signal 2	n.c.	Ť
1	R22 (0 10 V)	Signal:	+V <sub>1</sub>	Signal 1	0 V <sub>1</sub>	0 V Signal 1	+V 2	Signal 2	0 V <sub>2</sub>	0 V Signal 2	Ť
	R33 (1 kΩ)	Signal:	+V <sub>1</sub>	Slider 1	0 V <sub>1</sub>	n.c.	+V 2	Slider 2	0 V <sub>2</sub>	n.c.	Ť
		Core color:	WH	BN	GN	YE	GY	PK	BU	RD	shield

### Top view of mating side, male contact base







M12 connector, 8-pin





Draw wire mechanics for outdoor applications


Draw wire encoder D120


Measuring length up to 10 m Linearity up to ±0.1 %

### Technology in detail










## Housing with perforated sheet metal cover, closed wire guide

For use in the presence of dirt, particles size > 2mm and liquids.


Shock protection, wire cleaning device (in preparation).



## Closed housing, closed wire guide

(in preparation).

For use in the presence of sticky dust, cement, concrete, clay. Shock protection, wire cleaning device





# Draw wire mechanics for outdoor applications


Draw wire encoder D120


Measuring length up to 10 m Linearity up to ±0.1 %

#### **Dimensions**

Dimensions in mm [inch]

Open housing, open wire guide






Wire diameter ø 0.5 mm – drum pitch circumference: 335.2 [13.2]						
Measuring length A1 B C						
3 10 m	230 [9.06]	110 [4.33]	10.75 [0.42]			

Wire diameter ø 1.0 mi	circumference	336.8 [13.26]	
Measuring length	A1	В	С
3 5 m	230 [9.06]	110 [4.33]	10.75 [0.42]
6 8 m	320 [12.6]	200 [7.87]	12.25 [0.48]

Wire diameter ø 1.5 mm – drum pitch circumference: 338.3 [13.32]				
Measuring length	A1	В	C	
3 4 m	230 [9.06]	110 [4.33]	10.75 [0.42]	
5 6 m	320 [12.6]	200 [7.87]	12.25 [0.48]	

#### Connector output / Cable outlet

The cable must be protected in case of steam and high-pressure cleaning.





Draw wire mechanics for outdoor applications


**Draw wire encoder D120** 


Measuring length up to 10 m Linearity up to ±0.1 %

#### **Dimensions**

Dimensions in mm [inch]

Housing with perforated sheet metal cover, closed wire guide





Wire diameter ø 0.5 mm – drum pitch circumference: 335.2 [13.2]				
Measuring length	A2	В	С	
3 10 m	233 [9.17]	110 [4.33]	10.75 [0.42]	

Wire diameter ø 1.0 mm – drum pitch circumference: 336.8 [13.26]				
Measuring length	A2	В	C	
3 5 m	233 [9.17]	110 [4.33]	10.75 [0.42]	
6 8 m	323 [12.7]	200 [7.87]	12.25 [0.48]	

Wire diameter ø 1.5 mm – drum pitch circumference: 338.3 [13.32]				
Measuring length	A2	В	С	
3 4 m	233 [9.17]	110 [4.33]	10.75 [0.42]	
5 6 m	323 [12.7]	200 [7.87]	12.25 [0.48]	