



Fuse holder, low voltage, 32 A, DC 1000 V, 10 x 38 mm, gPV, 1P, UL, IEC, with indicator

Part no. **1P MFH For 10x38 gPV fuse with indicator**
 Catalog No. **CHPV1IU**

EL-Nummer (Norway) **4300321**

Delivery program

Product range			Fuse accessory
Basic function			Fuse-holder
Field of application			low voltage
Rated current	I	A	32
Rated voltage			DC 1000 V
Size			10 x 38 mm
Utilization category			gPV
Status indicator			with indicator
Description			DIN rail mounting colour-coded Rated for use with 75°C or 90°C wire fine stranded wire spade terminals and with comb-bus bars Use any higher temperature rated wire with appropriate derating. Modular
Number of poles			1P
usable for size/applications			Photovoltaic for cylindrical fuse-links
Standard/Approval			UL IEC
Standards/Regulations			IEC cULus CCC CSA UR

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Holder for cylindrical fuse (EC002705)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Holder for cylindrical fuse (ecl@ss10.0.1-27-14-21-21 [ADI305007])			
Nominal voltage		V	1500
Mounting method			DIN rail
For fuse size			10x38 mm
Number of poles			1
Concurrently switching N-neutral			No
Lockable			Yes
Optical defect indication			Yes
Width in number of modular spacings			1
Built-in depth		mm	51.5
Degree of protection (IP)			IP20