


UDIMM/SODIMM DDR5 - 4800

NEXT-LEVEL EDGE For Your System

Harness The Power Of DDR5

Taking speed, capacity, and reliability even further, the cutting-edge technology of this DDR5 module gives that next-level edge for your system's performance. With an aggressive 4800MHz frequency, it's 50% higher than a standard 3200MHz DDR4 to provide multi-core CPUs with extreme responsiveness and the power to multi-task seamlessly.



**HIGHER
FREQUENCY**

Greater Power Efficiency

Even with all of its extra power, this DDR5 module improves upon its predecessor with on-module voltage regulation. A power management integrated circuit (PMIC) reduces the burden on the motherboard control and results in a lower voltage of 1.1V versus 1.2V for DDR4 for even less power consumption.



**LOWER
VOLTAGE
1.1V**

Features

- 4800MHz grants faster transmission speeds and higher bandwidth than DDR4
- Low voltage of 1.1V for less power consumption
- Improved reliability versus DDR4 with On-Die Error Correction Code (ECC)
- Optimized efficiency with two independent 32-bit channels per module
- High computing performance with double the banks and double the burst length compared to DDR4
- Compatible with 12th Gen Intel® Core™ processors that support DDR5 and DDR5 compatible motherboards

Specifications

- Dimensions:
[UDIMM] 31.3mm x 133.4mm / [SODIMM] 30.0mm x 69.6mm
- Capacity:
Single Pack: 8GB, 16GB, 32GB
Dual Channel Kit: 16GB(8GB*2), 32GB(16GB*2), 64GB(32GB*2)
- Form Factor:
[UDIMM] 288 Pin UDIMM / [SODIMM] 262 Pin SOIMM
- Frequency (Speed): 4800MHz*
- CAS Latency: CL40
- Voltage: 1.1V
- Certification: CE, UKCA, Green dot (Germany & Spain Only), WEEE, Triman, RoHS
- Warranty: Limited Lifetime Warranty

*Actual speed may vary depending on system platform or configuration

DDR5 - 4800 | UDIMM

Capacity	CAS Latency / Voltage	IC Configuration	Rank	P/N
8GB x 1	CL40, 1.1V	1Gx16	Single Rank	SP008GBLVU480G02
8GB x 2	CL40, 1.1V	1Gx16	Single Rank	SP016GBLVU480G22
16GB x 1	CL40, 1.1V	2Gx8	Single Rank	SP016GBLVU480F02
16GB x 2	CL40, 1.1V	2Gx8	Single Rank	SP032GBLVU480F22
32GB x 1	CL40, 1.1V	2Gx8	Dual Rank	SP032GBLVU480F02
32GB x 2	CL40, 1.1V	2Gx8	Dual Rank	SP064GBLVU480F22

DDR5 - 4800 | SODIMM

Capacity	CAS Latency / Voltage	IC Configuration	Rank	P/N
8GB x 1	CL40, 1.1V	1Gx16	Single Rank	SP008GBSVU480G02
8GB x 2	CL40, 1.1V	1Gx16	Single Rank	SP016GBSVU480G22
16GB x 1	CL40, 1.1V	2Gx8	Single Rank	SP016GBSVU480F02
16GB x 2	CL40, 1.1V	2Gx8	Single Rank	SP032GBSVU480F22
32GB x 1	CL40, 1.1V	2Gx8	Dual Rank	SP032GBSVU480F02
32GB x 2	CL40, 1.1V	2Gx8	Dual Rank	SP064GBSVU480F22

