

KERN DE 12K1A

KERN

The long lasting story of success with dust and spray protected display device



Construction

Dimension display device (W×D×H)	225×110×60 mm
Dimension housing (W×D×H)	318×305×75 mm
Dimensions weighing platform (W×D×H)	318×308×75 mm
Dimensions weighing surface (W×D)	315×305 mm
Material display housing	Plastics
Material weighing plate	stainless steel
Material platform	metal, lacquered
Display device cable length	1,4 m
Allowed cable length display device [Max]	3 m
Load cells - number	4

Functions

Number of keys for operation	5
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Sum A
Underfloor weighing	None
Interfaces	RS-232 standard
IP protection - display	IP65

Counting

Smallest piece weight when piece counting - laboratory conditions	2 g
Smallest piece weight when piece counting - normal conditions	20 g
Reference quantity	5, 10, 20, 25, 50
Counting resolution (laboratory conditions)	6.000

Power Supply

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	15 V, 500 mA
Plug-in power supply type	Power adapter
Supplied plug-in power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH

Category

Brand	KERN
Product category	Industrial scales
Product group	Platform scales

Measuring System

Readability [d]	1 g
Weighing capacity [Max]	12000 g
Eccentric loading at 1/3 [Max]	5 g
Reproducibility	1 g
Linearity	± 3 g
Weighing system	Strain gauge
Resolution	12.000
Tare range	12000 g
Units	kg g dwt tl (Tw) tl (HK) ozt mo lb oz ffa tol
Default unit	g
Stabilization time	2,5 s
Warm-up time	30 min
Adjustment options	Adjusting with external weight
Recommended adjusting weight	12 kg (M1)
Possible calibration points	4 kg; 8 kg; 12 kg

Approval

CE mark	✓
---------	---

Display

Display digit height	25 mm
Display backlight	✓
Display screen size	87×29 mm

KERN DE 12K1A



The long lasting story of success with dust and spray protected display device

Plug-in power supply / adapter for countries - optional	EURO UK US CH
Rechargeable battery optional	Rchrg. battery optional
Rechargeable battery charging time	10 h
Rechargeable battery operating time - backlight on	15 h
Rechargeable battery operating time - backlight off	30 h
Battery	9 V block
Battery operating time	12 h

Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C

Packing & Shipping


Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	515×385×135 mm
Net weight approx.	4,8 kg
Gross weight approx.	6 kg

Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Piktogramme

STANDARD



OPTION

