
DI5020

Compact evaluation unit for speed monitoring

DIA3010-ZPKG







Application				
Application		simple evaluation of rotating and linear movement with regard to underspeed; blocking		
Electrical data				
Nominal voltage DC	[V]	1036		
Current consumption	[mA]	< 20		
Protection class		III		
Reverse polarity protection		yes		
Outputs				
Total number of outputs		1		
Electrical design		PNP		
Output function		normally open		
Max. voltage drop switching output DC	[V]	2.5		
Permanent current rating of switching output DC	[mA]	250		
Short-time current rating of switching output	[mA]	250		
Short-circuit proof		yes		
Overload protection		yes		
Monitoring range				
Sensing range	[mm]	10		
Sensing range adjustable		no		
Operating distance	[mm]	08.1		
Measuring/setting range				
Setting range [In	np/min]	53600		
Accuracy / deviations				
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3		
Hysteresis [9	6 of Sr]	10		
Reaction times				
Start-up delay	[s]	15		
Max. damping frequency [In	np/min]	18000		


DI5020

Compact evaluation unit for speed monitoring



DIA3010-ZPKG

Software / programming					
Adjustment of the switch point		multiturn potentiometer			
Operating conditions					
Ambient temperature	[°C]	-2580			
Protection		IP 65; IP 67			
Tests / approvals					
MTTF	[years]	656			
Mechanical data					
Weight	[g]	304.5			
Housing		Threaded type			
Mounting		flush mountable			
Dimensions	[mm]	M30 x 1.5 / L = 80			
Thread designation		M30 x 1.5			
Material		brass special coating; PA; TPE-U			
Displays / operating elements					
Display		Switching status	1 x LED, green		
Accessories					
Accessories (supplied)		lock nuts: 2			
Electrical connection					
Cable: 2 m, PUR; 3 x 0.5 mm ²					
Connection					



Core colors :

BK = black BN = brown BU = blue