


LEILA-SC-RS

~9.6° spot beam

SPECIFICATION:

Ø 21.6 mm **Dimensions** Height 14.8 mm Fastening clips **ROHS** compliant yes 🕕



MATERIALS:

Type Material Colour **Finish** Component LXP2-RS Single lens **PMMA** clear LEILA-SC-HLD Holder PC black

ORDERING INFORMATION:


» Box size: 480 x 280 x 300 mm

Component Qty in box MOQ **MPQ** Box weight (kg) CP17587_LEILA-SC-RS Single lens 1680 336 112 8.0

Published: 05/08/2020



PRODUCT DATASHEET CP17587_LEILA-SC-RS



See also our general installation guide: www.ledil.com/installation_guide

Published: 05/08/2020




OPTICAL RESULTS (MEASURED):

OSRAM Opto Semiconductors


LED OSLON Square CSSRM2/CSSRM3

FWHM / FWTM 9.0° / 20.0° Efficiency 93 % 22.9 cd/lm Peak intensity LEDs/each optic Light colour White Required components:



OSRAM Opto Semiconductors

LED OSLON SSL 150 FWHM / FWTM 5.5° / 14.5° Efficiency 93 % Peak intensity 42.3 cd/lm LEDs/each optic 1 White Light colour Required components:






OPTICAL RESULTS (SIMULATED):

CREE 1 LED

LED CLR6A-TKW
FWHM / FWTM 14.0° / 30.0°
Efficiency 93 %
Peak intensity 9.8 cd/lm
LEDs/each optic 1

Light colour RGBW

Required components:



CREE - LED

 LED
 XP-E2


 FWHM / FWTM
 8.0° / 16.0°

 Efficiency
 92 %

 Peak intensity
 38.8 cd/lm

LEDs/each optic 1
Light colour White

Required components:



CREE - LED

 LED
 XP-G3


 FWHM / FWTM
 12.0° / 24.0°

 Efficiency
 95 %

 Peak intensity
 16.9 cd/lm

LEDs/each optic 1
Light colour White


Required components:



DESCRIPTION LUMILEDS

LED LUXEON C
FWHM / FWTM 8.0° / 16.0°
Efficiency 87 %
Peak intensity 31.9 cd/lm
LEDs/each optic 1
Light colour White

Required components:





OPTICAL RESULTS (SIMULATED):


White



LED LUXEON CZ $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 6.0° / 14.0° Efficiency 92 % Peak intensity 44 cd/lm LEDs/each optic

Required components:


Light colour



MUMILEDS

LED LUXEON HL2X FWHM / FWTM 14.0° / 26.0° Efficiency 93 % Peak intensity 12.9 cd/lm LEDs/each optic 1 White Light colour


Required components:



LUMILEDS

LUXEON HL2X LED FWHM / FWTM 12.0° / 24.0° Efficiency 93 % Peak intensity 16.1 cd/lm LEDs/each optic 1

Light colour White Required components:




OSRAM

Light colour

LED OSCONIQ C 2424 FWHM / FWTM 10.0° / 22.0° Efficiency 93 % Peak intensity 19.2 cd/lm LEDs/each optic

White

Required components:




5/7

Published: 05/08/2020



OPTICAL RESULTS (SIMULATED):



6/7



PRODUCT DATASHEET CP17587_LEILA-SC-RS

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Salo, Finland Hong Kong, China

Distribution Partners

www.ledil.com/ where_to_buy

LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.