

## **LEILA-SC-W**

~40° wide beam

## **SPECIFICATION:**

Dimensions Ø 21.6 mm
Height 14.8 mm
Fastening clips
ROHS compliant yes ①



## **MATERIALS:**

ComponentTypeMaterialColourFinishLXP2-WSingle lensPMMALEILA-SC-HLDHolderPCblack


## **ORDERING INFORMATION:**

» Box size: 480 x 280 x 300 mm

ComponentQty in boxMOQMPQBox weight (kg)CP17591\_LEILA-SC-WSingle lens16803361127.8



## PRODUCT DATASHEET CP17591\_LEILA-SC-W



See also our general installation guide: www.ledil.com/installation\_guide




## **OPTICAL RESULTS (SIMULATED):**

## CREE . LED

LED XP-G3  $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 46.0° / 62.0° Efficiency 96 % Peak intensity 1.9 cd/lm LEDs/each optic Light colour White


Required components:



## CREE & LED

LED XP-L2 FWHM / FWTM 50.0° / 72.0° Efficiency 89 % Peak intensity 1.3 cd/lm LEDs/each optic 1 White Light colour


Required components:



## LUMILEDS

LUXEON C LED FWHM / FWTM 39.0° / 58.0° Efficiency 87 % Peak intensity 2.1 cd/lm LEDs/each optic Light colour White


Required components:



### **OSRAM**

LED OSLON Square CSSRM2/CSSRM3

FWHM / FWTM 46.0° / 64.0° 94 % Efficiency Peak intensity 1.7 cd/lm LEDs/each optic White Light colour Required components:



Published: 05/08/2020



## **OPTICAL RESULTS (SIMULATED):**



 LED
 OSLON SSL 150


 FWHM / FWTM
 40.0° / 60.0°

 Efficiency
 94 %

 Peak intensity
 2.2 cd/lm

LEDs/each optic 1
Light colour White

Required components:




## SEOUL SEMICONDUCTOR

Light colour

LED Z5M4
FWHM / FWTM 48.0° / 68.0°
Efficiency 95 %
Peak intensity 1.5 cd/lm
LEDs/each optic 1

White

Required components:





# PRODUCT DATASHEET CP17591\_LEILA-SC-W

### **GENERAL INFORMATION:**

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

## **MATERIALS:**

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

## PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

## **LEDIL Oy**

Joensuunkatu 13 FI-24240 SALO Finland

#### LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

# Ledil Optics Technology (Shenzhen) Co., Ltd.

# 405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

## Local sales and technical support

www.ledil.com/ where\_to\_buy

### **Shipping locations**

Salo, Finland Hong Kong, China

### **Distribution Partners**

www.ledil.com/ where\_to\_buy