

AMY-35-M-B

~24° medium beam. Assembly with holder B compatible with Ø35 mm BJB and B+W connectors. Black version.

SPECIFICATION:

Dimensions Ø 34.9 mm
Height 11 mm
ROHS compliant yes ①



MPQ

MATERIALS:

ComponentTypeMaterialColourFinishAMY-35-MSingle lensPMMAclearAMY-35-HLD-BHolderPCblack

ORDERING INFORMATION:

» Box size: 480 x 280 x 300 mm


Component Qty in box MOQ

CP17971_AMY-35-M-B 1320 132 66 9.5

Box weight (kg)



PRODUCT CP17971_AMY-35-M-B



See also our general installation guide: www.ledil.com/installation_guide



OPTICAL RESULTS (MEASURED):



LED Vesta TW 6mm DP
FWHM / FWTM 26.0° / 53.0°
Efficiency 89 %
Peak intensity 2.9 cd/lm


LEDs/each optic 1

Light colour Tunable White

Required components:

Bender Wirth: 504 Typ B35L






CITIZEN

LED CLU700/701/702/703

FWHM / FWTM 23.0° / 47.0°
Efficiency 90 %
Peak intensity 3.6 cd/lm
LEDs/each optic 1
Light colour White

Required components: BJB: 47.360.1020





CITIZEN


LED CLU700/701/702/703

FWHM / FWTM 23.0° / 46.0° Efficiency 91 % Peak intensity 3.8 cd/lm LEDs/each optic 1

Light colour White Required components:

Bender Wirth: 634a Bayonet35L






CITIZEN


LED CLU7L3

FWHM / FWTM 23.0° / 39.0°
Efficiency 93 %
Peak intensity 4.6 cd/lm
LEDs/each optic 1

Light colour White Required components:

Bender Wirth: 667a Bayonet35






Published: 07/07/2021



OPTICAL RESULTS (MEASURED):






bridgelux

LED V10 Gen 8 FWHM / FWTM 28.0° / 57.0°

Efficiency 89 %
Peak intensity 2.6 cd/lm

LEDs/each optic 1
Light colour White

Required components: BJB: 47.360.1020




bridgelux

LED V10 Gen 8 FWHM / FWTM 30.0° / 59.0°

Efficiency 91 %
Peak intensity 2.5 cd/lm
LEDs/each optic 1

Light colour White Required components:

Bender Wirth: 634b Bayonet35L




bridgelux

LED V3 HD Gen 8 FC

FWHM / FWTM 22.0° / 42.0°
Efficiency 95 %
Peak intensity 5 cd/lm
LEDs/each optic 1
Light colour White

Required components:

Bender Wirth: 634c Bayonet35L




bridgelux.

LED V6 HD Gen 8 FWHM / FWTM 25.0° / 49.0° Efficiency 94 %

Peak intensity 3.7 cd/lm LEDs/each optic 1 Light colour White

Required components:

Bender Wirth: 634c Bayonet35L






bridgelux

LED Vesta DTW 6mm FWHM / FWTM 24.0° / 49.0 + 50.0°

Efficiency 93 %
Peak intensity 3.7 cd/lm
LEDs/each optic 1
Light colour White

Required components:

Bender Wirth: 652b Bayonet35L




bridgelux

LED Vesta DTW 9mm (4W/6W/12W)

FWHM / FWTM 28.0° / 55.0°
Efficiency 92 %
Peak intensity 2.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:

Bender Wirth: 652b Bayonet35L




CITIZEN

LED CLL02x/CLU02x (LES10)

FWHM / FWTM 29.0° / 59.0°
Efficiency 89 %
Peak intensity 2.5 cd/lm
LEDs/each optic 1
Light colour White

Required components: BJB: 47.360.1020




CITIZEN

LED CLU7A2/7A3
FWHM / FWTM 20.0° / 40.0°
Efficiency 93 %

Peak intensity 5.4 cd/lm
LEDs/each optic 1
Light colour White

Required components: BJB: 47.360.1020





CITIZEN

CLU7B2


 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 22.0° / 40.0° 93 %

Efficiency

Peak intensity 5.3 cd/lm LEDs/each optic

Light colour White

Required components: BJB: 47.360.1020



CREE - LED

LED CMA1306

FWHM / FWTM 24.0° / 47.0°


Efficiency 93 %

Peak intensity 4 cd/lm

LEDs/each optic 1 White Light colour

Required components:

Bender Wirth: 634c Bayonet35L



CREE + LED

LED CXA/B 15xx

FWHM / FWTM 26.0° / 54.0°


Efficiency 89 %

Peak intensity 3 cd/lm

LEDs/each optic

Light colour White

Required components: BJB: 47.360.1030



CREE - LED

CXA/B 15xx


FWHM / FWTM 28.0° / 56.0°

Efficiency 88 % Peak intensity 2.7 cd/lm

LEDs/each optic

White Light colour

Required components: BJB: 47.360.1030



Published: 07/07/2021






LED LUXEON CoB 1202/1203

FWHM / FWTM 28.0° / 56.0°
Efficiency 91 %
Peak intensity 2.8 cd/lm
LEDs/each optic 1
Light colour White

Required components: BJB: 47.360.1110




MUMILEDS

LED LUXEON CoB 1202HD FWHM / FWTM 25.0 + 26.0° / 50.0°

Efficiency 94 %
Peak intensity 3.7 cd/lm
LEDs/each optic 1
Light colour White
Required components:

Bender Wirth: 652a Bayonet35L




TRIDONIC

LED SLE SNC8 LES06
FWHM / FWTM 24.0° / 46.0°
Efficiency 93 %
Peak intensity 4.1 cd/lm
LEDs/each optic 1

White

Light colour Required components: BJB: 47.360.1020





PRODUCT DATASHEET CP17971_AMY-35-M-B

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Salo, Finland Hong Kong, China

Distribution Partners

www.ledil.com/ where_to_buy