

## AMY-70-RS-C

~13° spot beam with tight cutoff. Assembly with holder C compatible with LEDiL HEKLA. Black version.

#### **SPECIFICATION:**

**Dimensions** Ø 69.9 mm Height 14.7 mm **ROHS** compliant yes 🕕



#### **MATERIALS:**

**Type Material** Colour **Finish** Component AMY-70-RS Single lens **PMMA** clear AMY-70-HLD-C PC Holder black

#### **ORDERING INFORMATION:**

Component


CP18562\_AMY-70-RS-C

» Box size: 480 x 280 x 300 mm

Qty in box	MOQ	MPQ	Box weight (kg)
210	210	15	9.2



# **PRODUCT** CP18562\_AMY-70-RS-C



See also our general installation guide: www.ledil.com/installation\_guide




# **OPTICAL RESULTS (MEASURED):**

# **CITIZEN**

LED CLL02x/CLU02x (LES10)

FWHM / FWTM 14.0° / 26.0°
Efficiency 88 %
Peak intensity 8.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:

F17435\_HEKLA-G2-C





# **CITIZEN**

LED CLU700/701/702/703

FWHM / FWTM 9.0° / 18.0°
Efficiency 90 %
Peak intensity 17.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:

F17435\_HEKLA-G2-C







White

bridgelux

Light colour


LED V18 Gen 8 FWHM / FWTM 24.0° / 52.0°

Efficiency 82 %

Peak intensity 2.8 cd/lm LEDs/each optic 1

Required components:

Bender Wirth: 639b Hekla XL



bridgelux


LED V3 HD Gen 8 FWHM / FWTM 6.0° / 14.0°

Efficiency 93 %
Peak intensity 33.7 cd/lm

LEDs/each optic 1
Light colour White

Required components:

F15253\_HEKLA-SOCKET-A



bridgelux

LED V4 HD Gen 8


 FWHM / FWTM
 8.0° / 14.0°

 Efficiency
 93 %

Peak intensity 27.6 cd/lm
LEDs/each optic 1
Light colour White

Required components:

F15253\_HEKLA-SOCKET-A




bridgelux.

LED V6 Gen 8 FWHM / FWTM 10.0° / 18.0°

Efficiency 92 %
Peak intensity 18.2 cd/lm

LEDs/each optic 1
Light colour White
Required components:

F15253\_HEKLA-SOCKET-A







 LED
 V6 HD Gen 8

 FWHM / FWTM
 10.0° / 18.0°


 Efficiency
 91 %

 Peak intensity
 17.8 cd/lm

LEDs/each optic 1
Light colour White

F15255\_HEKLA-SOCKET-C

Required components:



#### bridgelux.

 LED
 V9 HD Gen 8

 FWHM / FWTM
 12.0° / 22.0°


 Efficiency
 90 %

 Peak intensity
 12.2 cd/lm

 LEDs/each optic
 1

LEDs/each optic 1
Light colour White
Required components:

F15859\_HEKLA-SOCKET-I




#### bridgelux

LED VERO18
FWHM / FWTM 28.0° / 56.0°
Efficiency 86 %
Peak intensity 2.5 cd/lm
LEDs/each optic 1
Light colour White

Required components:

C16142\_HEKLA-SOCKET-K




#### bridgelux.

LED Vesta DTW 13mm (21W)

FWHM / FWTM 10.0° / 20.0°
Efficiency 91 %
Peak intensity 15.7 cd/lm
LEDs/each optic 1
Light colour White

Required components:

Bender Wirth: 632b Hekla XL






bridgelux

LED Vesta DTW 15mm (33W)
FWHM / FWTM 20.0 + 19.0° / 40.0 + 39.0°

Efficiency 87 %
Peak intensity 4.7 cd/lm
LEDs/each optic 1
Light colour White

Required components:

Bender Wirth: 632b Hekla XL



bridgelux

 LED
 Vesta DTW 6mm

 FWHM / FWTM
 10.0° / 20.0°

 Efficiency
 91 %


 Peak intensity
 15.3 cd/lm

 LEDs/each optic
 1

LEDs/each optic 1
Light colour White
Required components:

Required components:

Bender Wirth: 652b Hekla




bridgelux

LED Vesta TW 13mm (18W) DP FWHM / FWTM 22.0 + 24.0° / 46.0 + 45.0°

Efficiency 85 %
Peak intensity 3.3 cd/lm
LEDs/each optic 1

Light colour Tunable White

Required components: C16142\_HEKLA-SOCKET-K F18158\_HEKLA-RZ-LENS Bender Wirth: 492 Typ L8




bridgelux.

LED Vesta TW 9mm (9W) DP FWHM / FWTM 15.0 + 14.0° / 28.0 + 29.0°

Efficiency 92 %
Peak intensity 7.5 cd/lm
LEDs/each optic 1

Light colour Tunable White

Required components: C16142\_HEKLA-SOCKET-K Bender Wirth: 489 Typ L8





# **CITIZEN**

LED CLL03x/CLU03x


FWHM / FWTM 21.0° / 40.0°

Efficiency 86 %

Peak intensity 4.3 cd/lm

LEDs/each optic 1
Light colour White

Required components:



#### CREE - LED

LED CMA1516


FWHM / FWTM 13.0° / 25.0°

Efficiency 89 %

Peak intensity 10.3 cd/lm

LEDs/each optic 1
Light colour White

Required components:



#### CREE + LED

LED CMA1840

FWHM / FWTM 20.0° / 39.0°

Efficiency 85 %


Peak intensity 4.3 cd/lm

LEDs/each optic 1

Light colour White

Required components:

Bender Wirth: 637a Hekla



### CREE - LED

LED CMT14xx

FWHM / FWTM 14.0° / 26.0°


Efficiency 87 %

Peak intensity 9.2 cd/lm LEDs/each optic 1

Light colour White

Required components:

F17435\_HEKLA-G2-C





### CREE \$\text{LED}

LED CMU15xx

 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 20.0° / 40.0°


Efficiency 85 %

Peak intensity 4.4 cd/lm

LEDs/each optic Light colour White

Required components:

Bender Wirth: 633a Hekla



#### CREE + LED

LED CMU15xx

FWHM / FWTM 20.0° / 38.0°

Efficiency 85 %


Peak intensity 4.6 cd/lm

LEDs/each optic 1

White Light colour

Required components:

F17438\_HEKLA-G2-I



# LUMILEDS

LED LUXEON CoB 1202/1203

FWHM / FWTM 12.0° / 24.0°

Efficiency 90 %


Peak intensity 10.8 cd/lm

LEDs/each optic 1

Light colour White

Required components:

F15858\_HEKLA-SOCKET-H



## **MUMILEDS**

LED LUXEON CoB 1202HD

FWHM / FWTM 10.0° / 20.0°

Efficiency 92 %


Peak intensity 16.2 cd/lm

LEDs/each optic

Required components:

White Light colour

F15848\_HEKLA-SOCKET-G








LED LUXEON CoB 1204/1205

FWHM / FWTM 20.0° / 35.0 + 36.0°

Efficiency 88 %
Peak intensity 5.2 cd/lm
LEDs/each optic 1
Light colour White

Required components:

Bender Wirth: 632a Hekla XL




# LUMILEDS

LED LUXEON CoB 1204HD FWHM / FWTM 14.0° / 26.0 + 24.0°

Efficiency 90 %
Peak intensity 9.7 cd/lm
LEDs/each optic 1
Light colour White
Required components:

F15858\_HEKLA-SOCKET-H




# LUMILEDS

LED LUXEON CoB 1205HD FWHM / FWTM 17.0 + 18.0° / 30.0°

Efficiency 89 %
Peak intensity 6.5 cd/lm
LEDs/each optic 1
Light colour White

Required components:

F15858\_HEKLA-SOCKET-H




# **MILEDS**

LED LUXEON CoB 1208

FWHM / FWTM 21.0° / 40.0°
Efficiency 88 %
Peak intensity 4.3 cd/lm
LEDs/each optic 1
Light colour White

Required components:

Bender Wirth: 632a Hekla XL








LED LUXEON CX Plus CoB - HD S04H9

FWHM / FWTM 14.0° / 26.0°
Efficiency 88 %
Peak intensity 9.2 cd/lm
LEDs/each optic 1
Light colour White

Required components:

F15255\_HEKLA-SOCKET-C



## **ELUMINUS**


 LED
 CxM-14 (18.5x18.5)

 FWHM / FWTM
 22.0° / 41.0°

 Efficiency
 86 %

Peak intensity 4 cd/lm
LEDs/each optic 1
Light colour White

Required components: F17438\_HEKLA-G2-I



# **SAMSUNG**

LED LC003D / LC006D / LC009D / LC013D

FWHM / FWTM 14.0° / 27.0°


Efficiency 88 %

Peak intensity 8.7 cd/lm

LEDs/each optic 1

Light colour White

Required components: F17435\_HEKLA-G2-C




# **SAMSUNG**

LED LC016D / LC019D / LC026D / LC033D

FWHM / FWTM 20.0° / 40.0°
Efficiency 85 %
Peak intensity 4.3 cd/lm
LEDs/each optic 1
Light colour White

Required components: F17438\_HEKLA-G2-I






# **XICATO**

LED XOB 14.5 mm
FWHM / FWTM 20.0° / 38.0°
Efficiency 77 %
Peak intensity 4.1 cd/lm
LEDs/each optic 1
Light colour White

Required components: F17438\_HEKLA-G2-I





# PRODUCT DATASHEET CP18562 AMY-70-RS-C

#### **GENERAL INFORMATION:**

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

#### **MATERIALS:**

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

#### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

#### **LEDIL Oy**

Joensuunkatu 13 FI-24240 SALO Finland

#### LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

# Ledil Optics Technology (Shenzhen) Co., Ltd.

# 405, Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

# Local sales and technical support

www.ledil.com/ where\_to\_buy

#### **Shipping locations**

Salo, Finland Hong Kong, China

#### **Distribution Partners**

12/12

www.ledil.com/ where\_to\_buy