Capacitive switch







See below:

Approvals and Compliances

Description

- Capacitive touch sensor as momentary push button (NO or NC) or as latching switch (LA)
- Protection against unintended switching
- Multicolor illumination
- Floating switch connections
- Laser lettering possible
- Vandal resistant
- Wires (8 wires for Multicolor, 4 wires otherwise)2

Unique Selling Proposition

- Variable supply voltage
- Constant LED intensity
- Inputs protected against overvoltage
- Galvanic separated outputs

Characteristics

- Housing made from stainless steel
- Various illumination colors and color combinations possible
- Touch surface made from scratch-resistant ceramics with area illumination or made from stainless steel with ring illumination
- Ring or area illumination
- Wearless, no moving parts
- Attractive design with or without finger guide available

Weblinks

html-datasheet, General Product Information, CAD-Drawings, Product News, Detailed request for product, Microsite

Important information

- The CPS is not suitable for use in sanitary or other applications exposed to water or other liquids.
- The housing is connected to gnd.

Technical Data

Electrical Data	
Switching Function	momentary (NO1) or latching
Switching Voltage	max. 42 VAC / 60 VDC
Switching Current	max. 100 mA
Electrical Rating	1 W
Switch Resistance OFF	> 10 MΩ
Switch Resistance ON	< 16Ω
Supply Voltage	5 - 28 VDC
Current Consumption all LEDs off	2.5 mA (switch is open)
	8.5 mA (switch is closed)
Current Consumption 1 LED on	8.0 mA (switch is open)
	14.0 mA (switch is closed)
Current Consumption 2 LED on	14.0 mA (switch is open)
	20.0 mA (switch is closed)
Current Consumption 3 LED on	19.0 mA (switch is open)
	25.0 mA (switch is closed)
Reverse Polarity Protection	yes
Short Circuit Protection	yes
Output Type	OptoMOS Relay
connection type	Wires (8 wires for Multicolor, 4 wires otherwise) ²

Mechanical Data	
Actuation Type	capacitive
Actuating Force	none
Shock Protection	IK 09
Mounting Depth	with Finger Guide: 30.3 mm
	without Finger Guide: 30 mm
Tightening Torque Plastic Nut	2.5 Nm
Climatical Data	
Operating Temperature	-40 to +60°C
Storage Temperature	-40 to +85°C
IP Protection Class Front Side	IP 67 acc. to IEC 60529
Salt Spray Test (acc. to DIN	24 h / 48 h / 96 h Residence Time
50021-SS)	
Material	
Housings	Stainless Steel
Actuator	Area Illumination: Ceramics
	Ring Illumination: Stainless steel
Illuminated Ring (Ring Illumi-	PMMA
nation)	
Seal Ring	NBR70

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

 $^{^{\}rm 1}$ on request also available as NC $/\,^{\rm 2}$ on request also available with cable or connector

Application standards

Application standards where the product can be used

Org	anization	Design	Standard	Description
<u>IEC</u>		Designed for applications acc.	IEC/UL 60950	IEC 60950-1 includes the basic requirements for the safety of information technology equipment.


Compliances

The product complies with following Guide Lines


The product complies with following duide Lines					
Identification	Details	Initiator	Description		
ROHS	RoHS	SCHURTER AG	EU Directive RoHS 2011/65/EU		
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.		

Dimension [mm]


CPS with ring illuminating, with finger guide




CPS with ring illuminating, no finger guide



CPS with area illuminating, with finger guide



CPS with area illuminating, no finger guide



A= illuminating area

B= CPS16: 19.5 mm CPS19: 23.0 mm CPS22: 25.5 mm

C= CPS16: M16x1 CPS19: M19x0.75 CPS22: M22x1

D= CPS16: 14.7 mm CPS19: 14.5 mm CPS22: 14.5 mm

E= CPS16: ø20 mm CPS19: ø24 mm CPS22: ø27.6 mm


For multicolor configurations


Connection wire assignment				
Wire-number	Wire color	function		
Wire 1	brown	Vin = 5 VDC28 VDC		
Wire 2	black	GND		
Wire 3	white	OUT1		
Wire 4	white	OUT2		
Wire 5	red	LED red		
		GND = ON		
		Open* = OFF		
		LED green		
Wire 6	green	GND = ON		
		Open* = OFF		
	blue	LED blue		
Wire 7		GND = ON		
		Open* = OFF		
Wire 8 black GND				


For all other configurations

Connection wire assignment			
Wire-number Wire color function			
Wire 1	brown	Vin = 5 VDC28 VDC	
Wire 2	black	GND	
Wire 3	white	OUT1	
Wire 4	white	OUT2	

Dimension








 $^{^{\}star}$ internal pull-up resistor to vcc = 3.3 V

Diagrams



Illumination options for RGB

Lighting type	Wire red	Wire green	Wire blue	Resulting Color
Multicolor Singlecolor	x			Red 🛑
Multicolor Singlecolor		х		Green 🛑
Multicolor Singlecolor			x	Blue
Multicolor RGB Additive 2	х	х		Yellow —
Multicolor RGB Additive 2	х		x	Magenta 🛑
Multicolor RGB Additive 2		х	x	Cyan 🔵
Multicolor RGB Additive 3	х	х	х	White 🔘

Lettering Colour of Laser Lettering


Material	Lettering Colour		
Stainless Steel	black	Filled letters	
Ceramic	black	Filled letters	

Order Index Lettering

Order index Letterin	9		
Laser Marking			
001 = A	021 = U	041 = ÷	061 = EIN
002 = B	022 = V	042 = ?	062 = AUS
$003 = \mathbf{C}$	023 = W	043 = =	063 = AUF
$004 = \mathbf{D}$	024 = X	044 = #	064 = AB
005 = E	025 = Y	045 = ?	065 = ON
006 = F	026 = Z	046 = ?	066 = OFF
007 = G	027 = 0	047 = ?	067 = UP
$008 = \mathbf{H}$	028 = 1	048 = ?	068 = DOWN
009 = I	029 = 2	049 = ?	069 = HIGH
010 = J	030 = 3	050 = ?	070 = LOW
011 = K	031 = 4	051 = %	071 = ON/OFF
012 = L	032 = 5	052 = ?	072 = START
013 = M	033 = 6	053 = CTRL	073 = RESET
014 = N	034 = 7	054 = RETURN	074 = 🕛
015 = O	035 = 8	055 = SHIFT	075 = 🌣
016 = P	036 = 9	056 = LOCK	076 = △
017 = Q	037 = +	057 = STOP	077 = ①
018 = R	038 = -	058 = ENTER	
019 = S	039 = .	059 = BACK	
020 = T	040 = x	060 = LINE	

Configuration code for configuring customized variants (example)

For customized variants a minimum order quantity of 100 pieces has to be fulfilled.



0WY

White/Yellow

All Variants

Diameter [mm]	Illumination	Illumination Color active / inactive	Finger Guide	Function	Actuator Material	Accessories	Order Number	
16	Backlighted	red / green	with	latching	Ceramic	Knurled nut	3-101-398	
16	Backlighted	red / green	without	latching	Ceramic	Knurled nut	3-101-395	
16	Backlighted	multicolor	without	latching	Ceramic	Knurled nut	3-101-394	
16	Ring Illumination	red / green	with	latching	Stainless Steel	Knurled nut	3-101-413	
16	Ring Illumination	red / green	without	latching	Stainless Steel	Knurled nut	3-101-401	
16	Ring Illumination	multicolor	without	latching	Stainless Steel	Knurled nut	3-101-400	
16	Backlighted	multicolor	with	momentary (NO)	Ceramic	Knurled nut	3-101-397	
16	Backlighted	multicolor	without	momentary (NO)	Ceramic	Knurled nut	3-101-403	
16	Ring Illumination	multicolor	with	momentary (NO)	Stainless Steel	Knurled nut	3-101-412	
16	Ring Illumination	multicolor	without	momentary (NO)	Stainless Steel	Knurled nut	3-101-399	
19	Backlighted	red / green	with	latching	Ceramic	Hexnut	3-101-418	
19	Backlighted	red / green	without	latching	Ceramic	Hexnut	3-101-416	
19	Backlighted	multicolor	without	latching	Ceramic	Hexnut	3-101-415	
19	Ring Illumination	red / green	with	latching	Stainless Steel	Hexnut	3-101-423	
19	Ring Illumination	red / green	without	latching	Stainless Steel	Hexnut	3-101-421	
19	Ring Illumination	multicolor	without	latching	Stainless Steel	Hexnut	3-101-420	
19	Backlighted	multicolor	with	momentary (NO)	Ceramic	Hexnut	3-101-417	
19	Backlighted	multicolor	without	momentary (NO)	Ceramic	Hexnut	3-101-414	
19	Ring Illumination	multicolor	with	momentary (NO)	Stainless Steel	Hexnut	3-101-422	
19	Ring Illumination	multicolor	without	momentary (NO)	Stainless Steel	Hexnut	3-101-419	
22	Backlighted	red / green	with	latching	Ceramic	Knurled nut	3-101-428	
22	Backlighted	red / green	without	latching	Ceramic	Knurled nut	3-101-426	
22	Backlighted	multicolor	without	latching	Ceramic	Knurled nut	3-101-425	
22	Ring Illumination	red / green	with	latching	Stainless Steel	Knurled nut	3-101-405	
22	Ring Illumination	red / green	without	latching	Stainless Steel	Knurled nut	3-101-431	
22	Ring Illumination	multicolor	without	latching	Stainless Steel	Knurled nut	3-101-430	
22	Backlighted	multicolor	with	momentary (NO)	Ceramic	Knurled nut	3-101-427	
22	Backlighted	multicolor	without	momentary (NO)	Ceramic	Knurled nut	3-101-424	
22	Ring Illumination	multicolor	with	momentary (NO)	Stainless Steel	Knurled nut	3-101-404	
22	Ring Illumination	multicolor	without	momentary (NO)	Stainless Steel	Knurled nut	3-101-429	

Common parameters for all standard variants:

- Housing material: stainless steel
- Switching current: 100 mA
- Illumination supply voltage: 5 V 28 V (variable) IP protection: IP 67- IK protection: IK 09
- Terminal connection: wires (8 wires for RGB, 4 wires otherwise), standard wire length is 200 $\,\mathrm{mm}$

Latching and momentary NO switch are open after power-up (protection against unintended switching) NO: normaly open

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

Minimum order quantity for standard variants with or without laser marking is 10 pieces.

Configurations which are not listed as standard in the table above can be requested as customized variants. The configuration code can be used for customizing this product. Please contact us in case more detail information is needed.

10 ST Packaging unit